

Eaton 171385

Eaton Moeller® series SL4 Filament lamp,
230V, 4W

PRODUCT NAME	Eaton Moeller® series SL4 Accessory Filament lamp
CATALOG NUMBER	171385
PRODUCT LENGTH/DEPTH	16 mm
PRODUCT HEIGHT	35 mm
PRODUCT WIDTH	16 mm
PRODUCT WEIGHT	0.007 kg
COMPLIANCES	CE

PRODUCT CATEGORY	Accessories
CONNECTION TO SMARTWIRE-DT	No
MOUNTING METHOD	BA15d lamp socket
COLOR	Colorless
LAMP SHAPE	Tube, single-ended
LAMP TYPE	Incandescent lamp
LIFESPAN, ELECTRICAL	3,000 h
SUITABLE FOR	Pointer Round flashing luminaire
POWER CONSUMPTION	4 W
SOCKET TYPE	BA15d
RATED OPERATIONAL VOLTAGE (UE) AT AC - MAX	230 V
DIAMETER	0 mm
AMBIENT OPERATING TEMPERATURE - MAX	60 °C
AMBIENT OPERATING TEMPERATURE - MIN	-30 °C
AVERAGE NOMINAL LIFESPAN	3000 hour
COLOR TEMPERATURE - MAX	2800 K
EFFECTIVE LUMINOUS FLUX	0 lm
LAMP POWER - MAX	4 W
LAMP POWER - MIN	4 W
LAMP VOLTAGE - MAX	230 V
LAMP VOLTAGE - MIN	230 V
NOMINAL CURRENT	0 mA

DECLARATIONS OF CONFORMITY	DA-DC-00004253.pdf
	DA-DC-00004257.pdf
	IL047005ZU
	eaton-operating-sl7-filament-lamp-dimensions-002.eps
	eaton-operating-sl7-filament-lamp-3d-drawing.eps

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com
© 2025

Follow us on social media to get the latest product and support information.

