



□□□□

Eaton 171399

Eaton Moeller® series SL7 Flashing light module, white, LED, 230 V

□□□□

PRODUCT NAME	Eaton Moeller® series SL7 Flashing light module
CATALOG NUMBER	171399
PRODUCT LENGTH/DEPTH	73 mm
PRODUCT HEIGHT	73 mm
PRODUCT WIDTH	73 mm
PRODUCT WEIGHT	0.082 kg
CERTIFICATIONS	CSA Class No.: NKCR7 CSA-C22.2 No. 94-91 IEC/EN 60947-5-1 UL UL report applies to both US and Canada UL Category Control No.: NKCR CSA-C22.2 No. 14-10 UL File No.: E29184 UL 508 IEC/EN 60529 CE Certified by UL for use in Canada

□□□□	
TYPE	Flashing light module
PRODUCT CATEGORY	SL signal towers
POLLUTION DEGREE	3
FLASHING FREQUENCY	2 Hz
CLIMATIC PROOFING	Damp heat, cyclic, to IEC 60068-2-30 Damp heat, constant, to IEC 60068-2-78
CONNECTION TO SMARTWIRE-DT	No
RATED IMPULSE WITHSTAND VOLTAGE (UIMP)	4000 V AC
ENCLOSURE COLOR	Black
FUNCTIONS	Blinker light
COLOR	Other
VOLTAGE TYPE	AC
MATERIAL	Cap: Polycarbonate (PC) Enclosure: Polycarbonate (PC)
MOUNTING POSITION	As required
DEGREE OF PROTECTION	NEMA 4X IP66
LAMP TYPE	LED
OVERVOLTAGE CATEGORY	III
CURRENT CONSUMPTION	34 mA at 230/240 V AC
LIFESPAN, ELECTRICAL	100,000 h
LIGHT TYPE	Flashing light
LIGHT MODULES	LED
NUMBER OF MODULES	Max. 10 (with base for mounting on both sides) Max. 5 (with standard base)
SHOCK RESISTANCE	Mechanical, According to IEC/EN 60068-2-27 15 g, Mechanical, According to IEC/EN 60068-2-27, Sinusoidal shock 11 ms
RATED OPERATIONAL VOLTAGE (UE) AT AC - MAX	240 V
RATED OPERATIONAL VOLTAGE (UE) AT AC - MIN	230 V
RATED OPERATIONAL	0 V

□□	
DECLARATIONS OF CONFORMITY	eaton-continuous-light-module-declaration-of-conformity-uk251039en.pdf
□□□□□	IL047004ZU
	eaton-operating-dimensions-005.eps
□□	eaton-operating-button-sl7-continuous-light-symbol-003.eps
	eaton-operating-sl7-flashing-light-symbol.eps

VOLTAGE (UE) AT DC - MAX	
RATED OPERATIONAL VOLTAGE (UE) AT DC - MIN	0 V
AMBIENT OPERATING TEMPERATURE - MAX	60 °C
AMBIENT OPERATING TEMPERATURE - MIN	-30 °C
LEAKAGE CURRENT	0.003 A
OUTSIDE DIAMETER	73 mm
RADIATION ANGLE	360 °
RATED INSULATION VOLTAGE (UI)	250 V

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY: