



□□□□□

Eaton 171406

Eaton Moeller® series SL7 Strobe light module, yellow, LED, 24 V

□□□□

PRODUCT NAME	Eaton Moeller® series SL7 Strobe light module
CATALOG NUMBER	171406
PRODUCT LENGTH/DEPTH	73 mm
PRODUCT HEIGHT	73 mm
PRODUCT WIDTH	73 mm
PRODUCT WEIGHT	0.08 kg
COMPLIANCES	CE Marked
CERTIFICATIONS	UL Listed CSA Certified cULus Listed UL 508 CSA Std. C22.2 No. 14-10 CSA Std. C22.2 No. 94-91 CSA Class No. NKCR7 UL Listed file E29184 IEC Rated CSA Class No.: NKCR7 IEC/EN 60529 UL CE UL Category Control No.: NKCR UL report applies to both US and Canada IEC/EN 60947-5-1 UL File No.: E29184 CSA-C22.2 No. 14-10 Certified by UL for use in Canada CSA-C22.2 No. 94-91
CATALOG NOTES	0

□□□□	
TYPE	Strobe light module
ENVIRONMENTAL RATING	IP66
PRODUCT CATEGORY	SL signal towers
VOLTAGE RATING	24 Vac/Vdc
FREQUENCY RATING	1.4 Hz
POLLUTION DEGREE	3
FLASHING FREQUENCY	1.4 Hz
CLIMATIC PROOFING	Damp heat, cyclic, to IEC 60068-2-30 Damp heat, constant, to IEC 60068-2-78
CONNECTION TO SMARTWIRE-DT	No
RATED IMPULSE WITHSTAND VOLTAGE (UIMP)	4000 V AC
ENCLOSURE COLOR	Black
FUNCTIONS	Flash light
ILLUMINATION	Strobe LED
COLOR	Yellow
VOLTAGE TYPE	AC/DC
MATERIAL	Cap: Polycarbonate (PC) Enclosure: Polycarbonate (PC)
MOUNTING POSITION	As required
DEGREE OF PROTECTION	NEMA 4 IP66
LAMP TYPE	LED
OVERVOLTAGE CATEGORY	III
CURRENT CONSUMPTION	max. 130 mA at 24 V AC/DC
LIFESPAN, ELECTRICAL	100,000 h
LIGHT TYPE	Strobe light
LIGHT MODULES	LED
NUMBER OF MODULES	Max. 5 (with standard base) Max. 10 (with base for mounting on both sides)
SHOCK RESISTANCE	15 g, Mechanical, According to IEC/EN 60068-2-27, Sinusoidal shock 11 ms Mechanical, According to IEC/EN 60068-2-27
RATED OPERATIONAL	24 V

□□	
DECLARATIONS OF CONFORMITY	eaton-continuous-light-module-declaration-of-conformity-uk251039en.pdf
□□□□□	IL047004ZU
□□□□□□□	Eaton Specification Sheet - SL7-FL24-Y
□□	eaton-operating-dimensions-005.eps eaton-operating-button-sl7-continuous-light-symbol-004.eps eaton-operating-sl7-strobe-light-module-symbol.eps

VOLTAGE (UE) AT AC - MAX	
RATED OPERATIONAL VOLTAGE (UE) AT AC - MIN	24 V
RATED OPERATIONAL VOLTAGE (UE) AT DC - MAX	24 V
RATED OPERATIONAL VOLTAGE (UE) AT DC - MIN	24 V
AMBIENT OPERATING TEMPERATURE - MAX	60 °C
AMBIENT OPERATING TEMPERATURE - MIN	-30 °C
LEAKAGE CURRENT	0.003 A
OUTSIDE DIAMETER	73 mm
QUANTITY	1
RADIATION ANGLE	360 °
RATED INSULATION VOLTAGE (UI)	250 V
ENCLOSURE	UL type 4, 4X, 13
SERIES	SL7

□□□□:
□□□□:
□□□:
□□: