

Eaton 174430

Eaton Moeller series Power Defense -
Molded Case Circuit Breaker. Circuit-
breaker, 4 p, 80A, N, 1

| | |
|---------------------------------|--|
| | |
| PRODUCT NAME | Eaton Moeller series Power Defense molded case circuit-breaker |
| CATALOG NUMBER | 174430 |
| PRODUCT LENGTH/DEPTH | 84.5 mm |
| PRODUCT HEIGHT | 145 mm |
| PRODUCT WIDTH | 120 mm |
| PRODUCT WEIGHT | 1.316 kg |
| COMPLIANCES | RoHS conform |
| CERTIFICATIONS | IEC VDE 0660 IEC/EN 60947 |

| | |
|---|--|
| AMPERAGE RATING | 80 A |
| VOLTAGE RATING | 690 V - 690 V |
| CIRCUIT BREAKER FRAME TYPE | LZM1 |
| FEATURES | Protection unit |
| 10.10 TEMPERATURE RISE | The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices. |
| 10.11 SHORT-CIRCUIT RATING | Is the panel builder's responsibility. The specifications for the switchgear must be observed. |
| 10.12 ELECTROMAGNETIC COMPATIBILITY | Is the panel builder's responsibility. The specifications for the switchgear must be observed. |
| 10.13 MECHANICAL FUNCTION | The device meets the requirements, provided the information in the instruction leaflet (IL) is observed. |
| 10.2.2 CORROSION RESISTANCE | Meets the product standard's requirements. |
| 10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES | Meets the product standard's requirements. |
| 10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT | Meets the product standard's requirements. |
| 10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS | Meets the product standard's requirements. |
| 10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION | Meets the product standard's requirements. |
| 10.2.5 LIFTING | Does not apply, since the entire switchgear needs to be evaluated. |
| 10.2.6 MECHANICAL IMPACT | Does not apply, since the entire switchgear needs to be evaluated. |

| | |
|-----------------------------------|---|
| CHARACTERISTIC CURVE | eaton-circuit-breaker-nzm-mccb-characteristic-curve-051.eps eaton-circuit-breaker-nzm-mccb-characteristic-curve.eps eaton-circuit-breaker-let-through-current-nzm-mccb-characteristic-curve-002.eps |
| DECLARATIONS OF CONFORMITY | DA-DC-03 N1 eaton-circuit-breaker-switch-nzm-mccb-dimensions-014.eps eaton-circuit-breaker-nzm-mccb-dimensions-018.eps |

| | |
|---|--|
| 10.2.7 INSCRIPTIONS | Meets the product standard's requirements. |
| 10.3 DEGREE OF PROTECTION OF ASSEMBLIES | Does not apply, since the entire switchgear needs to be evaluated. |
| 10.4 CLEARANCES AND CREEPAGE DISTANCES | Meets the product standard's requirements. |
| 10.5 PROTECTION AGAINST ELECTRIC SHOCK | Does not apply, since the entire switchgear needs to be evaluated. |
| 10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS | Does not apply, since the entire switchgear needs to be evaluated. |
| 10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS | Is the panel builder's responsibility. |
| 10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS | Is the panel builder's responsibility. |
| 10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH | Is the panel builder's responsibility. |
| 10.9.3 IMPULSE WITHSTAND VOLTAGE | Is the panel builder's responsibility. |
| 10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL | Is the panel builder's responsibility. |
| POLLUTION DEGREE | 3 |
| MOUNTING METHOD | DIN rail (top hat rail) mounting optional Built-in device fixed built-in technique Fixed |
| CLIMATIC PROOFING | Damp heat, cyclic, to IEC 60068-2-30 Damp heat, constant, to IEC 60068-2-78 |
| EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT | 16.32 W |
| UTILIZATION CATEGORY | A (IEC/EN 60947-2) |
| ISOLATION | 300 V AC (between the auxiliary contacts) 500 V AC (between auxiliary contacts and main contacts) |
| NUMBER OF AUXILIARY CONTACTS (CHANGE-OVER CONTACTS) | 0 |
| NUMBER OF AUXILIARY CONTACTS (NORMALLY | 0 |

| | |
|--|--|
| CLOSED CONTACTS) | |
| NUMBER OF AUXILIARY CONTACTS (NORMALLY OPEN CONTACTS) | 0 |
| PROTECTION AGAINST DIRECT CONTACT | Finger and back-of-hand proof to DIN EN 50274/VDE 0106 part 110 |
| DEGREE OF PROTECTION | In the area of the HMI devices: IP20 (basic protection type) IP20 |
| DIRECTION OF INCOMING SUPPLY | As required |
| ELECTRICAL CONNECTION TYPE OF MAIN CIRCUIT | Frame clamp |
| CURRENT RATING OF NEUTRAL CONDUCTOR | 200% of phase conductor |
| LIFESPAN, MECHANICAL | 20000 operations |
| OVERVOLTAGE CATEGORY | III |
| RATED OPERATIONAL CURRENT | 125 A (500 V DC-3, making and breaking capacity) 80 A (415 V AC-3, making and breaking capacity) 160 A (380/400 V AC-1, making and breaking capacity) 125 A (415 V AC-1, making and breaking capacity) 125 A (500 V DC-1, making and breaking capacity) 160 A (690 V AC-1, making and breaking capacity) 80 A (660-690 V AC-3, making and breaking capacity) |
| DEGREE OF PROTECTION (IP), FRONT SIDE | IP66 (with door coupling rotary handle) IP40 (with insulating surround) |
| DEGREE OF PROTECTION (TERMINATIONS) | IP10 (tunnel terminal) IP00 (terminations, phase isolator and band terminal) |
| NUMBER OF POLES | Four-pole |
| TERMINAL CAPACITY (COPPER STRIP) | Max. 9 segments of 9 mm x 0.8 mm at box terminal Min. 2 segments of 9 mm x 0.8 mm at box terminal |
| LIFESPAN, ELECTRICAL | 10000 operations at 500 V |

| | |
|--|--|
| | DC-1 7500 operations at 690 V AC-1 7500 operations at 415 V AC-3 5000 operations at 500 V DC-3 10000 operations at 400 V AC-1 7500 operations at 400 V AC-3 10000 operations at 415 V AC-1 5000 operations at 690 V AC-3 |
| FUNCTIONS | System and cable protection |
| TYPE | Circuit breaker |
| SPECIAL FEATURES | <ul style="list-style-type: none"> • Maximum back-up fuse, if the expected short-circuit currents at the installation location exceed the switching capacity of the circuit breaker (Rated short-circuit breaking capacity I_{cn}) • Rated current = rated uninterrupted current: 80 A • Set value in neutral conductor is synchronous with set value I_r of main pole. |
| APPLICATION | Use in unearthed supply systems at 690 V |
| SHOCK RESISTANCE | 20 g (half-sinusoidal shock 20 ms) |
| POSITION OF CONNECTION FOR MAIN CURRENT CIRCUIT | Front side |
| RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN) | 80 A |
| RELEASE SYSTEM | Thermomagnetic release |
| SHORT-CIRCUIT TOTAL BREAKTIME | < 10 ms |

| | |
|--|--|
| SHORT-CIRCUIT RELEASE NON-DELAYED SETTING - MAX | 800 A |
| SHORT-CIRCUIT RELEASE NON-DELAYED SETTING - MIN | 480 A |
| TERMINAL CAPACITY (CONTROL CABLE) | 0.75 mm ² - 2.5 mm ² (1x) 0.75 mm ² - 1.5 mm ² (2x) |
| TERMINAL CAPACITY (COPPER BUSBAR) | M8 at rear-side screw connection Min. 12 mm x 5 mm direct at switch rear-side connection Max. 16 mm x 5 mm direct at switch rear-side connection |
| TERMINAL CAPACITY (COPPER SOLID CONDUCTOR/CABLE) | 10 mm ² - 16 mm ² (1x) direct at switch rear-side connection 16 mm ² - 95 mm ² (1x) at tunnel terminal 6 mm ² - 16 mm ² (2x) direct at switch rear-side connection 10 mm ² - 16 mm ² (1x) at box terminal 6 mm ² - 16 mm ² (2x) at box terminal |
| TERMINAL CAPACITY (ALUMINUM SOLID CONDUCTOR/CABLE) | 16 mm ² (1x) at tunnel terminal |
| TERMINAL CAPACITY (COPPER STRANDED CONDUCTOR/CABLE) | 25 mm ² (2x) at box terminal 25 mm ² - 70 mm ² (1x) at box terminal 25 mm ² - 70 mm ² (1x) direct at switch rear-side connection 25 mm ² - 95 mm ² (1x) at tunnel terminal 25 mm ² (2x) direct at switch rear-side connection |
| TERMINAL CAPACITY (ALUMINUM STRANDED CONDUCTOR/CABLE) | 25 mm ² - 95 mm ² (1x) at tunnel terminal |
| HANDLE TYPE | Rocker lever |
| SHORT DELAY CURRENT SETTING (ISD) - MAX | 0 A |
| SHORT DELAY CURRENT SETTING (ISD) - MIN | 0 A |
| INSTANTANEOUS | 800 A |

| | |
|--|--------------|
| CURRENT SETTING (II) - MAX | |
| INSTANTANEOUS CURRENT SETTING (II) - MIN | 480 A |
| NUMBER OF OPERATIONS PER HOUR - MAX | 120 |
| OVERLOAD CURRENT SETTING (IR) - MAX | 80 A |
| OVERLOAD CURRENT SETTING (IR) - MIN | 63 A |
| OVERLOAD CURRENT SETTING (IR) | 63 A - 80 A |
| RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 230 V, 50/60 HZ | 85 kA |
| RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 400/415 V, 50/60 HZ | 50 kA |
| RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 440 V, 50/60 HZ | 35 kA |
| RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 525 V, 50/60 HZ | 10 kA |
| RATED SHORT-CIRCUIT MAKING CAPACITY ICM AT 400/415 V, 50/60 HZ | 105 kA |
| RATED SHORT-CIRCUIT MAKING CAPACITY ICM AT 440 V, 50/60 HZ | 74 kA |
| RATED SHORT-CIRCUIT MAKING CAPACITY ICM AT 525 V, 50/60 HZ | 40 kA |
| RATED SHORT-CIRCUIT MAKING CAPACITY ICM AT 690 V, 50/60 HZ | 17 kA |
| STANDARD TERMINALS | Box terminal |
| RATED SHORT-CIRCUIT MAKING CAPACITY ICM AT 240 V, 50/60 HZ | 187 kA |
| RATED IMPULSE WITHSTAND VOLTAGE (UIMP) AT AUXILIARY CONTACTS | 6000 V |

| | |
|--|----------|
| RATED IMPULSE WITHSTAND VOLTAGE (UIMP) AT MAIN CONTACTS | 6000 V |
| VOLTAGE RATING (DC) | 500 VDC |
| RATED INSULATION VOLTAGE (UI) | 690 V AC |

| |
|------------------------|
| PROJECT NAME: |
| PROJECT NUMBER: |
| PREPARED BY: |
| : |



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com
© 2025

Follow us on social media to get the latest product and support information.

