



Eaton 171307

Eaton Moeller® series SL4 Base module;400 mm aluminum tube

□□□□

PRODUCT NAME	Eaton Moeller® series SL4 Base module
CATALOG NUMBER	171307
PRODUCT LENGTH/DEPTH	43 mm
PRODUCT HEIGHT	484 mm
PRODUCT WIDTH	43 mm
PRODUCT WEIGHT	0.214 kg
CERTIFICATIONS	CSA-C22.2 No. 94-91 UL report applies to both US and Canada UL Category Control No.: NKCR IEC/EN 60947-5-1 CSA-C22.2 No. 14-10 Certified by UL for use in Canada CE UL UL 508 UL File No.: E29184 CSA Class No.: NKCR7 IEC/EN 60529

□□□□

TYPE	Base module
PRODUCT CATEGORY	SL signal towers
FITTED WITH:	Cover Aluminum tube Banjo bolt
POLLUTION DEGREE	3
CLIMATIC PROOFING	Damp heat, cyclic, to IEC 60068-2-30 Damp heat, constant, to IEC 60068-2-78
CONNECTION TO SMARTWIRE-DT	No
MOUNTING METHOD	Tube Floor Horizontal Bracket
RATED IMPULSE WITHSTAND VOLTAGE (UIMP)	4000 V AC
AMBIENT OPERATING TEMPERATURE - MAX	60 °C
AMBIENT OPERATING TEMPERATURE - MIN	-30 °C
RATED INSULATION VOLTAGE (UI)	250 V
TUBE LENGTH	400 mm
COLOR	Other
MOUNTING POSITION	As required
DEGREE OF PROTECTION	IP66 NEMA 4 NEMA 13 NEMA 4X
OVERVOLTAGE CATEGORY	III
CONNECTION TYPE (AUXILIARY CIRCUIT)	Spring clamp connection
TERMINAL CAPACITY (AWG)	24 - 16
NUMBER OF MODULES	Max. 10 (with base for mounting on both sides) Max. 5 (with standard base) Max. 5
TERMINAL CAPACITY (SOLID/FLEXIBLE WITH FERRULE)	0.25 - 1.5 mm ²
SHOCK RESISTANCE	15 g, Mechanical, According to IEC/EN 60068-2-27, Sinusoidal

□□

DECLARATIONS OF CONFORMITY	eaton-continuous-light-module-declaration-of-conformity-uk251039en.pdf
□□□□□	IL047001ZU
	eaton-operating-sl4-base-module-dimensions-017.eps
□□	eaton-operating-button-sl7-base-module-symbol.eps
	eaton-operating-sl4-base-module-3d-drawing-006.eps

	shock 11 ms Mechanical, According to IEC/EN 60068-2-27
RATED OPERATIONAL VOLTAGE	230/240 V AC ± 10 % 24 V AC/DC ± 10 % 110/120 V AC ± 10 %
TERMINAL CAPACITY (FLEXIBLE WITH FERRULE AND PLASTIC COLLAR)	0.25 - 0.75 mm²
TERMINAL CAPACITY (SOLID/FLEXIBLE)	0.2 - 1.5 mm²

□□□□:
□□□□:
□□□:
□□: