



Eaton 171309

Eaton Moeller® series SL4 Base module,
quick-mounting, 250 mm aluminum tube

□□□□

PRODUCT NAME	Eaton Moeller® series SL4 Base module
CATALOG NUMBER	171309
PRODUCT LENGTH/DEPTH	81 mm
PRODUCT HEIGHT	298 mm
PRODUCT WIDTH	81 mm
PRODUCT WEIGHT	0.22 kg
CERTIFICATIONS	Certified by UL for use in Canada UL CSA-C22.2 No. 14-10 CE CSA Class No.: NKCR7 UL 508 UL Category Control No.: NKCR UL File No.: E29184 UL report applies to both US and Canada IEC/EN 60529 IEC/EN 60947-5-1 CSA-C22.2 No. 94-91

□□□□

TYPE	Base module
PRODUCT CATEGORY	SL signal towers
FITTED WITH:	Cover Base adapter for slipping onto place (rapid mounting and wiring system)
POLLUTION DEGREE	3
CLIMATIC PROOFING	Damp heat, cyclic, to IEC 60068-2-30 Damp heat, constant, to IEC 60068-2-78
CONNECTION TO SMARTWIRE-DT	No
MOUNTING METHOD	Floor Bracket Horizontal
RATED IMPULSE WITHSTAND VOLTAGE (UIMP)	4000 V AC
AMBIENT OPERATING TEMPERATURE - MAX	60 °C
AMBIENT OPERATING TEMPERATURE - MIN	-30 °C
RATED INSULATION VOLTAGE (UI)	250 V
TUBE LENGTH	250 mm
COLOR	Other
MOUNTING POSITION	As required
DEGREE OF PROTECTION	IP66 NEMA 4X NEMA 4 NEMA 13
OVERVOLTAGE CATEGORY	III
CONNECTION TYPE (AUXILIARY CIRCUIT)	Screw connection
TERMINAL CAPACITY (AWG)	24 - 16
NUMBER OF MODULES	Max. 5 Max. 10 (with base for mounting on both sides) Max. 5 (with standard base)
TERMINAL CAPACITY (SOLID/FLEXIBLE WITH FERRULE)	0.25 - 1.5 mm²
SHOCK RESISTANCE	15 g, Mechanical, According to IEC/EN

□□

DECLARATIONS OF CONFORMITY	eaton-continuous-light-module-declaration-of-conformity-uk251039en.pdf
□□□□□	IL047007ZU
	eaton-operating-sl4-base-module-dimensions-006.eps
□□	eaton-operating-signal-module-sl4-base-module-3d-drawing.eps
	eaton-operating-button-sl7-base-module-symbol.eps

	60068-2-27, Sinusoidal shock 11 ms Mechanical, According to IEC/EN 60068-2-27
RATED OPERATIONAL VOLTAGE	24 V AC/DC ± 10 % 110/120 V AC ± 10 % 230/240 V AC ± 10 %
TERMINAL CAPACITY (FLEXIBLE WITH FERRULE AND PLASTIC COLLAR)	0.25 - 0.75 mm²
TERMINAL CAPACITY (SOLID/FLEXIBLE)	0.2 - 1.5 mm²

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



0000
Eaton House
30 Pembroke Road
Dublin 4, 000
Eaton.com

© 2025 00 00000000

Follow us on social media to get the latest product and support information.

