

# Eaton 171316

Eaton Moeller® series SL4 Continuous light  
module, white, LED, 24 V

PRODUCT NAME	Eaton Moeller® series SL4 Continuous light module
CATALOG NUMBER	171316
PRODUCT LENGTH/DEPTH	43 mm
PRODUCT HEIGHT	75 mm
PRODUCT WIDTH	43 mm
PRODUCT WEIGHT	0.042 kg
CERTIFICATIONS	CE IEC/EN 60529 UL report applies to both US and Canada CSA-C22.2 No. 94-91 UL File No.: E29184 CSA-C22.2 No. 14-10 UL Category Control No.: NKR7 Certified by UL for use in Canada CSA Class No.: NKR7 IEC/EN 60947-5-1 UL UL 508

<b>TYPE</b>	Continuous light module
<b>PRODUCT CATEGORY</b>	SL signal towers
<b>POLLUTION DEGREE</b>	3
<b>CLIMATIC PROOFING</b>	Damp heat, cyclic, to IEC 60068-2-30 Damp heat, constant, to IEC 60068-2-78
<b>CONNECTION TO SMARTWIRE-DT</b>	No
<b>RATED IMPULSE WITHSTAND VOLTAGE (UIMP)</b>	4000 V AC
<b>ENCLOSURE COLOR</b>	Black
<b>FUNCTIONS</b>	Continuous light
<b>COLOR</b>	Other
<b>VOLTAGE TYPE</b>	AC/DC
<b>MATERIAL</b>	Enclosure: Polycarbonate (PC) Cap: Polycarbonate (PC)
<b>MOUNTING POSITION</b>	As required
<b>DEGREE OF PROTECTION</b>	IP66 NEMA 4
<b>LAMP TYPE</b>	LED
<b>OVERVOLTAGE CATEGORY</b>	III
<b>CURRENT CONSUMPTION</b>	50 mA at 24 V AC/DC
<b>LIFESPAN, ELECTRICAL</b>	100,000 h
<b>LIGHT TYPE</b>	Continuous light
<b>LIGHT MODULES</b>	LED
<b>NUMBER OF MODULES</b>	Max. 10 (with base for mounting on both sides) Max. 5 (with standard base)
<b>SHOCK RESISTANCE</b>	Mechanical, According to IEC/EN 60068-2-27 15 g, Mechanical, According to IEC/EN 60068-2-27, Sinusoidal shock 11 ms
<b>RATED OPERATIONAL VOLTAGE (UE) AT AC - MAX</b>	24 V
<b>RATED OPERATIONAL VOLTAGE (UE) AT AC - MIN</b>	24 V

<b>DECLARATIONS OF CONFORMITY</b>	<a href="#">eaton-continuous-light-module-declaration-of-conformity-uk251039en.pdf</a>
	<a href="#">IL047001ZU</a>
	<a href="#">eaton-operating-sl4-continuous-light-dimensions.eps</a>
	<a href="#">eaton-operating-sl7-continuous-light-symbol-002.eps</a>
	<a href="#">eaton-operating-button-sl7-continuous-light-symbol-003.eps</a>

<b>RATED OPERATIONAL VOLTAGE (UE) AT DC - MAX</b>	24 V
<b>RATED OPERATIONAL VOLTAGE (UE) AT DC - MIN</b>	24 V
<b>AMBIENT OPERATING TEMPERATURE - MAX</b>	60 °C
<b>AMBIENT OPERATING TEMPERATURE - MIN</b>	-30 °C
<b>LEAKAGE CURRENT</b>	0.003 A
<b>OUTSIDE DIAMETER</b>	43 mm
<b>RADIATION ANGLE</b>	360 °
<b>RATED INSULATION VOLTAGE (UI)</b>	250 V

<b>PROJECT NAME:</b>
<b>PROJECT NUMBER:</b>
<b>PREPARED BY:</b>
:



Eaton House  
30 Pembroke Road  
Dublin 4,  
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

