

Eaton 177012

Eaton DA1 Variable frequency drive, 500 V
AC, 3-phase, 2.1 A, 0.75 kW, IP66/NEMA 4X,
OLED display, Local controls

PRODUCT NAME	Eaton DA1 Variable frequency drive
CATALOG NUMBER	177012
PRODUCT LENGTH/DEPTH	239.3 mm
PRODUCT HEIGHT	257 mm
PRODUCT WIDTH	188 mm
PRODUCT WEIGHT	1.8 kg
CERTIFICATIONS	CUL IEC/EN61800-3 RCM Safety: EN 61800-5-1: 2003
	UL 508C UL Category Control No.: NMMS, NMMS7 CE UL report applies to both US and Canada UkrSEPRO Certified by UL for use in Canada CSA-C22.2 No. 14 EAC IEC/EN 61800-3 IEC/EN61800-5 RoHS, ISO 9001 Specification for general requirements: IEC/EN 61800-2 UL UL File No.: E172143
CATALOG NOTES	The brake resistors are assigned based on the maximum rated power of the variable frequency drive. Additional brake resistors and designs (e.g. different duty cycles) are

PRODUCT CATEGORY	Variable frequency drives
FEATURES	Parameterization: drivesConnect Parameterization: drivesConnect mobile (App) Parameterization: Fieldbus Parameterization: Keypad
10.10 TEMPERATURE RISE	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 SHORT-CIRCUIT RATING	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 ELECTROMAGNETIC COMPATIBILITY	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 MECHANICAL FUNCTION	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.
10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	Meets the product standard's requirements.
10.2.5 LIFTING	Does not apply, since the entire switchgear needs to be evaluated.

INSTALLATION VIDEOS	Video PowerXL DA1
	eaton-powerxl-variable-frequency-drives-dc1-da1-brochure-br040001en-en-us.pdf
	eaton-powerxl-da1-application-manual-mn04020006z-en-us.pdf
	eaton-powerxl-da1-installation-manual-mn04020005z-en-us.pdf
	eaton-frequency-inverter-da1-dimensions-006.eps
	eaton-frequency-inverter-da1-3d-drawing-005.eps

10.2.6 MECHANICAL IMPACT	Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 INSCRIPTIONS	Meets the product standard's requirements.
10.3 DEGREE OF PROTECTION OF ASSEMBLIES	Does not apply, since the entire switchgear needs to be evaluated.
10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
FITTED WITH:	OLED display PC connection Internal DC link Breaking resistance Brake chopper Additional PCB protection Control unit Local controls IGBT inverter
CLIMATIC PROOFING	< 95 average relative humidity (RH), no condensation, no corrosion
CONNECTION TO SMARTWIRE-DT	No
OPERATING MODE	Optional: Vector control with feedback (CLV) Speed control with slip compensation U/f control Sensorless vector control (SLV)

FRAME SIZE	FS2
ALTITUDE	Above 1000 m with 1 % derating per 100 m Max. 4000 m Max. 1000 m
ENVIRONMENTAL CLASS	3C2, 3S2 (Air quality)
APPLICATION IN DOMESTIC AND COMMERCIAL AREA PERMITTED	Yes
MAINS SWITCH-ON FREQUENCY	Maximum of one time every 30 seconds
APPLICATION IN INDUSTRIAL AREA PERMITTED	Yes
AMBIENT OPERATING TEMPERATURE - MAX	40 °C
AMBIENT OPERATING TEMPERATURE - MIN	-10 °C
AMBIENT OPERATING TEMPERATURE AT 150% OVERLOAD - MAX	40 °C
AMBIENT OPERATING TEMPERATURE AT 150% OVERLOAD - MIN	-10 °C
AMBIENT STORAGE TEMPERATURE - MAX	60 °C
AMBIENT STORAGE TEMPERATURE - MIN	-40 °C
APPARENT POWER AT 600 V	2.18 kVA
MOUNTING POSITION	Vertical
RELATIVE SYMMETRIC NET FREQUENCY TOLERANCE	10 %
RELATIVE SYMMETRIC NET VOLTAGE TOLERANCE	10 %
PROTECTION	Finger and back-of-hand proof, Protection against direct contact (BGV A3, VBG4)
HEAT DISSIPATION DETAILS	Operation (with 150 % overload)
RATED OPERATIONAL POWER AT 525 V, 50 HZ, 3-PHASE	1.1 kW
RESOLUTION	0.1 Hz (Frequency resolution, setpoint value)

STATIC HEAT DISSIPATION, NON-CURRENT-DEPENDENT PVS	0 W
SWITCH-ON THRESHOLD FOR THE BRAKING TRANSISTOR	975 VDC
VOLTAGE RATING - MAX	600 VAC
COMMUNICATION INTERFACE	Ethernet IP, optional DeviceNet, optional CANopen®, built in EtherCAT, optional Modbus-TCP, optional PROFINET, optional PROFIBUS, optional Modbus RTU, built in OP-Bus (RS485), built in
CONVERTER TYPE	U converter
DEGREE OF PROTECTION	NEMA 4X IP66
PROTOCOL	PROFINET IO CAN Other bus systems EtherNet/IP MODBUS DeviceNet PROFIBUS TCP/IP
ASSIGNED MOTOR CURRENT IM AT 500 V, 50 HZ, 150% OVERLOAD	1.5 A
ASSIGNED MOTOR CURRENT IM AT 525 V, 50 HZ, 150% OVERLOAD	2 A
ASSIGNED MOTOR CURRENT IM AT 550 - 600 V, 60 HZ, 150% OVERLOAD	1.7 A
SYSTEM CONFIGURATION TYPE	AC supply systems with earthed center point
ASSIGNED MOTOR POWER AT 575/600 V, 60 HZ, 3-PHASE	1 HP
BRAKING RESISTANCE	600 Ω
EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT PVID	22.5 W
HEAT DISSIPATION CAPACITY PDISS	0 W
HEAT DISSIPATION PER	0 W

POLE, CURRENT-DEPENDENT PVID	
INPUT CURRENT ILN AT 150% OVERLOAD	3.4 A
BRAKING TORQUE	<p>Max. 100 % of rated operational current I_e with external braking resistor - Main circuit</p> <p>Max. 100 % of rated operational current I_e, variable, DC - Main circuit</p> <p>Max. 30 % MN, Standard - Main circuit</p>
CABLE LENGTH	<p>150 m, unscreened, maximum permissible, Motor feeder</p> <p>300 m, unscreened, with motor choke, maximum permissible, Motor feeder</p> <p>100 m, screened, maximum permissible, Motor feeder</p> <p>200 m, screened, with motor choke, maximum permissible, Motor feeder</p>
FUNCTIONS	4-quadrant operation possible
OUTPUT VOLTAGE (U2)	<p>500 V AC, 3-phase</p> <p>600 V AC, 3-phase</p>
NUMBER OF INPUTS (ANALOG)	2
NUMBER OF INPUTS (DIGITAL)	5
NUMBER OF OUTPUTS (DIGITAL)	2
STARTING CURRENT - MAX	200 %, I_H , max. starting current (High Overload), for 4 seconds every 40 seconds, Power section
NUMBER OF PHASES (INPUT)	3
NUMBER OF RELAY OUTPUTS	2 (parameterizable, 1 N/O and 1 changeover contact, 6 A (250 V, AC-1) / 5 A (30 V, DC-1))
NUMBER OF PHASES (OUTPUT)	3
POWER CONSUMPTION	22.5 W
RATED CONTROL SUPPLY VOLTAGE	10 V DC (U_s , max. 10 mA)

EFFICIENCY	97 % (η)
RATED CONTROL VOLTAGE (UC)	24 V DC (external, max. 100 mA)
SUPPLY FREQUENCY	50/60 Hz
LEAKAGE CURRENT AT GROUND IPE - MAX	2.1 mA
MAINS VOLTAGE - MAX	600 V
MAINS VOLTAGE - MIN	500 V
NOMINAL OUTPUT CURRENT I2N	2.1 A
NUMBER OF HW-INTERFACES (INDUSTRIAL ETHERNET)	0
NUMBER OF HW-INTERFACES (OTHER)	0
NUMBER OF HW-INTERFACES (PARALLEL)	0
NUMBER OF HW-INTERFACES (RS-232)	0
NUMBER OF HW-INTERFACES (RS-422)	0
NUMBER OF HW-INTERFACES (RS-485)	1
NUMBER OF HW-INTERFACES (SERIAL TTY)	0
NUMBER OF HW-INTERFACES (USB)	0
NUMBER OF INTERFACES (PROFINET)	0
NUMBER OF OUTPUTS (ANALOG)	2
OUTPUT AT LINEAR LOAD AT RATED OUTPUT VOLTAGE - MAX	0.75 kW
OUTPUT AT QUADRATIC LOAD AT RATED OUTPUT VOLTAGE - MAX	0.75 kW
OUTPUT FREQUENCY - MAX	500 Hz
OUTPUT FREQUENCY - MIN	0 Hz
OUTPUT VOLTAGE - MAX	600 V
OVERLOAD CURRENT IL AT 150% OVERLOAD	3.15 A
SUITABLE FOR	Branch circuits, (UL/CSA)
SWITCHING FREQUENCY	8 kHz, 4 - 24 kHz adjustable (audible),

	fPWM, Power section, Main circuit
RATED OPERATIONAL VOLTAGE	500 V AC, 3-phase 600 V AC, 3-phase
SHORT-CIRCUIT PROTECTION RATING	6 A, UL (Class CC or J), Safety device (fuse or miniature circuit-breaker), Power Wiring
RATED FREQUENCY - MAX	62 Hz
RATED FREQUENCY - MIN	48 Hz
RATED OPERATIONAL CURRENT (IE) AT 150% OVERLOAD	2.1 A
RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)	2.1 A
RATED OPERATIONAL POWER AT 500 V, 50 HZ, 3-PHASE	0.75 kW
SAFETY FUNCTION/LEVEL	STO (Safe Torque Off, SIL2, PLc Cat 2)
SHORT-CIRCUIT PROTECTION	LPJ fuse used together with J60060-3 fuse base, Power wiring, Assigned switching and protective elements NH fuse used together with TB00-D fuse base, Power wiring, Assigned switching and protective elements
HEAT DISSIPATION AT CURRENT/SPEED	48 W at 100% current and 0% speed 48 W at 25% current and 0% speed 48 W at 50% current and 0% speed 49 W at 100% current and 50% speed 49 W at 25% current and 50% speed 49 W at 50% current and 50% speed 51 W at 100% current and 90% speed 51 W at 50% current and 90% speed

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

