

Eaton 171318

Eaton Moeller® series SL4 Continuous light module, orange, LED, 24 V

PRODUCT NAME	Eaton Moeller® series SL4 Continuous light module
CATALOG NUMBER	171318
PRODUCT LENGTH/DEPTH	43 mm
PRODUCT HEIGHT	75 mm
PRODUCT WIDTH	43 mm
PRODUCT WEIGHT	0.042 kg
COMPLIANCES	CE Marked
CERTIFICATIONS	UL 508 UL Listed CSA Certified cULus Listed UL Listed file E29184 CSA Std. C22.2 No. 94-91 CSA Class No. NKCR7 CSA Std. C22.2 No. 14-10 IEC Rated IEC/EN 60529 CSA-C22.2 No. 14-10 CE UL report applies to both US and Canada CSA-C22.2 No. 94-91 Certified by UL for use in Canada UL File No.: E29184 UL Category Control No.: NKCR CSA Class No.: NKCR7 IEC/EN 60947-5-1 UL
CATALOG NOTES	0

TYPE	Continuous light module
ENVIRONMENTAL RATING	IP66
PRODUCT CATEGORY	SL signal towers
VOLTAGE RATING	24 Vac/Vdc
POLLUTION DEGREE	3
CLIMATIC PROOFING	Damp heat, constant, to IEC 60068-2-78 Damp heat, cyclic, to IEC 60068-2-30
CONNECTION TO SMARTWIRE-DT	No
RATED IMPULSE WITHSTAND VOLTAGE (UIMP)	4000 V AC
ENCLOSURE COLOR	Black
FUNCTIONS	Continuous light
ILLUMINATION	Continuous LED
COLOR	Orange
VOLTAGE TYPE	AC/DC
MATERIAL	Enclosure: Polycarbonate (PC) Cap: Polycarbonate (PC)
MOUNTING POSITION	As required
DEGREE OF PROTECTION	IP66 NEMA 13
LAMP TYPE	LED
OVERVOLTAGE CATEGORY	III
CURRENT CONSUMPTION	50 mA at 24 V AC/DC
LIFESPAN, ELECTRICAL	100,000 h
LIGHT TYPE	Continuous light
LIGHT MODULES	LED
NUMBER OF MODULES	Max. 10 (with base for mounting on both sides) Max. 5 (with standard base)
SHOCK RESISTANCE	15 g, Mechanical, According to IEC/EN 60068-2-27, Sinusoidal shock 11 ms Mechanical, According to IEC/EN 60068-2-27
RATED OPERATIONAL	24 V

DECLARATIONS OF CONFORMITY	DA-DC-00004253.pdf
	DA-DC-00004257.pdf
	IL047001ZU
	Eaton Specification Sheet - SL4-L24-A
	eaton-operating-sl4-continuous-light-dimensions.eps
	eaton-operating-button-sl7-continuous-light-symbol.eps
	eaton-operating-sl7-continuous-light-symbol-002.eps

VOLTAGE (UE) AT AC - MAX	
RATED OPERATIONAL VOLTAGE (UE) AT AC - MIN	24 V
RATED OPERATIONAL VOLTAGE (UE) AT DC - MAX	24 V
RATED OPERATIONAL VOLTAGE (UE) AT DC - MIN	24 V
AMBIENT OPERATING TEMPERATURE - MAX	60 °C
AMBIENT OPERATING TEMPERATURE - MIN	-30 °C
LEAKAGE CURRENT	0.003 A
OUTSIDE DIAMETER	43 mm
QUANTITY	1
RADIATION ANGLE	360 °
RATED INSULATION VOLTAGE (UI)	250 V
ENCLOSURE	UL type 4, 4X, 13
SERIES	SL4

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
 30 Pembroke Road
 Dublin 4,
 Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

