

Eaton 177313

Eaton Moeller® series SL4 Base module;
800-mm aluminum tube and foot

PRODUCT NAME	Eaton Moeller® series SL4 Base module
CATALOG NUMBER	177313
PRODUCT LENGTH/DEPTH	72 mm
PRODUCT HEIGHT	869 mm
PRODUCT WIDTH	72 mm
PRODUCT WEIGHT	0.8 kg
CERTIFICATIONS	IEC/EN 60529 IEC/EN 60947-5-1

TYPE	Base module
PRODUCT CATEGORY	SL signal towers
FITTED WITH:	Cover Aluminum tube Plastic foot
CLIMATIC PROOFING	Damp heat, cyclic, to IEC 60068-2-30 Damp heat, constant, to IEC 60068-2-78
CONNECTION TO SMARTWIRE-DT	No
MOUNTING METHOD	Floor Horizontal Bracket
RATED IMPULSE WITHSTAND VOLTAGE (UIMP)	4000 V AC
AMBIENT OPERATING TEMPERATURE - MAX	60 °C
AMBIENT OPERATING TEMPERATURE - MIN	-30 °C
RATED INSULATION VOLTAGE (UI)	250 V
TUBE LENGTH	800 mm
COLOR	Other
MOUNTING POSITION	As required
DEGREE OF PROTECTION	IP66 NEMA 4 NEMA 4X NEMA 13
CONNECTION TYPE (AUXILIARY CIRCUIT)	Spring clamp connection
TERMINAL CAPACITY (AWG)	24 - 16
NUMBER OF MODULES	Max. 5 (with standard base) Max. 10 (with base for mounting on both sides) Max. 5
TERMINAL CAPACITY (SOLID/FLEXIBLE WITH FERRULE)	0.25 - 1.5 mm ²
SHOCK RESISTANCE	15 g, Mechanical, According to IEC/EN 60068-2-27, Sinusoidal shock 11 ms Mechanical, According to

DECLARATIONS OF CONFORMITY	DA-DC-00004253.pdf
	DA-DC-00004257.pdf
	IL047001ZU
	eaton-operating-sl4-base-module-dimensions-003.eps
	eaton-operating-sl4-base-module-3d-drawing.eps
	eaton-operating-button-sl7-base-module-symbol.eps

	IEC/EN 60068-2-27
RATED OPERATIONAL VOLTAGE	24 V AC/DC ± 10 % 230/240 V AC ± 10 % 110/120 V AC ± 10 %
TERMINAL CAPACITY (FLEXIBLE WITH FERRULE AND PLASTIC COLLAR)	0.25 - 0.75 mm ²
TERMINAL CAPACITY (SOLID/FLEXIBLE)	0.2 - 1.5 mm ²

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
: