



Eaton 171394

Eaton Moeller® series SL7 Flashing light module, yellow, LED, 120 V

□□□□

PRODUCT NAME	Eaton Moeller® series SL7 Flashing light module
CATALOG NUMBER	171394
PRODUCT LENGTH/DEPTH	73 mm
PRODUCT HEIGHT	73 mm
PRODUCT WIDTH	73 mm
PRODUCT WEIGHT	0.082 kg
CERTIFICATIONS	UL Category Control No.: NKCR CSA-C22.2 No. 94-91 UL UL report applies to both US and Canada CSA-C22.2 No. 14-10 CSA Class No.: NKCR7 CE UL File No.: E29184 IEC/EN 60947-5-1 Certified by UL for use in Canada IEC/EN 60529 UL 508

□□□□	
TYPE	Flashing light module
PRODUCT CATEGORY	SL signal towers
POLLUTION DEGREE	3
FLASHING FREQUENCY	2 Hz
CLIMATIC PROOFING	Damp heat, cyclic, to IEC 60068-2-30 Damp heat, constant, to IEC 60068-2-78
CONNECTION TO SMARTWIRE-DT	No
RATED IMPULSE WITHSTAND VOLTAGE (UIMP)	4000 V AC
ENCLOSURE COLOR	Black
FUNCTIONS	Blinker light
COLOR	Yellow
VOLTAGE TYPE	AC
MATERIAL	Cap: Polycarbonate (PC) Enclosure: Polycarbonate (PC)
MOUNTING POSITION	As required
DEGREE OF PROTECTION	NEMA 4 IP66
LAMP TYPE	LED
OVERVOLTAGE CATEGORY	III
CURRENT CONSUMPTION	45 mA at 110/120 V AC
LIFESPAN, ELECTRICAL	100,000 h
LIGHT TYPE	Flashing light
LIGHT MODULES	LED
NUMBER OF MODULES	Max. 10 (with base for mounting on both sides) Max. 5 (with standard base)
SHOCK RESISTANCE	15 g, Mechanical, According to IEC/EN 60068-2-27, Sinusoidal shock 11 ms Mechanical, According to IEC/EN 60068-2-27
RATED OPERATIONAL VOLTAGE (UE) AT AC - MAX	120 V
RATED OPERATIONAL VOLTAGE (UE) AT AC - MIN	110 V
RATED OPERATIONAL	0 V

□□	
DECLARATIONS OF CONFORMITY	eaton-continuous-light-module-declaration-of-conformity-uk251039en.pdf
□□□□□	IL047004ZU
	eaton-operating-dimensions-005.eps
□□	eaton-operating-button-sl7-continuous-light-symbol-004.eps
	eaton-operating-sl7-flashing-light-symbol.eps

VOLTAGE (UE) AT DC - MAX	
RATED OPERATIONAL VOLTAGE (UE) AT DC - MIN	0 V
AMBIENT OPERATING TEMPERATURE - MAX	60 °C
AMBIENT OPERATING TEMPERATURE - MIN	-30 °C
LEAKAGE CURRENT	0.003 A
OUTSIDE DIAMETER	73 mm
RADIATION ANGLE	360 °
RATED INSULATION VOLTAGE (UI)	250 V
