

Eaton 177370

Eaton DE1 Variable speed starter, Rated operational voltage 400 V AC, 3-phase, Ie 8.5 A, 4 kW, 5 HP

PRODUCT NAME	Eaton DE1 Variable speed starter
CATALOG NUMBER	177370
PRODUCT LENGTH/DEPTH	169 mm
PRODUCT HEIGHT	230 mm
PRODUCT WIDTH	90 mm
PRODUCT WEIGHT	1.6 kg
CERTIFICATIONS	RCM CE IEC/EN 61800-3 CSA-C22.2 No. 14 IEC/EN61800-3 CUL RoHS, ISO 9001 UL File No.: E172143 UL UL report applies to both US and Canada Certified by UL for use in Canada IEC/EN61800-5 UL Category Control No.: NMMS, NMMS7 UL 508C Specification for general requirements: IEC/EN 61800-2 Safety requirements: IEC/EN 61800-5-1
CATALOG NOTES	Overload cycle for 60 s every 600 s

AMPERAGE RATING	8.50A output
HORSEPOWER	5 hp
PHASE	Three-phase main, three-phase motor
SPECIAL FEATURES	Basic Device
TYPE	PowerXL
FEATURES	Parameterization: drivesConnect Parameterization: drivesConnect mobile (App) Parameterization: Fieldbus Parameterization: Keypad
10.10 TEMPERATURE RISE	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 SHORT-CIRCUIT RATING	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 ELECTROMAGNETIC COMPATIBILITY	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 MECHANICAL FUNCTION	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.

DECLARATIONS OF CONFORMITY	DA-DC-00004556.pdf DA-DC-00004551.pdf IL040005ZU eaton-powerxl-de1-variable-speed-starter-brochure-br040003en-en-us.pdf eaton-powerxl-variable-frequency-drives-hvac-brochure-br040012en-en-us.pdf
	eaton-de1-variable-speed-starter-manual-mn040011-hu-hu.pdf eaton-de1-variable-speed-starter-manual-mn040011-zh-cn.pdf
	eaton-frequency-inverter-dimensions-010.eps eaton-frequency-inverter-3d-drawing-018.eps
	The OP System Bus - Parameterizing - Control DX-COM-STICK3 Connection How does the internal motor protection work?

10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	Meets the product standard's requirements.
10.2.5 LIFTING	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 MECHANICAL IMPACT	Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 INSCRIPTIONS	Meets the product standard's requirements.
10.3 DEGREE OF PROTECTION OF ASSEMBLIES	Does not apply, since the entire switchgear needs to be evaluated.
10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
FITTED WITH:	PC connection
CLIMATIC PROOFING	< 95 average relative humidity (RH), no condensation, no corrosion
CONNECTION TO SMARTWIRE-DT	In conjunction with DX-NET-SWD3 SmartWire DT module Yes
OPERATING MODE	Speed control with slip compensation U/f control
RATED IMPULSE WITHSTAND VOLTAGE (UIMP)	2000 V

FRAME SIZE	FS2
ALTITUDE	Max. 2000 m Above 1000 m with 1 % derating per 100 m
APPLICATION IN DOMESTIC AND COMMERCIAL AREA PERMITTED	Yes
MAINS SWITCH-ON FREQUENCY	Maximum of one time every 30 seconds
AMBIENT OPERATING TEMPERATURE - MAX	60 °C
AMBIENT OPERATING TEMPERATURE - MIN	-10 °C
MAINS VOLTAGE - MAX	480 V
OUTPUT VOLTAGE - MAX	500 V
RELATIVE SYMMETRIC NET FREQUENCY TOLERANCE	10 %
RELATIVE SYMMETRIC NET VOLTAGE TOLERANCE	10 %
SERIES	Economy
AMBIENT OPERATING TEMPERATURE AT 150% OVERLOAD - MAX	60 °C
AMBIENT OPERATING TEMPERATURE AT 150% OVERLOAD - MIN	-10 °C
AMBIENT STORAGE TEMPERATURE - MAX	70 °C
AMBIENT STORAGE TEMPERATURE - MIN	-40 °C
APPARENT POWER AT 400 V	5.89 kVA
APPARENT POWER AT 480 V	7.07 kVA
APPLICATION IN INDUSTRIAL AREA PERMITTED	Yes
HEAT DISSIPATION DETAILS	Operation (with 150 % overload)
PRODUCT CATEGORY	Variable speed starter
PROTECTION	Finger and back-of-hand proof, Protection against direct contact (BGV A3, VBG4)
RESOLUTION	0.025 Hz (Frequency

	resolution, setpoint value)
STATIC HEAT DISSIPATION, NON-CURRENT-DEPENDENT PVS	0 W
VOLTAGE RATING - MAX	480 V
MOUNTING POSITION	Vertical
OVERVOLTAGE CATEGORY	III
COMMUNICATION INTERFACE	OP-Bus (RS485), built in Modbus RTU, built in
CONVERTER TYPE	U converter
DEGREE OF PROTECTION	IP20 NEMA Other
ASSIGNED MOTOR POWER AT 460/480 V, 60 HZ, 3-PHASE	5 HP
EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT PVID	120 W
HEAT DISSIPATION CAPACITY PDISS	0 W
HEAT DISSIPATION PER POLE, CURRENT-DEPENDENT PVID	0 W
INPUT CURRENT ILN AT 150% OVERLOAD	10 A
MAINS CURRENT DISTORTION	120 %
PROTOCOL	MODBUS Other bus systems EtherNet/IP
OVERLOAD CURRENT IL AT 150% OVERLOAD	12.75 A
RATED FREQUENCY - MAX	66 Hz
RATED FREQUENCY - MIN	45 Hz
RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)	8.5 A
RATED OPERATIONAL POWER AT 380/400 V, 50 HZ, 3-PHASE	4 kW
ASSIGNED MOTOR CURRENT IM AT 400 V, 50 HZ, 150% OVERLOAD	8.5 A
ASSIGNED MOTOR CURRENT IM AT 440 - 480	7.6 A

V, 60 HZ, 150% OVERLOAD	
BRAKING CURRENT	≤ 0.6 A (max. 6 A for 120 ms), Actuator for external motor brake
ELECTROMAGNETIC COMPATIBILITY	1st and 2nd environments (according to EN 61800-3)
BRAKING TORQUE	Adjustable to 100 %, DC - Main circuit Max. 30 % MN, Standard - Main circuit
CABLE LENGTH	C3 ≤ 25 m, Radio interference level, maximum motor cable length C2 ≤ 10 m, Radio interference level, maximum motor cable length
OUTPUT VOLTAGE (U2)	480 V AC, 3-phase 400 V AC, 3-phase
DELAY TIME	< 10 ms, On-delay < 10 ms, Off-delay
NUMBER OF INPUTS (ANALOG)	1 (parameterizable, 0 - 10 V DC, 0/4 - 20 mA)
NUMBER OF INPUTS (DIGITAL)	4 (parameterizable, 10 - 30 V DC)
RADIO INTERFERENCE CLASS	C2, C3: depending on the motor cable length, the connected load, and ambient conditions. External radio interference suppression filters (optional) may be necessary. Optional external radio interference suppression filter for longer motor cable lengths and for use in different EMC environments
NUMBER OF OUTPUTS (DIGITAL)	0
STARTING CURRENT - MAX	200 %, IH, max. starting current (High Overload), For 1.875 seconds every 600 seconds, Power section
NUMBER OF PHASES (INPUT)	3
NUMBER OF RELAY	1 (parameterizable, N/O, 6

OUTPUTS	A (250 V, AC-1) / 5 A (30 V, DC-1))
NUMBER OF PHASES (OUTPUT)	3
POWER CONSUMPTION	120 W
RATED CONTROL SUPPLY VOLTAGE	10 V DC (Us, max. 0.2 mA)
SUPPLY FREQUENCY	50/60 Hz
LEAKAGE CURRENT AT GROUND IPE - MAX	< 3.5 mA (AC-operated) < 10 mA (DC-operated)
MAINS VOLTAGE - MIN	380 V
NOMINAL OUTPUT CURRENT I2N	8.5 A
NUMBER OF HW-INTERFACES (INDUSTRIAL ETHERNET)	0
NUMBER OF HW-INTERFACES (OTHER)	0
NUMBER OF HW-INTERFACES (PARALLEL)	0
NUMBER OF HW-INTERFACES (RS-232)	0
NUMBER OF HW-INTERFACES (RS-422)	0
NUMBER OF HW-INTERFACES (RS-485)	1
NUMBER OF HW-INTERFACES (SERIAL TTY)	0
NUMBER OF HW-INTERFACES (USB)	0
NUMBER OF INTERFACES (PROFINET)	0
NUMBER OF OUTPUTS (ANALOG)	0
OUTPUT AT LINEAR LOAD AT RATED OUTPUT VOLTAGE - MAX	4 kW
OUTPUT AT QUADRATIC LOAD AT RATED OUTPUT VOLTAGE - MAX	4 kW
OUTPUT FREQUENCY - MAX	300 Hz
OUTPUT FREQUENCY - MIN	0 Hz
SHORT-CIRCUIT PROTECTION (EXTERNAL OUTPUT CIRCUITS)	Type 1 coordination via the power bus' feeder unit, Main circuit

SHOCK RESISTANCE	15 g, Mechanical, According to IEC/EN 60068-2-27, 11 ms
SUITABLE FOR	Branch circuits, (UL/CSA)
SWITCHING FREQUENCY	16 kHz, 4 - 32 kHz adjustable (audible), fPWM, Power section, Main circuit
RATED OPERATIONAL CURRENT (IE)	8.5 A at 150% overload (at an operating frequency of 16 kHz and an ambient air temperature of +50 °C)
RATED OPERATIONAL VOLTAGE	480 V AC, 3-phase 400 V AC, 3-phase
SHORT-CIRCUIT PROTECTION RATING	15 A, UL (Class CC or J), Safety device (fuse or miniature circuit-breaker), Power Wiring
VIBRATION	Resistance: According to EN 61800-5-1
HEAT DISSIPATION AT CURRENT/SPEED	101 W at 100% current and 90% speed 47 W at 25% current and 0% speed 51 W at 25% current and 50% speed 55 W at 50% current and 0% speed 60 W at 50% current and 50% speed 65 W at 50% current and 90% speed 76 W at 100% current and 0% speed 93 W at 100% current and 50% speed

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

