

Eaton 171415

Eaton Moeller® series SL7 Strobe light module, green, LED, 230 V

PRODUCT NAME	Eaton Moeller® series SL7 Strobe light module
CATALOG NUMBER	171415
PRODUCT LENGTH/DEPTH	73 mm
PRODUCT HEIGHT	73 mm
PRODUCT WIDTH	73 mm
PRODUCT WEIGHT	0.083 kg
COMPLIANCES	CE Marked
CERTIFICATIONS	UL 508 CSA Certified UL Listed cULus Listed UL Listed file E29184 CSA Std. C22.2 No. 94-91 CSA Std. C22.2 No. 14-10 CSA Class No. NKCR7 IEC Rated UL Category Control No.: NKCR IEC/EN 60947-5-1 CSA-C22.2 No. 14-10 UL report applies to both US and Canada CE Certified by UL for use in Canada CSA Class No.: NKCR7 UL UL File No.: E29184 CSA-C22.2 No. 94-91 IEC/EN 60529
CATALOG NOTES	0

TYPE	Strobe light module
ENVIRONMENTAL RATING	IP66
PRODUCT CATEGORY	SL signal towers
VOLTAGE RATING	230/240 V
FREQUENCY RATING	1.4 Hz
POLLUTION DEGREE	3
FLASHING FREQUENCY	1.4 Hz
CLIMATIC PROOFING	Damp heat, constant, to IEC 60068-2-78 Damp heat, cyclic, to IEC 60068-2-30
CONNECTION TO SMARTWIRE-DT	No
RATED IMPULSE WITHSTAND VOLTAGE (UIMP)	4000 V AC
ENCLOSURE COLOR	Black
FUNCTIONS	Flash light
ILLUMINATION	Strobe LED
COLOR	Green
VOLTAGE TYPE	AC
MATERIAL	Cap: Polycarbonate (PC) Enclosure: Polycarbonate (PC)
MOUNTING POSITION	As required
DEGREE OF PROTECTION	NEMA 4 IP66
LAMP TYPE	LED
OVERVOLTAGE CATEGORY	III
CURRENT CONSUMPTION	20 mA at 230/240 V AC
LIFESPAN, ELECTRICAL	100,000 h
LIGHT TYPE	Strobe light
LIGHT MODULES	LED
NUMBER OF MODULES	Max. 5 (with standard base) Max. 10 (with base for mounting on both sides)
SHOCK RESISTANCE	Mechanical, According to IEC/EN 60068-2-27 15 g, Mechanical, According to IEC/EN 60068-2-27, Sinusoidal

DECLARATIONS OF CONFORMITY	DA-DC-00004257.pdf
	DA-DC-00004253.pdf
	IL047004ZU
	Eaton Specification Sheet - SL7-FL230-G
	eaton-operating-dimensions-005.eps
	eaton-operating-button-sl7-continuous-light-symbol-002.eps
	eaton-operating-sl7-strobe-light-module-symbol.eps

	shock 11 ms
RATED OPERATIONAL VOLTAGE (UE) AT AC - MAX	240 V
RATED OPERATIONAL VOLTAGE (UE) AT AC - MIN	230 V
RATED OPERATIONAL VOLTAGE (UE) AT DC - MAX	0 V
RATED OPERATIONAL VOLTAGE (UE) AT DC - MIN	0 V
AMBIENT OPERATING TEMPERATURE - MAX	60 °C
AMBIENT OPERATING TEMPERATURE - MIN	-30 °C
LEAKAGE CURRENT	0.003 A
OUTSIDE DIAMETER	73 mm
QUANTITY	1
RADIATION ANGLE	360 °
RATED INSULATION VOLTAGE (UI)	250 V
ENCLOSURE	UL type 4, 4X, 13
SERIES	SL7

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

