



□□□□

Eaton 171417

Eaton Moeller® series SL7 Strobe light module, white, LED, 230 V

□□□□

PRODUCT NAME	Eaton Moeller® series SL7 Strobe light module
CATALOG NUMBER	171417
PRODUCT LENGTH/DEPTH	73 mm
PRODUCT HEIGHT	73 mm
PRODUCT WIDTH	73 mm
PRODUCT WEIGHT	0.083 kg
CERTIFICATIONS	UL report applies to both US and Canada UL Category Control No.: NKCR Certified by UL for use in Canada IEC/EN 60947-5-1 CSA-C22.2 No. 14-10 IEC/EN 60529 UL 508 UL CSA-C22.2 No. 94-91 CE UL File No.: E29184 CSA Class No.: NKCR7

□□□□	
TYPE	Strobe light module
PRODUCT CATEGORY	SL signal towers
POLLUTION DEGREE	3
FLASHING FREQUENCY	1.4 Hz
CLIMATIC PROOFING	Damp heat, cyclic, to IEC 60068-2-30 Damp heat, constant, to IEC 60068-2-78
CONNECTION TO SMARTWIRE-DT	No
RATED IMPULSE WITHSTAND VOLTAGE (UIMP)	4000 V AC
ENCLOSURE COLOR	Black
FUNCTIONS	Flash light
COLOR	Other
VOLTAGE TYPE	AC
MATERIAL	Cap: Polycarbonate (PC) Enclosure: Polycarbonate (PC)
MOUNTING POSITION	As required
DEGREE OF PROTECTION	IP66 NEMA 4
LAMP TYPE	LED
OVERVOLTAGE CATEGORY	III
CURRENT CONSUMPTION	20 mA at 230/240 V AC
LIFESPAN, ELECTRICAL	100,000 h
LIGHT TYPE	Strobe light
LIGHT MODULES	LED
NUMBER OF MODULES	Max. 5 (with standard base) Max. 10 (with base for mounting on both sides)
SHOCK RESISTANCE	15 g, Mechanical, According to IEC/EN 60068-2-27, Sinusoidal shock 11 ms Mechanical, According to IEC/EN 60068-2-27
RATED OPERATIONAL VOLTAGE (UE) AT AC - MAX	240 V
RATED OPERATIONAL VOLTAGE (UE) AT AC - MIN	230 V
RATED OPERATIONAL	0 V

□□	
DECLARATIONS OF CONFORMITY	eaton-continuous-light-module-declaration-of-conformity-uk251039en.pdf
□□□□□	IL047004ZU
	eaton-operating-dimensions-005.eps
□□	eaton-operating-sl7-strobe-light-module-symbol.eps
	eaton-operating-button-sl7-continuous-light-symbol-003.eps

VOLTAGE (UE) AT DC - MAX	
RATED OPERATIONAL VOLTAGE (UE) AT DC - MIN	0 V
AMBIENT OPERATING TEMPERATURE - MAX	60 °C
AMBIENT OPERATING TEMPERATURE - MIN	-30 °C
LEAKAGE CURRENT	0.003 A
OUTSIDE DIAMETER	73 mm
RADIATION ANGLE	360 °
RATED INSULATION VOLTAGE (UI)	250 V
