



□□□□□

Eaton 171470

Eaton Moeller® series SL7 Continuous light module, white, LED, 120 V

□□□□

PRODUCT NAME	Eaton Moeller® series SL7 Continuous light module
CATALOG NUMBER	171470
PRODUCT LENGTH/DEPTH	73 mm
PRODUCT HEIGHT	73 mm
PRODUCT WIDTH	73 mm
PRODUCT WEIGHT	0.082 kg
CERTIFICATIONS	CSA Class No.: NKCR7 CSA-C22.2 No. 94-91 UL report applies to both US and Canada IEC/EN 60529 UL UL 508 Certified by UL for use in Canada CSA-C22.2 No. 14-10 CE UL File No.: E29184 UL Category Control No.: NKCR IEC/EN 60947-5-1

□□□□

TYPE	Continuous light module
PRODUCT CATEGORY	SL signal towers
POLLUTION DEGREE	3
CLIMATIC PROOFING	Damp heat, cyclic, to IEC 60068-2-30 Damp heat, constant, to IEC 60068-2-78
CONNECTION TO SMARTWIRE-DT	No
RATED IMPULSE WITHSTAND VOLTAGE (UIMP)	4000 V AC
ENCLOSURE COLOR	Black
FUNCTIONS	Continuous light
COLOR	Other
VOLTAGE TYPE	AC
MATERIAL	Cap: Polycarbonate (PC) Enclosure: Polycarbonate (PC)
MOUNTING POSITION	As required
DEGREE OF PROTECTION	NEMA 4X IP66
LAMP TYPE	LED
OVERVOLTAGE CATEGORY	III
CURRENT CONSUMPTION	45 mA at 110/120 V AC
LIFESPAN, ELECTRICAL	100,000 h
LIGHT TYPE	Continuous light
LIGHT MODULES	LED
NUMBER OF MODULES	Max. 5 (with standard base) Max. 10 (with base for mounting on both sides)
SHOCK RESISTANCE	15 g, Mechanical, According to IEC/EN 60068-2-27, Sinusoidal shock 11 ms Mechanical, According to IEC/EN 60068-2-27
RATED OPERATIONAL VOLTAGE (UE) AT AC - MAX	120 V
RATED OPERATIONAL VOLTAGE (UE) AT AC - MIN	110 V
RATED OPERATIONAL VOLTAGE (UE) AT DC -	0 V

□□

DECLARATIONS OF CONFORMITY	eaton-continuous-light-module-declaration-of-conformity-uk251039en.pdf
□□□□□	IL047004ZU
	eaton-operating-dimensions-005.eps
□□	eaton-operating-button-sl7-continuous-light-symbol-003.eps eaton-operating-sl7-continuous-light-symbol-002.eps

MAX	
RATED OPERATIONAL VOLTAGE (UE) AT DC - MIN	0 V
AMBIENT OPERATING TEMPERATURE - MAX	60 °C
AMBIENT OPERATING TEMPERATURE - MIN	-30 °C
LEAKAGE CURRENT	0.003 A
OUTSIDE DIAMETER	73 mm
RADIATION ANGLE	360 °
RATED INSULATION VOLTAGE (UI)	250 V
