

Eaton 182938

Eaton Moeller® series M30 Pushbutton,
RMQ-Titan, Flat, maintained, White,
inscribed, Metal bezel

PRODUCT NAME	Eaton Moeller® series M30 Pushbutton
CATALOG NUMBER	182938
PRODUCT LENGTH/DEPTH	36 mm
PRODUCT HEIGHT	30 mm
PRODUCT WIDTH	46 mm
PRODUCT WEIGHT	0.041 kg
CERTIFICATIONS	VDE 0660
	IEC/EN 60947
	CSA File No.: 012528
	CSA Class No.: 3211-03
	DNV
	UL File No.: E29184
	GL
	IEC/EN 60947-5
	UL 508
	CSA-C22.2 No. 14-05 and 94-M91
	CE marking
	UL Category Control No.: NKCR
	UL Listed
	CSA certified

TYPE	Pushbutton actuator
ACTUATOR COLOR	White
FEATURES	Labelled
ACTUATOR FUNCTION	Maintained Switching function latching
FITTED WITH:	Front ring
OPERATING FREQUENCY	1800 Operations/h
CLIMATIC PROOFING	Damp heat, constant, to IEC 60068-2-78 Damp heat, cyclic, to IEC 60068-2-30
CONNECTION TO SMARTWIRE-DT	With SWD-RMQ connections Yes
ACTUATING FORCE	5 N
AMBIENT OPERATING TEMPERATURE - MAX	70 °C
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
AMBIENT STORAGE TEMPERATURE - MAX	80 °C
AMBIENT STORAGE TEMPERATURE - MIN	40 °C
FORCE FOR POSITIVE OPENING - MIN	0 N
NUMBER OF COMMAND POSITIONS	1
OPENING DIAMETER	30.5 mm
OPENING HEIGHT	0 mm
BEZEL COLOR	Titanium
SHOCK RESISTANCE	15 g, Mechanical, According to IEC/EN 60068-2-27, Sinusoidal shock 11 ms Mechanical, According to IEC/EN 60068-2-27
BEZEL MATERIAL	Metal
DESIGN	Flat Flat front
MOUNTING POSITION	As required
DEGREE OF PROTECTION	IP67 IP69K IP66
DEGREE OF PROTECTION (FRONT SIDE)	IP67/IP69K NEMA 4X, 13

DECLARATIONS OF CONFORMITY	eaton-key-operated-actuator-declaration-of-conformity-uk251346en.pdf eaton-key-operated-actuator-declaration-of-conformity-uk251347en.pdf
	eaton-operating-devices-m30-rmq-titan-flat-front-instruction-leaflet-il047019zu.pdf eaton-operating-m30-dimensions-005.eps eaton-operating-m30-dimensions-004.eps eaton-operating-m30-dimensions.eps eaton-operating-m30-dimensions-006.eps eaton-operating-m30-3d-drawing.eps
/	RMQ small E-Stop emergency-stop button

INSCRIPTION	Inscribed
FRONT ELEMENT TYPE	Flat
FUNCTIONS	Stay-put/spring-return function can be changed on device
LENS TYPE	Round
LIFESPAN, MECHANICAL	1,000,000 Operations (AC operated)
WIDTH OPENING	0 mm
PRODUCT CATEGORY	RMQ-Titan
SIZE	Front dimensions: Ø 36 x 3 mm

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
: