

Eaton 183034

Eaton xEffect - XNH circuit protection. NH fuse-switch 3p box terminal 1,5 - 95 mm², busbar 60 mm, NH000 & NH00

PRODUCT NAME	Eaton xEffect XNH device for busbar system
CATALOG NUMBER	183034
PRODUCT LENGTH/DEPTH	204 mm
PRODUCT HEIGHT	137 mm
PRODUCT WIDTH	106 mm
PRODUCT WEIGHT	0.811 kg
COMPLIANCES	RoHS conform
CERTIFICATIONS	IEC/EN 60947-3

FEATURES	Halogen free Standard sealable
10.10 TEMPERATURE RISE	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 SHORT-CIRCUIT RATING	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 ELECTROMAGNETIC COMPATIBILITY	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 MECHANICAL FUNCTION	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.
10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	Meets the product standard's requirements.
10.2.5 LIFTING	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 MECHANICAL IMPACT	Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 INSCRIPTIONS	Meets the product standard's requirements.
10.3 DEGREE OF	Does not apply, since the

<u>eaton-xeffect-xnh-fuse-switch-disconnector-installation-leaflet-il0131111z.pdf</u>
<u>eaton-xeffect-xnh-fuse-switch-disconnector-brochure-br019002en-en-us.pdf</u>
<u>eaton-circuit-breaker-xeffect-xeffect-xnh-circuit-protection-dimensions-009.eps</u>

PROTECTION OF ASSEMBLIES	entire switchgear needs to be evaluated.
10.4 CLEARANCES AND CREEPAGE DISTANCES	Is the panel builder's responsibility.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Ui = 800 V AC
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
FREQUENCY RATING	40 Hz - 60 Hz
POLLUTION DEGREE	3
CREEPAGE RESISTANCE	CTI 600
EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT	14 W
RATED UNINTERRUPTED CURRENT (IU)	160 A
TOTAL HEAT DISSIPATION WITHOUT FUSES AT ITH	14 W
AMBIENT OPERATING TEMPERATURE DETAILS	Ambient temperature range: -25 °C - 70 °C
VOLTAGE RATING AT AC	<ul style="list-style-type: none"> • 400 V (AC-23B) • 500 V (AC-22B) • 690 V (AC-21B)
VOLTAGE RATING AT DC	<ul style="list-style-type: none"> • 250 V DC at DC-22B • 440 V DC at DC-21B
CONDITIONED RATED SHORT-CIRCUIT CURRENT IQ	120 kA
NUMBER OF POLES	Three-pole
RATED OPERATION	0 kW

POWER AT AC-23, 400 V	
SIZE	NH000 / NH00 fuse
RATED IMPULSE WITHSTAND VOLTAGE (UIMP)	8 kV
COLOR	Gray
CONNECTION TYPE	Box terminal
DEGREE OF PROTECTION	IP2XC (contact protection, XNH installed) IP10 (handle cover open, XNH installed) IP20 (operating status, XNH installed)
RATED SHORT-TIME WITHSTAND CURRENT (ICW)	7 kA
DIRECTION OF INCOMING SUPPLY	As required (FLEX System)
ELECTRICAL CONNECTION TYPE OF MAIN CIRCUIT	Frame clamp
ACTIVATION TYPE	Dependent manual activation
ACTUATOR POSITION	Front side
ACTUATOR TYPE	Cover grip
VOLTAGE TEST	Yes, sliding inspection windows
HEAT DISSIPATION AT 80% WITHOUT FUSES	9 W
HEAT DISSIPATION PER POLE, CURRENT-DEPENDENT	4.7 W
MOUNTING POSITION	Vertical or horizontal
SUITABLE FOR	Busbar mounting Front mounting
RATED CONDITIONAL SHORT-CIRCUIT CURRENT (IQ)	120 kA
OVERVOLTAGE CATEGORY	III
SUITABLE FOR FUSES	NH00
MATERIAL	Polyamide
CABLE ENTRY TYPE	Other
FREQUENCY RATING OF CONTACTS	40 Hz - 60 Hz
MOUNTING METHOD	Busbars of 60 mm
RATED OPERATION	160 A

CURRENT (IE)	
LOCKING FACILITY	Yes, optional
FLAMMABILITY CHARACTERISTICS (UL)	Self-extinguishing (UL 94)
TYPE	Basic device
SPECIAL FEATURES	<ul style="list-style-type: none"> • Permanent operation (rated operating mode) • Current paths of electrolytic copper, silver-plated • Cable connection optionally at the top or bottom
DEGREE OF PROTECTION (FRONT SIDE)	Other
HEAT DEFLECTION TEMPERATURE	125 °C
LIFESPAN, ELECTRICAL	300 operations
LIFESPAN, MECHANICAL	1400 operations
TERMINAL CAPACITY (COPPER BUSBAR)	Bolt diameter at flange connection: M8 Max. 25 mm cable lug width at flange connection 20 mm x 10 mm
TERMINAL CAPACITY (COPPER BAND)	9 mm x 0.8 mm (6x) at box terminal
TERMINAL CAPACITY (STRANDED CABLE)	1.5 mm ² - 50 mm ² at box terminal 1.5 mm ² - 95 mm ² at box terminal 10 mm ² - 70 mm ² at clamp-type terminal
RATED OPERATIONAL CURRENT	160 A (AC-22B) 160 A 160 A (AC-23B) 160 A (AC-21B)
OPERATING ALTITUDE WITHOUT DERATING - MAX	2000 mm
PERMITTED POWER LOSS PER FUSE LINK - MAX	12 W
POWER RATING AT AC-23, 400 V	0 kW
RATED INSULATION VOLTAGE (UI)	800 VAC
RATED OPERATING	690 V

**VOLTAGE (UE) AT AC -
MAX**

RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)	160 A
------------------------------------------------------------------------------	-------

RATED CONDITIONAL SHORT-CIRCUIT RATING	100 kA (690 V) 120 kA (500 V)
---------------------------------------------------	----------------------------------

TERMINAL CAPACITY (COPPER STRIP)	9 mm x 0.8 mm (9x) at box terminal
---------------------------------------------	---------------------------------------

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the
latest product and support
information.

