

Eaton 177366

Eaton DE1 Variable speed starter, Rated operational voltage 400 V AC, 3-phase, Ie 2.1 A, 0.75 kW, 1 HP

PRODUCT NAME	Eaton DE1 Variable speed starter
CATALOG NUMBER	177366
PRODUCT LENGTH/DEPTH	169 mm
PRODUCT HEIGHT	230 mm
PRODUCT WIDTH	45 mm
PRODUCT WEIGHT	1 kg
CERTIFICATIONS	Certified by UL for use in Canada UL File No.: E172143 Specification for general requirements: IEC/EN 61800-2 RoHS, ISO 9001 UL Category Control No.: NMMS, NMMS7 UL RCM Safety requirements: IEC/EN 61800-5-1 CSA-C22.2 No. 14 CUL UL 508C IEC/EN61800-3 CE UL report applies to both US and Canada IEC/EN 61800-3 IEC/EN61800-5
CATALOG NOTES	Overload cycle for 60 s every 600 s

FEATURES	Parameterization: drivesConnect Parameterization: drivesConnect mobile (App) Parameterization: Fieldbus
	Parameterization: Keypad
10.10 TEMPERATURE RISE	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 SHORT-CIRCUIT RATING	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 ELECTROMAGNETIC COMPATIBILITY	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 MECHANICAL FUNCTION	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.
10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	Meets the product standard's requirements.
10.2.5 LIFTING	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 MECHANICAL	Does not apply, since the

DECLARATIONS OF CONFORMITY	DA-DC-00004551.pdf
	DA-DC-00004556.pdf
	IL040005ZU
	eaton-powerxl-de1-variable-speed-starter-brochure-br040003en-en-us.pdf
	eaton-powerxl-variable-frequency-drives-hvac-brochure-br040012en-en-us.pdf
	eaton-de1-variable-speed-starter-manual-mn040011-zh-cn.pdf
	eaton-de1-variable-speed-starter-manual-mn040011-hu-hu.pdf
	eaton-frequency-inverter-dimensions-009.eps
	eaton-frequency-inverter-3d-drawing-017.eps
	How does the internal motor protection work?
	DX-COM-STICK3 Connection
	The OP System Bus - Parameterizing - Control

IMPACT	entire switchgear needs to be evaluated.
10.2.7 INSCRIPTIONS	Meets the product standard's requirements.
10.3 DEGREE OF PROTECTION OF ASSEMBLIES	Does not apply, since the entire switchgear needs to be evaluated.
10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
FITTED WITH:	PC connection
CLIMATIC PROOFING	< 95 average relative humidity (RH), no condensation, no corrosion
CONNECTION TO SMARTWIRE-DT	Yes In conjunction with DX-NET-SWD3 SmartWire DT module
OPERATING MODE	Speed control with slip compensation U/f control
RATED IMPULSE WITHSTAND VOLTAGE (UIMP)	2000 V
FRAME SIZE	FS1
ALTITUDE	Above 1000 m with 1 % derating per 100 m Max. 2000 m
APPLICATION IN DOMESTIC AND	Yes

COMMERCIAL AREA PERMITTED	
MAINS SWITCH-ON FREQUENCY	Maximum of one time every 30 seconds
AMBIENT OPERATING TEMPERATURE - MAX	60 °C
AMBIENT OPERATING TEMPERATURE - MIN	-10 °C
MAINS VOLTAGE - MAX	480 V
OUTPUT VOLTAGE - MAX	500 V
RELATIVE SYMMETRIC NET FREQUENCY TOLERANCE	10 %
RELATIVE SYMMETRIC NET VOLTAGE TOLERANCE	10 %
AMBIENT OPERATING TEMPERATURE AT 150% OVERLOAD - MAX	50 °C
AMBIENT OPERATING TEMPERATURE AT 150% OVERLOAD - MIN	-10 °C
AMBIENT STORAGE TEMPERATURE - MAX	70 °C
AMBIENT STORAGE TEMPERATURE - MIN	-40 °C
APPARENT POWER AT 400 V	1.45 kVA
APPARENT POWER AT 480 V	1.75 kVA
APPLICATION IN INDUSTRIAL AREA PERMITTED	Yes

AMBIENT OPERATING TEMPERATURE DETAILS	<ul style="list-style-type: none"> • Derating between 50 °C and 60 °C: • None if fPWM ≤ 16 kHz • None if fPWM ≤ 20 kHz up to a max. of 57 °C • None if I_e ≤ 1.6 A
HEAT DISSIPATION DETAILS	Operation (with 150 % overload)
PRODUCT CATEGORY	Variable speed starter
PROTECTION	Finger and back-of-hand proof, Protection against direct contact (BGV A3, VBG4)

RESOLUTION	0.025 Hz (Frequency resolution, setpoint value)
STATIC HEAT DISSIPATION, NON-CURRENT-DEPENDENT PVS	0 W
VOLTAGE RATING - MAX	480 V
MOUNTING POSITION	Vertical
OVERVOLTAGE CATEGORY	III
COMMUNICATION INTERFACE	OP-Bus (RS485), built in Modbus RTU, built in
CONVERTER TYPE	U converter
DEGREE OF PROTECTION	IP20 NEMA Other
ASSIGNED MOTOR POWER AT 460/480 V, 60 HZ, 3-PHASE	1 HP
EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT PVID	28 W
HEAT DISSIPATION CAPACITY PDISS	0 W
HEAT DISSIPATION PER POLE, CURRENT-DEPENDENT PVID	0 W
INPUT CURRENT ILN AT 150% OVERLOAD	3.1 A
MAINS CURRENT DISTORTION	120 %
PROTOCOL	MODBUS EtherNet/IP Other bus systems
OVERLOAD CURRENT IL AT 150% OVERLOAD	3.15 A
RATED FREQUENCY - MAX	66 Hz
RATED FREQUENCY - MIN	45 Hz
RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)	2.1 A
RATED OPERATIONAL POWER AT 380/400 V, 50 HZ, 3-PHASE	0.75 kW
ASSIGNED MOTOR CURRENT IM AT 400 V, 50 HZ, 150% OVERLOAD	1.9 A
ASSIGNED MOTOR	2.1 A

CURRENT IM AT 440 - 480 V, 60 HZ, 150% OVERLOAD	
BRAKING CURRENT	≤ 0.6 A (max. 6 A for 120 ms), Actuator for external motor brake
ELECTROMAGNETIC COMPATIBILITY	1st and 2nd environments (according to EN 61800-3)
BRAKING TORQUE	Adjustable to 100 %, DC - Main circuit Max. 30 % MN, Standard - Main circuit
CABLE LENGTH	C3 ≤ 25 m, Radio interference level, maximum motor cable length C2 ≤ 10 m, Radio interference level, maximum motor cable length
OUTPUT VOLTAGE (U2)	400 V AC, 3-phase 480 V AC, 3-phase
DELAY TIME	< 10 ms, On-delay < 10 ms, Off-delay
NUMBER OF INPUTS (ANALOG)	1 (parameterizable, 0 - 10 V DC, 0/4 - 20 mA)
NUMBER OF INPUTS (DIGITAL)	4 (parameterizable, 10 - 30 V DC)
RADIO INTERFERENCE CLASS	C2, C3: depending on the motor cable length, the connected load, and ambient conditions. External radio interference suppression filters (optional) may be necessary. Optional external radio interference suppression filter for longer motor cable lengths and for use in different EMC environments
NUMBER OF OUTPUTS (DIGITAL)	0
STARTING CURRENT - MAX	200 %, IH, max. starting current (High Overload), For 1.875 seconds every 600 seconds, Power section
NUMBER OF PHASES (INPUT)	3

NUMBER OF RELAY OUTPUTS	1 (parameterizable, N/O, 6 A (250 V, AC-1) / 5 A (30 V, DC-1))
NUMBER OF PHASES (OUTPUT)	3
POWER CONSUMPTION	28 W
RATED CONTROL SUPPLY VOLTAGE	10 V DC (Us, max. 0.2 mA)
SUPPLY FREQUENCY	50/60 Hz
LEAKAGE CURRENT AT GROUND IPE - MAX	< 10 mA (DC-operated) < 3.5 mA (AC-operated)
MAINS VOLTAGE - MIN	380 V
NOMINAL OUTPUT CURRENT I2N	2.1 A
NUMBER OF HW-INTERFACES (INDUSTRIAL ETHERNET)	0
NUMBER OF HW-INTERFACES (OTHER)	0
NUMBER OF HW-INTERFACES (PARALLEL)	0
NUMBER OF HW-INTERFACES (RS-232)	0
NUMBER OF HW-INTERFACES (RS-422)	0
NUMBER OF HW-INTERFACES (RS-485)	1
NUMBER OF HW-INTERFACES (SERIAL TTY)	0
NUMBER OF HW-INTERFACES (USB)	0
NUMBER OF INTERFACES (PROFINET)	0
NUMBER OF OUTPUTS (ANALOG)	0
OUTPUT AT LINEAR LOAD AT RATED OUTPUT VOLTAGE - MAX	0.75 kW
OUTPUT AT QUADRATIC LOAD AT RATED OUTPUT VOLTAGE - MAX	0.75 kW
OUTPUT FREQUENCY - MAX	300 Hz
OUTPUT FREQUENCY - MIN	0 Hz
SHORT-CIRCUIT PROTECTION (EXTERNAL OUTPUT CIRCUITS)	Type 1 coordination via the power bus' feeder unit, Main circuit

SHOCK RESISTANCE	15 g, Mechanical, According to IEC/EN 60068-2-27, 11 ms
SUITABLE FOR	Branch circuits, (UL/CSA)
SWITCHING FREQUENCY	16 kHz, 4 - 32 kHz adjustable (audible), fPWM, Power section, Main circuit
RATED OPERATIONAL CURRENT (IE)	2.1 A at 150% overload (at an operating frequency of 16 kHz and an ambient air temperature of +50 °C)
RATED OPERATIONAL VOLTAGE	480 V AC, 3-phase 400 V AC, 3-phase
SHORT-CIRCUIT PROTECTION RATING	6 A, UL (Class CC or J), Safety device (fuse or miniature circuit-breaker), Power Wiring
VIBRATION	Resistance: According to EN 61800-5-1
HEAT DISSIPATION AT CURRENT/SPEED	11.8 W at 50% current and 0% speed 14.3 W at 25% current and 0% speed 14.3 W at 25% current and 50% speed 16.7 W at 50% current and 90% speed 17.2 W at 50% current and 50% speed 25.4 W at 100% current and 0% speed 26.8 W at 100% current and 90% speed 27.9 W at 100% current and 50% speed

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

