



Eaton 183607

Eaton Moeller series IZMX/INX - ACB. Circuit-breaker, 3p, 2000A, 105 kA, P measurement, IEC, Withdrawable

□□□□

PRODUCT NAME	Eaton Moeller series IZMX/INX circuit-breaker
CATALOG NUMBER	183607
PRODUCT LENGTH/DEPTH	584 mm
PRODUCT HEIGHT	597 mm
PRODUCT WIDTH	521 mm
PRODUCT WEIGHT	69 kg
COMPLIANCES	IEC/EN 60947 IEC RoHS conform



Powering Business Worldwide

USED WITH	Open circuit breaker Air circuit breakers/switch-disconnector
AMPERAGE RATING	2000 A
FEATURES	Motor drive optional Complete device with protection unit
10.10 TEMPERATURE RISE	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 SHORT-CIRCUIT RATING	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 ELECTROMAGNETIC COMPATIBILITY	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 MECHANICAL FUNCTION	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.
10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	Meets the product standard's requirements.
10.2.5 LIFTING	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 MECHANICAL IMPACT	Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 INSCRIPTIONS	Meets the product

[eaton-circuit-breaker-izmx-inx-mccb-dimensions-014.eps](#)

[eaton-circuit-breaker-mounting-izmx-inx-mccb-dimensions.eps](#)

[eaton-circuit-breaker-mounting-izmx-inx-mccb-dimensions-002.eps](#)

[eaton-circuit-breaker-izmx-inx-mccb-dimensions-015.eps](#)

	standard's requirements.
10.3 DEGREE OF PROTECTION OF ASSEMBLIES	Does not apply, since the entire switchgear needs to be evaluated.
10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
FITTED WITH:	Switched-off indicator
FRAME	IZMX40
POLLUTION DEGREE	3
RATED UNINTERRUPTED CURRENT (IU)	2000 A
MOUNTING METHOD	Withdrawable
EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT	220 W
RATED IMPULSE WITHSTAND VOLTAGE (UIMP)	12 kV AC
UTILIZATION CATEGORY	B
DEVICE CONSTRUCTION	Built-in device slide-in technique (withdrawable)
DIRECTION OF INCOMING SUPPLY	As required
ELECTRICAL CONNECTION TYPE OF MAIN CIRCUIT	Rail connection
ACTUATOR TYPE	Push button
SHORT-CIRCUIT RELEASE NON-DELAYED SETTING	1.5 - 10 x I _r
ADJUSTMENT RANGE SHORT-TERM DELAYED	20000 A

SHORT-CIRCUIT RELEASE - MAX	
ADJUSTMENT RANGE SHORT-TERM DELAYED SHORT-CIRCUIT RELEASE - MIN	1200 A
ADJUSTMENT RANGE UNDELAYED SHORT- CIRCUIT RELEASE - MAX	30000 A
ADJUSTMENT RANGE UNDELAYED SHORT- CIRCUIT RELEASE - MIN	4000 A
AMBIENT OPERATING TEMPERATURE - MAX	70 °C
AMBIENT OPERATING TEMPERATURE - MIN	-20 °C
AMBIENT STORAGE TEMPERATURE - MAX	70 °C
AMBIENT STORAGE TEMPERATURE - MIN	-20 °C
NUMBER OF AUXILIARY CONTACTS (CHANGE- OVER CONTACTS)	2
NUMBER OF AUXILIARY CONTACTS (NORMALLY CLOSED CONTACTS)	0
NUMBER OF AUXILIARY CONTACTS (NORMALLY OPEN CONTACTS)	0
NUMBER OF STANDARD MECHANICAL OPERATIONS PER HOUR - MAX	60
OPERATING SEQUENCE UP TO 690 V, 50/60 HZ (IEC/EN 60947)	85 kA
OVERLOAD RELEASE CURRENT SETTING - MAX	2000 A
OVERLOAD RELEASE CURRENT SETTING - MIN	800 A
POWER OF WITHDRAWABLE SWITCH WITH CASSETTE	220 W
RATED INSULATION VOLTAGE (UI)	1000 V
LIFESPAN, MECHANICAL	20000 operations (switching capacity, with maintenance) 10000 switching cycles (ON/OFF)
OVERVOLTAGE CATEGORY	III

SHORT-CIRCUIT RELEASE NON-DELAYED SETTING - MIN	0 A
WEIGHT OF CASSETTE VERSION (3-POLE)	29 kg
WEIGHT OF FIXED WITHDRAWABLE VERSION (3-POLE)	69 kg
AMBIENT OPERATING TEMPERATURE DETAILS	-20 °C - 70 °C
PROTECTION	P measurement
VOLTAGE RATING AT AC	690 V AC
SHORT-CIRCUIT RELEASE NON-DELAYED SETTING - MAX	30000 A
SHORT-CIRCUIT RELEASE DELAYED SETTING - MAX	20000 A
NUMBER OF POLES	Three-pole
DEGREE OF PROTECTION	IP55 with protective cover IP31 with door seals IP31
CLOSING DELAY VIA SPRING RELEASE	35 ms
LIFESPAN, ELECTRICAL	8000 operations (switching capacity) 16000 operations (switching cycles ON/OFF, with maintenance)
TYPE	• Air circuit breakers/switch-disconnector • Open circuit breaker
SPECIAL FEATURES	• Cassette must be separately ordered. • External IZMX-DTP-PTM-1 voltage measuring module required (1 module is suitable for 16 circuit breakers) • IZMX-DTP-PTM external voltage measuring module required • suitable for zone selectivity • suitable for communication • with integrated system monitor

- with integrated test possibility
- With graphic LCD display
- optionally fittable by user with comprehensive accessories
- Terminal capacity
hint: These are values used in separate switchgear. The actual values will depend on the temperature around the circuit breaker, which is influenced by the ambient temperature, the degree of protection (IP), the mounting height, the partitions, and any external ventilation. Depending on the specific switchgear design, this may result in derating, which can then be compensated for by increasing the cross-sectional area. Temperature rise tests in the specific switchgear can provide specific and detailed information.

**POSITION OF
CONNECTION FOR MAIN
CURRENT CIRCUIT**

Back side

RELEASE SYSTEM

Electronic release

**RATED OPERATING
VOLTAGE (UE) - MAX**

690 V

**RATED OPERATING
VOLTAGE (UE) - MIN**

690 V

**RATED OPERATIONAL
CURRENT FOR SPECIFIED
HEAT DISSIPATION (IN)**

2000 A

**RATED SHORT-CIRCUIT
BREAKING CAPACITY AT
400 V, 50 HZ**

105 kA

RATED SHORT-CIRCUIT MAKING CAPACITY UP TO 440 V, 50/60 HZ	231 kA
RATED SHORT-CIRCUIT MAKING CAPACITY UP TO 690 V, 50/60 HZ	166 kA
RATED SHORT-TIME WITHSTAND CURRENT (T = 1 S)	85 kA
RATED SHORT-TIME WITHSTAND CURRENT AT 50/60 HZ (T = 3 S)	66 kA
RATED UNINTERRUPTED CURRENT (IU) AT 50°C	2000 A
RATED UNINTERRUPTED CURRENT (IU) AT 60°C	2000 A
RATED UNINTERRUPTED CURRENT (IU) AT 70°C	2000 A
SHORT-CIRCUIT RELEASE DELAYED SETTING - MIN	1500 A
TERMINAL CAPACITY (COPPER BAR)	80 mm x 10 mm (2x) for withdrawable units (black)
POWER LOSS	220 W

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
□□:



□□□□
 Eaton House
 30 Pembroke Road
 Dublin 4, □□□
 Eaton.com

© 2025 □□ □□□□□□

Follow us on social media to get the latest product and support information.

