

Eaton 178577

Eaton Moeller® series M22 Joystick, with one operating point per operating direction, with metal shaft, 2 positions, Bezel: black, maintained, Vertical

PRODUCT NAME	Eaton Moeller® series M22 Joystick
CATALOG NUMBER	178577
PRODUCT LENGTH/DEPTH	100 mm
PRODUCT HEIGHT	30 mm
PRODUCT WIDTH	30 mm
PRODUCT WEIGHT	0.038 kg
CERTIFICATIONS	CSA File No.: 012528 CSA-C22.2 No. 94-91 IEC/EN 60947 IEC/EN 60947-5 VDE 0660 CSA CE CSA-C22.2 No. 14-13 UL 508 UL Category Control No.: NKCR CSA Class No.: 3211-03 UL UL File No.: E29184

TYPE	Joystick
PRODUCT CATEGORY	RMQ-Titan
ACTUATOR FUNCTION	Maintained Vertical
FITTED WITH:	Metal shaft Filament bulb (24 V) Front ring
OPERATING FREQUENCY	2000 Operations/h
CLIMATIC PROOFING	Damp heat, cyclic, to IEC 60068-2-30 Damp heat, constant, to IEC 60068-2-78
CONNECTION TO SMARTWIRE-DT	Yes With SWD-RMQ connections
ACTUATING FORCE	5 N
AMBIENT OPERATING TEMPERATURE - MAX	70 °C
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
FORCE FOR POSITIVE OPENING - MIN	0 N
JOYSTICK LENGTH	75 mm
NUMBER OF ACTUATION DIRECTIONS	2
NUMBER OF CONTACTS (NORMALLY CLOSED) PER ACTUATION DIRECTION	0
NUMBER OF CONTACTS (NORMALLY OPEN) PER ACTUATION DIRECTION	0
NUMBER OF MAKE-AND-BREAK CONTACTS PER DIRECTION	0
NUMBER OF SWITCH LEVELS	1
OPENING DIAMETER	22.5 mm
RATED OPERATIONAL CURRENT (IE) AT AC-21, 400 V, 415 V	0 A
BEZEL COLOR	Black
BEZEL MATERIAL	Plastic
MOUNTING POSITION	As required
DEGREE OF PROTECTION	IP66 NEMA 4X, 13

	IL04716002Z
	eaton-operating-m22-joystick-dimensions.eps
	eaton-operating-operating-m22-joystick-dimensions.eps
	eaton-operating-symbol-m22-joystick-symbol-004.eps
/	RMQ small E-Stop emergency-stop button

LIFESPAN, MECHANICAL	100,000 Operations
SHOCK RESISTANCE	30 g, Mechanical, According to IEC/EN 60068-2-27, Sinusoidal shock 11 ms Mechanical, According to IEC/EN 60068-2-27

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

