

## Eaton 178802

Eaton xComfort KLV LV systems Final Distribution Boards. Compact distribution board-flush mounting, 3-rows, flush sheet steel door, 36UPP-F

PRODUCT NAME	Eaton xComfort KLV energy distribution board
CATALOG NUMBER	178802
PRODUCT LENGTH/DEPTH	100 mm
PRODUCT HEIGHT	590 mm
PRODUCT WIDTH	360 mm
PRODUCT WEIGHT	4.2 kg
COMPLIANCES	RoHS conform
CERTIFICATIONS	IEC/EN 62208 IEC/EN 60670-24 (PD)

<b>USED WITH</b>	Installation distribution board KLV energy Basic device
<b>SPECIAL FEATURES</b>	<ul style="list-style-type: none"> <li>• IP30</li> <li>• Protection Class II</li> <li>• Plastic enclosure with sheet steel door, white (RAL 9016)</li> </ul>
<b>TYPE</b>	<ul style="list-style-type: none"> <li>• Basic device</li> <li>• Installation distribution board</li> <li>• KLV energy</li> </ul>
<b>FEATURES</b>	EMC-version
<b>10.10 TEMPERATURE RISE</b>	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
<b>10.11 SHORT-CIRCUIT RATING</b>	Is the panel builder's responsibility.
<b>10.12 ELECTROMAGNETIC COMPATIBILITY</b>	Is the panel builder's responsibility.
<b>10.13 MECHANICAL FUNCTION</b>	Meets the product standard's requirements.
<b>10.2.2 CORROSION RESISTANCE</b>	Meets the product standard's requirements.
<b>10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES</b>	Meets the product standard's requirements.
<b>10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT</b>	Meets the product standard's requirements.
<b>10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS</b>	650 °C; meets the product standard's requirements.
<b>10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION</b>	Not relevant to indoor installations.
<b>10.2.5 LIFTING</b>	Does not apply to enclosures without lifting aids.

	<a href="#">eaton-xcomfort-compact-distribution-boxes-brochure-br014015en-en-us.pdf</a>
	<a href="#">eaton-lighting-xcomfort-klv-lv-systems-dimensions-003.eps</a>
	<a href="#">eaton-lighting-xcomfort-klv-lv-systems-dimensions-007.eps</a>

<b>10.2.6 MECHANICAL IMPACT</b>	IK05
<b>10.2.7 INSCRIPTIONS</b>	Meets the product standard's requirements.
<b>10.3 DEGREE OF PROTECTION OF ASSEMBLIES</b>	IP30
<b>10.4 CLEARANCES AND CREEPAGE DISTANCES</b>	Is the panel builder's responsibility.
<b>10.5 PROTECTION AGAINST ELECTRIC SHOCK</b>	Protection class 2, therefore not applicable.
<b>10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS</b>	Is the panel builder's responsibility.
<b>10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS</b>	Is the panel builder's responsibility.
<b>10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS</b>	Is the panel builder's responsibility.
<b>10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH</b>	Ui = 400 V AC
<b>10.9.3 IMPULSE WITHSTAND VOLTAGE</b>	4 kV
<b>10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL</b>	Meets the product standard's requirements.
<b>FITTED WITH:</b>	Neutral and protective conductor terminals with KSK plug-in terminal technology Wall trough Cable retainer Nail lugs Door/Frame Spirit level for leveling Front cover Imprintable sheet Device support rails Installation instructions 3D adjustment element for mounting designed to adjust the mounting depth by up to 18 mm
<b>ENCLOSURE MATERIAL</b>	Plastic
<b>BUILT-IN HEIGHT</b>	0 mm
<b>BUILT-IN WIDTH</b>	0 mm
<b>CABLE ENTRY POSTION</b>	Cable entries on top and bottom, side, back plate

<b>TERMINAL TYPE</b>	Plug-in terminals
<b>BUILT-IN DEPTH</b>	88 mm
<b>HEAT DISS. AMBIENT 35°C DELTA T:20°C FLUSH MOUNT INDIVID. ENCL. TOP(IEC 60890)</b>	20 W
<b>HEAT DISS. AMBIENT 35°C DELTA T:35°C FLUSH MOUNT INDIVID. ENCL. TOP(IEC 60890)</b>	43 W
<b>CLOSURE TYPE</b>	Other
<b>COVER/DOOR COLOR</b>	White
<b>COVER/DOOR MODEL</b>	With notch
<b>COVER/DOOR TYPE</b>	Door Single
<b>RAL-NUMBER</b>	9016
<b>WIDTH IN NUMBER OF MODULAR SPACINGS</b>	12
<b>AMBIENT OPERATING TEMPERATURE DETAILS</b>	-5 °C - 40 °C
<b>APPLICATION</b>	Indoor (installation site)
<b>VOLTAGE RATING AT AC</b>	400 V AC
<b>COLOR</b>	White Traffic white (RAL 9016)
<b>NUMBER OF ROWS</b>	3
<b>FREQUENCY RATING OF CONTACTS</b>	50 Hz
<b>MODULE RACK TYPE</b>	Rail frame
<b>DEGREE OF PROTECTION</b>	IK05 (impact resistance) IP30
<b>NUMBER OF MODULE SPACE UNITS PER ROW</b>	12
<b>PROTECTION CLASS</b>	II (totally insulated)
<b>PROTECTIVE SHROUDING MATERIAL</b>	Plastic
<b>FUNCTIONS</b>	Extension possible Basic device Sealable
<b>MATERIAL</b>	Sheet steel, powder- coated Polystyren (plastic)
<b>MOUNTING METHOD</b>	Flush mounting Flush mounted (plaster) DIN-rail
<b>INTERNAL DEPTH</b>	75 mm
<b>PE AND N TERMINAL</b>	PE: 4 x (2.5 mm <sup>2</sup> - 25 mm <sup>2</sup> )

<b>NUMBER AND CROSS SECTION</b>	+ 28 x (0.5 mm <sup>2</sup> - 4 mm <sup>2</sup> ) N: 4 x (2.5 mm <sup>2</sup> - 25 mm <sup>2</sup> ) + 28 x (0.5 mm <sup>2</sup> - 4 mm <sup>2</sup> )
<b>NUMBER OF OPENINGS FOR SOCKET OUTLETS</b>	0

<b>PROJECT NAME:</b>
<b>PROJECT NUMBER:</b>
<b>PREPARED BY:</b>
:



Eaton House  
30 Pembroke Road  
Dublin 4,  
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

