

Eaton 183906

Eaton Moeller series IZMX/INX - ACB. Circuit-breaker, 4 pole, 2000A, 85 kA, Selective operation, IEC, Fixed

PRODUCT NAME	Eaton Moeller series IZMX/INX circuit-breaker
CATALOG NUMBER	183906
PRODUCT LENGTH/DEPTH	584 mm
PRODUCT HEIGHT	597 mm
PRODUCT WIDTH	521 mm
PRODUCT WEIGHT	56 kg
COMPLIANCES	IEC/EN 60947 IEC RoHS conform

USED WITH	Air circuit breakers/switch-disconnector Open circuit breaker
AMPERAGE RATING	2000 A
FEATURES	Motor drive optional Complete device with protection unit
10.10 TEMPERATURE RISE	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 SHORT-CIRCUIT RATING	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 ELECTROMAGNETIC COMPATIBILITY	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 MECHANICAL FUNCTION	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.
10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	Meets the product standard's requirements.
10.2.5 LIFTING	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 MECHANICAL	Does not apply, since the

[eaton-circuit-breaker-izmx-inx-mccb-dimensions-013.eps](#)

[eaton-circuit-breaker-mounting-izmx-inx-mccb-dimensions.eps](#)

[eaton-circuit-breaker-mounting-izmx-inx-mccb-dimensions-002.eps](#)

IMPACT	entire switchgear needs to be evaluated.
10.2.7 INSCRIPTIONS	Meets the product standard's requirements.
10.3 DEGREE OF PROTECTION OF ASSEMBLIES	Does not apply, since the entire switchgear needs to be evaluated.
10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
FITTED WITH:	Switched-off indicator
FRAME	IZMX40
POLLUTION DEGREE	3
RATED UNINTERRUPTED CURRENT (IU)	2000 A
MOUNTING METHOD	Fixed
EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT	150 W
RATED IMPULSE WITHSTAND VOLTAGE (UIMP)	12 kV AC
UTILIZATION CATEGORY	B
DEVICE CONSTRUCTION	Built-in device fixed built-in technique
DIRECTION OF INCOMING SUPPLY	As required
ELECTRICAL CONNECTION TYPE OF MAIN CIRCUIT	Rail connection

ACTUATOR TYPE	Push button
SHORT-CIRCUIT RELEASE NON-DELAYED SETTING	1.5 - 10 x I _r
ADJUSTMENT RANGE SHORT-TERM DELAYED SHORT-CIRCUIT RELEASE - MAX	20000 A
ADJUSTMENT RANGE SHORT-TERM DELAYED SHORT-CIRCUIT RELEASE - MIN	1200 A
ADJUSTMENT RANGE UNDELAYED SHORT- CIRCUIT RELEASE - MAX	30000 A
ADJUSTMENT RANGE UNDELAYED SHORT- CIRCUIT RELEASE - MIN	4000 A
AMBIENT OPERATING TEMPERATURE - MAX	70 °C
AMBIENT OPERATING TEMPERATURE - MIN	-20 °C
AMBIENT STORAGE TEMPERATURE - MAX	70 °C
AMBIENT STORAGE TEMPERATURE - MIN	-20 °C
HEAT DISSIPATION AT RATED CURRENT WITH FIXED MOUNTING	150 W
NUMBER OF AUXILIARY CONTACTS (CHANGE- OVER CONTACTS)	2
NUMBER OF AUXILIARY CONTACTS (NORMALLY CLOSED CONTACTS)	0
NUMBER OF AUXILIARY CONTACTS (NORMALLY OPEN CONTACTS)	0
NUMBER OF STANDARD MECHANICAL OPERATIONS PER HOUR - MAX	60
OPERATING SEQUENCE UP TO 690 V, 50/60 HZ (IEC/EN 60947)	75 kA
OVERLOAD RELEASE CURRENT SETTING - MAX	2000 A
OVERLOAD RELEASE CURRENT SETTING - MIN	800 A
RATED INSULATION	1000 V

VOLTAGE (UI)	
LIFESPAN, MECHANICAL	20000 operations (switching capacity, with maintenance) 10000 switching cycles (ON/OFF)
OVERVOLTAGE CATEGORY	III
SHORT-CIRCUIT RELEASE NON-DELAYED SETTING - MIN	0 A
WEIGHT OF FIXED MOUNTING VERSION (4- POLE)	56 kg
AMBIENT OPERATING TEMPERATURE DETAILS	-20 °C - 70 °C
PROTECTION	Selective operation
VOLTAGE RATING AT AC	690 V AC
SHORT-CIRCUIT RELEASE NON-DELAYED SETTING - MAX	30000 A
SHORT-CIRCUIT RELEASE DELAYED SETTING - MAX	20000 A
NUMBER OF POLES	Four-pole
DEGREE OF PROTECTION	IP31 IP31 with door seals IP55 with protective cover
CLOSING DELAY VIA SPRING RELEASE	35 ms
LIFESPAN, ELECTRICAL	16000 operations (switching cycles ON/OFF, with maintenance) 8000 operations (switching capacity)
TYPE	<ul style="list-style-type: none"> • Air circuit breakers/switch-disconnector • Open circuit breaker
SPECIAL FEATURES	<ul style="list-style-type: none"> • Main terminals must be separately ordered. • suitable for zone selectivity • optionally fittable by user with comprehensive accessories

- Terminal capacity
hint: These are values used in separate switchgear. The actual values will depend on the temperature around the circuit breaker, which is influenced by the ambient temperature, the degree of protection (IP), the mounting height, the partitions, and any external ventilation. Depending on the specific switchgear design, this may result in derating, which can then be compensated for by increasing the cross-sectional area. Temperature rise tests in the specific switchgear can provide specific and detailed information.

POSITION OF CONNECTION FOR MAIN CURRENT CIRCUIT	Back side
RELEASE SYSTEM	Electronic release
RATED OPERATING VOLTAGE (UE) - MAX	690 V
RATED OPERATING VOLTAGE (UE) - MIN	690 V
RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)	2000 A
RATED SHORT-CIRCUIT BREAKING CAPACITY AT 400 V, 50 HZ	85 kA
RATED SHORT-CIRCUIT MAKING CAPACITY UP TO 440 V, 50/60 HZ	187 kA
RATED SHORT-CIRCUIT MAKING CAPACITY UP TO	166 kA

690 V, 50/60 HZ

RATED SHORT-TIME WITHSTAND CURRENT (T = 1 S)	85 kA
---	-------

RATED SHORT-TIME WITHSTAND CURRENT AT 50/60 HZ (T = 3 S)	66 kA
---	-------

RATED UNINTERRUPTED CURRENT (IU) AT 50°C	2000 A
---	--------

RATED UNINTERRUPTED CURRENT (IU) AT 60°C	2000 A
---	--------

RATED UNINTERRUPTED CURRENT (IU) AT 70°C	2000 A
---	--------

SHORT-CIRCUIT RELEASE DELAYED SETTING - MIN	1500 A
--	--------

TERMINAL CAPACITY (COPPER BAR)	80 mm x 10 mm (2x) for fixed mounting (black)
---	--

POWER LOSS	150 W
-------------------	-------

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

