

Eaton 179529

Eaton Moeller® series DILH Contactor, Ith = 1714 A, RA 110: 48 - 110 V 40 - 60 Hz/48 - 110 V DC, AC and DC operation, Screw connection

PRODUCT NAME	Eaton Moeller® series DILH contactor
CATALOG NUMBER	179529
PRODUCT LENGTH/DEPTH	232 mm
PRODUCT HEIGHT	342 mm
PRODUCT WIDTH	260 mm
PRODUCT WEIGHT	15 kg
CERTIFICATIONS	CSA-C22.2 No. 60947-4-1-14 UL UL File No.: E29096 CSA File No.: 012528 CCC CE CSA IEC/EN 60947-4-1 VDE 0660 CSA Class No.: 3211-04 UL 60947-4-1 UL Category Control No.: NLDX IEC/EN 60947
CATALOG NOTES	<ul style="list-style-type: none">• Contacts according to EN 50012• Conventional thermal current Ith of main contacts (1-pole, open) at 60°

ACCESSORIES	Fitting options auxiliary contacts: on the side: 2 x DILM820-XHI11(V)-SI; 2 x DILM820-XHI11-SA
10.10 TEMPERATURE RISE	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 SHORT-CIRCUIT RATING	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 ELECTROMAGNETIC COMPATIBILITY	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 MECHANICAL FUNCTION	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.
10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	Meets the product standard's requirements.
10.2.5 LIFTING	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 MECHANICAL IMPACT	Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 INSCRIPTIONS	Meets the product standard's requirements.

CHARACTERISTIC CURVE	eaton-contactors-dilh-characteristic-curve.eps IL034039ZU2021_09.pdf
	eaton-contactors-contact-dilm-wiring-diagram-004.eps
	eaton-contactors-dimensions-009.eps eaton-contactors-dimensions-010.eps eaton-contactors-3d-drawing.eps eaton-contactors-mounting-dilm-3d-drawing-002.eps

10.3 DEGREE OF PROTECTION OF ASSEMBLIES	Does not apply, since the entire switchgear needs to be evaluated.
10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
FITTED WITH:	Suppressor circuit in actuating electronics
OPERATING FREQUENCY	1000 mechanical Operations/h (AC operated) 1000 mechanical Operations/h (DC operated)
POLLUTION DEGREE	3
CLIMATIC PROOFING	Damp heat, cyclic, to IEC 60068-2-30 Damp heat, constant, to IEC 60068-2-78
RATED IMPULSE WITHSTAND VOLTAGE (UIMP)	8000 V AC
UTILIZATION CATEGORY	AC-1: Non-inductive or slightly inductive loads, resistance furnaces
CONNECTION	Screw terminals
AMBIENT OPERATING TEMPERATURE - MAX	60 °C
AMBIENT OPERATING TEMPERATURE - MIN	-40 °C
AMBIENT STORAGE	80 °C

TEMPERATURE - MAX	
AMBIENT STORAGE TEMPERATURE - MIN	-40 °C
CONVENTIONAL THERMAL CURRENT ITH AT 55°C (3-POLE, OPEN)	1462 A
CONVENTIONAL THERMAL CURRENT ITH OF MAIN CONTACTS (1-POLE, OPEN)	3500 A
EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT PVID	0 W
HEAT DISSIPATION CAPACITY PDISS	0 W
HEAT DISSIPATION PER POLE, CURRENT-DEPENDENT PVID	63 W
APPLICATION	Mains contactors for resistive loads from 1000 A
PRODUCT CATEGORY	Contactors
ELECTRICAL CONNECTION TYPE OF MAIN CIRCUIT	Rail connection
SCREWDRIVER SIZE	0.8 x 5.5/1 x 6 mm, Terminal screw, Control circuit cables, Standard screwdriver 2, Terminal screw, Control circuit cables, Pozidriv screwdriver
VOLTAGE TYPE	AC/DC
DEGREE OF PROTECTION	IP00
NUMBER OF AUXILIARY CONTACTS (NORMALLY CLOSED CONTACTS)	2
NUMBER OF AUXILIARY CONTACTS (NORMALLY OPEN CONTACTS)	2
NUMBER OF CONTACTS (NORMALLY CLOSED) AS MAIN CONTACT	0
NUMBER OF MAIN CONTACTS (NORMALLY OPEN CONTACT)	3
RATED BREAKING CAPACITY AT 1000 V	5800 A
RATED BREAKING	8200 A

CAPACITY AT 220/230 V	
RATED BREAKING CAPACITY AT 380/400 V	8200 A
RATED BREAKING CAPACITY AT 500 V	8200 A
RATED BREAKING CAPACITY AT 660/690 V	8200 A
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 50 HZ - MAX	110 V
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 50 HZ - MIN	110 V
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 60 HZ - MAX	110 V
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 60 HZ - MIN	110 V
DROP-OUT VOLTAGE	AC operated: 0.2 x US max - 0.6 x US min, AC operated 0.2 x US max - 0.6 x US min, DC operated
OVERVOLTAGE CATEGORY	III
BEHAVIOR IN MARGINAL AND TRANSITIONAL CONDITIONS	Sealing - Voltage interruptions (0 - 0.2 x Uc min ≤ 10 ms: Time is bridged successfully Sealing - Pick-up phase (0 - 0.7 x Uc min: Contactor does not switch on Sealing - Excess voltage (1.15 - 1.3 x Uc max): Contactor remains switched on Sealing - Voltage drops (0.2 - 0.6 x Uc min ≤ 12 ms Sealing - Pick-up phase (0.7 x Uc min - 1.15 x Uc max): Contactor switches on with certainty Sealing - Voltage drops (0.2 - 0.6 x Uc min) > 12 ms: Drop-out of the contactor Sealing - Voltage drops (0.6 - 0.7 x Uc min: Contactor remains switched on Sealing - Voltage interruptions 0 - 0.2 x Uc

	min) > 10 ms: Drop-out of the contactor
DUTY FACTOR	100 %
ELECTROMAGNETIC COMPATIBILITY	Designed for operation in industrial environments. Its use in residential environments may cause radio-frequency interference, requiring additional noise suppression.
LIFESPAN, MECHANICAL	5,000,000 Operations (AC operated) 5,000,000 Operations (DC operated)
PICK-UP VOLTAGE	0.7 - 1.15 V DC x Us 0.7 - 1.15 V AC x Us
POWER CONSUMPTION, PICK-UP, 50 HZ	800 VA, Pull-in power, Coil in a cold state and 1.0 x Us 700 W, Pull-in power, Coil in a cold state and 1.0 x Us
SAFE ISOLATION	1000 V AC, Between coil and contacts, According to EN 61140
POWER CONSUMPTION, PICK-UP, 60 HZ	700 W, Pull-in power, Coil in a cold state and 1.0 x Us 800 VA, Pull-in power, Coil in a cold state and 1.0 x Us
SCREW SIZE	M3.5, Terminal screw, Control circuit cables M12, Terminal screw, Main connections
POWER CONSUMPTION, SEALING, 50 HZ	26.4 VA, Coil in a cold state and 1.0 x Us 10.3 W, Coil in a cold state and 1.0 x Us
POWER CONSUMPTION, SEALING, 60 HZ	10.3 W, Coil in a cold state and 1.0 x Us 26.4 VA, Coil in a cold state and 1.0 x Us
RESISTANCE	500 mΩ (Admissible transitional contact resistance - of the external control circuit device when actuating A11)
SWITCHING CAPACITY (AUXILIARY CONTACTS, GENERAL USE)	15 A, 600 V AC, (UL/CSA) 1 A, 250 V DC, (UL/CSA)
SWITCHING CAPACITY	P300, DC operated

(AUXILIARY CONTACTS, PILOT DUTY)	(UL/CSA) A600, AC operated (UL/CSA)
TERMINAL CAPACITY (FLEXIBLE WITH FERRULE)	1 x (0.75 - 2.5) mm ² , Control circuit cables 2 x (0.75 - 2.5) mm ² , Control circuit cables
SHOCK RESISTANCE	8 g, N/C auxiliary contact, Mechanical, according to IEC/EN 60068-2-27, Half- sinusoidal shock 10 ms 10 g, N/O auxiliary contact, Mechanical, according to IEC/EN 60068-2-27, Half- sinusoidal shock 10 ms 10 g, N/O main contact, Mechanical, according to IEC/EN 60068-2-27, Half- sinusoidal shock 10 ms
TERMINAL CAPACITY (SOLID)	1 x (0.75 - 2.5) mm ² , Control circuit cables 2 x (0.75 - 2.5) mm ² , Control circuit cables
TERMINAL CAPACITY (SOLID/STRANDED AWG)	18 - 14, Control circuit cables
SIGNAL LEVEL	5 V - 15 V, PLC signal level (A3 - A4) to IEC/EN 61131-2 (type 2), Magnet systems
TERMINAL CAPACITY (BUSBAR)	80 mm width, Main connection
SWITCHING CAPACITY (MAIN CONTACTS, GENERAL USE)	1600 A, Maximum motor rating (UL/CSA)
POWER CONSUMPTION	Control transformer with uk ≤ 7%
TIGHTENING TORQUE	1.2 Nm, Screw terminals, Control circuit cables 35 Nm, Main cable connection screw/bolt
WIDTH ACROSS FLATS	18 mm
RATED CONTROL SUPPLY VOLTAGE (US) AT DC - MAX	110 V
RATED CONTROL SUPPLY VOLTAGE (US) AT DC - MIN	110 V
RATED INSULATION VOLTAGE (UI)	1000 V
RATED MAKING CAPACITY (COS PHI TO IEC/EN 60947)	9840 A

RATED OPERATIONAL CURRENT (IE) AT AC-3, 380 V, 400 V, 415 V	0 A
RATED OPERATIONAL CURRENT (IE) AT AC-4, 400 V	0 A
RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)	1400 A
RATED OPERATIONAL POWER AT AC-3, 380/400 V, 50 HZ	0 kW
RATED OPERATIONAL POWER AT AC-4, 380/400 V, 50 HZ	0 kW
RATED OPERATIONAL POWER (NEMA)	0 kW
RATED OPERATIONAL VOLTAGE (UE) AT AC - MAX	1000 V
STATIC HEAT DISSIPATION, NON-CURRENT-DEPENDENT PVS	6.5 W
STRIPPING LENGTH (CONTROL CIRCUIT CABLE)	10 mm
SWITCHING TIME (AC OPERATED, MAKE CONTACTS, CLOSING DELAY) - MAX	70 ms
SWITCHING TIME (AC OPERATED, MAKE CONTACTS, OPENING DELAY) - MAX	110 ms
SPECIAL PURPOSE RATING OF RESISTANCE AIR HEATING	1400 A, 600 V 60 Hz 3phase, 347 V 60 Hz 1phase, (UL/CSA) 1400 A, 480 V 60 Hz 3phase, 277 V 60 Hz 1phase, (UL/CSA)
CONVENTIONAL THERMAL CURRENT ITH AT 40°C (3-POLE, OPEN)	1714 A
CONVENTIONAL THERMAL CURRENT ITH AT 50°C (3-POLE, OPEN)	1533 A
CONVENTIONAL THERMAL CURRENT ITH AT 60°C (3-POLE, OPEN)	1400 A

ACTUATING VOLTAGE	RA 110: 48 - 110 V 40 - 60 Hz/48 - 110 V DC
ALTITUDE	Max. 2000 m
OPERATING VOLTAGE AT AC, 50 HZ - MIN	48 V
OPERATING VOLTAGE AT AC, 50 HZ - MAX	110 V
OPERATING VOLTAGE AT AC, 60 HZ - MIN	48 V
OPERATING VOLTAGE AT AC, 60 HZ - MAX	110 V

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

