



Eaton 180615

Eaton Moeller series xEffect - FRCmM Type AC, A, U, R RCCB. Residual current circuit breaker (RCCB), 40A, 4p, 300mA, type A, 110V

□□□□

PRODUCT NAME	Eaton Moeller series xEffect - FRCmM Type AC, A, U, R RCCB
CATALOG NUMBER	180615
PRODUCT LENGTH/DEPTH	76 mm
PRODUCT HEIGHT	80 mm
PRODUCT WIDTH	70 mm
PRODUCT WEIGHT	0.373 kg
COMPLIANCES	RoHS conform
CERTIFICATIONS	IEC/EN 61008 EN45545-2 IEC 61373

USED WITH	Type A Residual current circuit breakers FRCmM
AMPERAGE RATING	40 A
FEATURES	Additional equipment possible Residual current circuit breaker
10.10 TEMPERATURE RISE	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 SHORT-CIRCUIT RATING	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 ELECTROMAGNETIC COMPATIBILITY	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 MECHANICAL FUNCTION	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.
10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	Meets the product standard's requirements.
10.2.5 LIFTING	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 MECHANICAL IMPACT	Does not apply, since the entire switchgear needs to

	be evaluated.
10.2.7 INSCRIPTIONS	Meets the product standard's requirements.
10.3 DEGREE OF PROTECTION OF ASSEMBLIES	Does not apply, since the entire switchgear needs to be evaluated.
10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
FITTED WITH:	Interlocking device
FRAME	45 mm
FREQUENCY RATING	50 Hz / 60 Hz
POLLUTION DEGREE	2
MOUNTING METHOD	DIN rail Quick attachment with 2 latch positions for DIN-rail IEC/EN 60715
CLIMATIC PROOFING	25-55 °C / 90-95% relative humidity according to IEC 60068-2
EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT	8.8 W
RATED IMPULSE WITHSTAND VOLTAGE (UIMP)	4 kV
RATED SHORT-TIME WITHSTAND CURRENT (ICW)	10 kA
ADMISSIBLE BACK-UP FUSE OVERLOAD - MAX	40 A gG/gL
BUILT-IN WIDTH (NUMBER OF UNITS)	70 mm (4 SU)

BUSBAR MATERIAL THICKNESS	0.8 mm - 2 mm
SHORT-CIRCUIT RATING	63 A (max. admissible back-up fuse)
STATUS INDICATION	White / blue
TERMINAL PROTECTION	Finger and hand touch safe, DGUV VS3, EN 50274
TERMINALS (TOP AND BOTTOM)	Twin-purpose terminals
TEST CIRCUIT RANGE	94 V AC - 210 V AC
AMBIENT OPERATING TEMPERATURE - MAX	40 °C
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
BUILT-IN DEPTH	70.5 mm
CONNECTABLE CONDUCTOR CROSS SECTION (MULTI-WIRED) - MAX	16 mm ²
CONNECTABLE CONDUCTOR CROSS SECTION (MULTI-WIRED) - MIN	1.5 mm ²
CONNECTABLE CONDUCTOR CROSS SECTION (SOLID-CORE) - MAX	35 mm ²
CONNECTABLE CONDUCTOR CROSS SECTION (SOLID-CORE) - MIN	1.5 mm ²
FAULT CURRENT RATING	300 mA
HEAT DISSIPATION CAPACITY	0 W
HEAT DISSIPATION PER POLE, CURRENT-DEPENDENT	2.2 W
PERMITTED STORAGE AND TRANSPORT TEMPERATURE - MAX	60 °C
PERMITTED STORAGE AND TRANSPORT TEMPERATURE - MIN	-35 °C
CONTACT POSITION INDICATOR COLOR	Red / green
MOUNTING POSITION	As required
LIFESPAN, MECHANICAL	20000 operations
DEGREE OF PROTECTION	IP20, IP40 with suitable enclosure IP20
IMPULSE WITHSTAND	Partly surge-proof 250 A

CURRENT	250 A (8/20 µs) surge-proof
NUMBER OF POLES	Four-pole
LEAKAGE CURRENT TYPE	A
LIFESPAN, ELECTRICAL	4000 operations
TYPE	• FRCmM • Residual current circuit breakers • Type A
SPECIAL FEATURES	• Current test marks as per inscription • Maximum operating temperature is 75 °C: Starting at 40 °C, the max. permissible continuous current decreases by 2.5% for every 1 °C
APPLICATION	• Switchgear for industrial and advanced commercial applications • xEffect - Switchgear for industrial and advanced commercial applications
SENSITIVITY TYPE	Pulse-current sensitive
TERMINAL CAPACITY (CABLE)	M5 (with cross-recessed screw as defined in EN ISO 4757-Z2, PZ2)
RATED FAULT CURRENT - MAX	0.3 A
RATED FAULT CURRENT - MIN	0.3 A
RATED INSULATION VOLTAGE (UI)	440 V
RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)	40 A
RATED OPERATIONAL VOLTAGE (UE) - MAX	110 V
RATED RESIDUAL MAKING AND BREAKING CAPACITY	500 A
STATIC HEAT	0 W

DISSIPATION, NON-CURRENT-DEPENDENT	
SURGE CURRENT CAPACITY	0.25 kA
WIDTH IN NUMBER OF MODULAR SPACINGS	4
VOLTAGE RATING (IEC/EN 60947-2)	110/190 V
VOLTAGE TYPE	AC
TERMINAL CAPACITY (SOLID WIRE)	1.5 mm ² - 35 mm ²
TRIPPING TIME	Non-delayed
RATED SHORT-CIRCUIT STRENGTH	10 kA with back-up fuse
TIGHTENING TORQUE	2 Nm - 2.4 Nm
TERMINAL CAPACITY (STRANDED CABLE)	16 mm ² (2x)
RAL-NUMBER	7035
COLOR	Gray

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



0000
Eaton House
30 Pembroke Road
Dublin 4, 0000
Eaton.com

© 2025 00 00000000

Follow us on social media to get the latest product and support information.

