

Eaton 184261

Eaton Moeller series IZMX/INX - ACB. Motor operator 110-125 VAC/DC, 40, +

PRODUCT NAME	Eaton Moeller series IZMX/INX motor operator
CATALOG NUMBER	184261
PRODUCT LENGTH/DEPTH	200 mm
PRODUCT HEIGHT	100 mm
PRODUCT WIDTH	150 mm
PRODUCT WEIGHT	1.25 kg
COMPLIANCES	RoHS conform

USED WITH	INX40... IZMX40...
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 50 HZ - MAX	127 V
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 50 HZ - MIN	110 V
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 60 HZ - MAX	127 V
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 60 HZ - MIN	110 V
RATED CONTROL SUPPLY VOLTAGE (US) AT DC - MAX	125 V
RATED CONTROL SUPPLY VOLTAGE (US) AT DC - MIN	110 V
ACCESSORY/SPARE PART TYPE	Remote switching
STARTING CURRENT RATING	9 A AC 50/60 Hz, 7.5 A DC
SWITCH DRIVE TYPE	Motor drive
AMBIENT OPERATING TEMPERATURE - MAX	70 °C
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
NUMBER OF ACTUATION PER MINUTE - MAX	3
VOLTAGE TYPE	AC/DC
CONTROL VOLTAGE OPERATING RANGE	110 - 125 V DC 0.85 - 1.1 x Us 110 - 127 V AC (50/60 Hz)
TYPE	Accessory

SPECIAL FEATURES

- Signalling switch for "Spring-operated stored energy mechanism tensioned" message is included as standard.
- Switching frequency = 60/h
- The motor

eaton-izmx16-40-spring-release-latch-check-il0131088en-us.pdf	
eaton-circuit-breaker-izmx-inx-motor-operator-3d-drawing-002.eps	

automatically
tensions the spring
force storage
mechanism for
remote or local
actuation.

POWER CONSUMPTION	425 VA AC 50/60 Hz 275 W DC
--------------------------	--------------------------------

NECESSARY TIME FOR CHARGING SPRING- OPERATED STORED ENERGY MECHANISM AT 1 X US	6 s DC 6 s AC 50/60 Hz
---	---------------------------

RATED OPERATIONAL CURRENT	2 A DC 3 A AC 50/60 Hz
--------------------------------------	---------------------------

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the
latest product and support
information.

