

## Eaton 180658

Eaton DE11 Variable speed starter, Rated operational voltage 230 V AC, 1-phase, Ie 2.7 A, 0.55 kW, 0.5 HP

<b>PRODUCT NAME</b>	Eaton DE11 Variable speed starter
<b>CATALOG NUMBER</b>	180658
<b>PRODUCT LENGTH/DEPTH</b>	169 mm
<b>PRODUCT HEIGHT</b>	230 mm
<b>PRODUCT WIDTH</b>	45 mm
<b>PRODUCT WEIGHT</b>	1.04 kg
<b>CERTIFICATIONS</b>	IEC/EN61800-3 IEC/EN61800-5 RoHS, ISO 9001 UL Category Control No.: NMMS, NMMS7 CSA-C22.2 No. 14 IEC/EN 61800-3 Safety requirements: IEC/EN 61800-5-1 UL File No.: E172143 UL RCM UL 508C UL report applies to both US and Canada CE Certified by UL for use in Canada Specification for general requirements: IEC/EN 61800-2 CUL
<b>CATALOG NOTES</b>	Overload cycle for 60 s every 600 s

<b>FEATURES</b>	Parameterization: drivesConnect Parameterization: drivesConnect mobile (App) Parameterization: Fieldbus
	Parameterization: Keypad
<b>10.10 TEMPERATURE RISE</b>	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
<b>10.11 SHORT-CIRCUIT RATING</b>	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
<b>10.12 ELECTROMAGNETIC COMPATIBILITY</b>	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
<b>10.13 MECHANICAL FUNCTION</b>	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
<b>10.2.2 CORROSION RESISTANCE</b>	Meets the product standard's requirements.
<b>10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES</b>	Meets the product standard's requirements.
<b>10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT</b>	Meets the product standard's requirements.
<b>10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS</b>	Meets the product standard's requirements.
<b>10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION</b>	Meets the product standard's requirements.
<b>10.2.5 LIFTING</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.2.6 MECHANICAL</b>	Does not apply, since the

<b>DECLARATIONS OF CONFORMITY</b>	<a href="#">eaton-variable-speed-starter-declaration-of-conformity-uk251079en.pdf</a>
	<a href="#">IL040005ZU</a>
	<a href="#">eaton-powerxl-variable-frequency-drives-hvac-brochure-br040012en-en-us.pdf</a>
	<a href="#">eaton-powerxl-de1-variable-speed-starter-brochure-br040003en-en-us.pdf</a>
	<a href="#">eaton-de1-variable-speed-starter-manual-mn040011-zh-cn.pdf</a>
	<a href="#">eaton-frequency-inverter-dimensions-009.eps</a>
	<a href="#">eaton-frequency-inverter-3d-drawing-017.eps</a>
	<a href="#">How does the internal motor protection work?</a>
	<a href="#">The OP System Bus - Parameterizing - Control</a>
	<a href="#">DX-COM-STICK3 Connection</a>

<b>IMPACT</b>	entire switchgear needs to be evaluated.
<b>10.2.7 INSCRIPTIONS</b>	Meets the product standard's requirements.
<b>10.3 DEGREE OF PROTECTION OF ASSEMBLIES</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.4 CLEARANCES AND CREEPAGE DISTANCES</b>	Meets the product standard's requirements.
<b>10.5 PROTECTION AGAINST ELECTRIC SHOCK</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS</b>	Is the panel builder's responsibility.
<b>10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS</b>	Is the panel builder's responsibility.
<b>10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH</b>	Is the panel builder's responsibility.
<b>10.9.3 IMPULSE WITHSTAND VOLTAGE</b>	Is the panel builder's responsibility.
<b>10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL</b>	Is the panel builder's responsibility.
<b>FITTED WITH:</b>	PC connection
<b>CLIMATIC PROOFING</b>	< 95 average relative humidity (RH), no condensation, no corrosion
<b>CONNECTION TO SMARTWIRE-DT</b>	In conjunction with DX-NET-SWD3 SmartWire DT module Yes
<b>OPERATING MODE</b>	Speed control with slip compensation U/f control
<b>RATED IMPULSE WITHSTAND VOLTAGE (UIMP)</b>	2000 V
<b>FRAME SIZE</b>	FS1
<b>ALTITUDE</b>	Max. 2000 m Above 1000 m with 1 % derating per 100 m
<b>APPLICATION IN DOMESTIC AND</b>	Yes

<b>COMMERCIAL AREA PERMITTED</b>	
<b>MAINS SWITCH-ON FREQUENCY</b>	Maximum of one time every 30 seconds
<b>AMBIENT OPERATING TEMPERATURE - MAX</b>	60 °C
<b>AMBIENT OPERATING TEMPERATURE - MIN</b>	-10 °C
<b>MAINS VOLTAGE - MAX</b>	240 V
<b>OUTPUT VOLTAGE - MAX</b>	250 V
<b>RATED OPERATIONAL POWER AT 220/230 V, 50 HZ, 3-PHASE</b>	0.55 kW
<b>RELATIVE SYMMETRIC NET FREQUENCY TOLERANCE</b>	10 %
<b>RELATIVE SYMMETRIC NET VOLTAGE TOLERANCE</b>	10 %
<b>AMBIENT OPERATING TEMPERATURE AT 150% OVERLOAD - MAX</b>	60 °C
<b>AMBIENT OPERATING TEMPERATURE AT 150% OVERLOAD - MIN</b>	-10 °C
<b>AMBIENT STORAGE TEMPERATURE - MAX</b>	70 °C
<b>AMBIENT STORAGE TEMPERATURE - MIN</b>	-40 °C
<b>APPARENT POWER AT 230 V</b>	1.08 kVA
<b>APPARENT POWER AT 240 V</b>	1.12 kVA
<b>APPLICATION IN INDUSTRIAL AREA PERMITTED</b>	Yes
<b>HEAT DISSIPATION DETAILS</b>	Operation (with 150 % overload)
<b>PRODUCT CATEGORY</b>	Variable speed starter
<b>PROTECTION</b>	Finger and back-of-hand proof, Protection against direct contact (BGV A3, VBG4)
<b>RESOLUTION</b>	0.03 Hz (Frequency resolution, setpoint value)
<b>STATIC HEAT DISSIPATION, NON-CURRENT-DEPENDENT</b>	0 W

<b>PVS</b>	
<b>VOLTAGE RATING - MAX</b>	240 V
<b>MOUNTING POSITION</b>	Vertical
<b>OVERVOLTAGE CATEGORY</b>	III
<b>COMMUNICATION INTERFACE</b>	Modbus RTU, built in CANopen®, built in OP-Bus (RS485), built in
<b>CONVERTER TYPE</b>	U converter
<b>DEGREE OF PROTECTION</b>	IP20 NEMA Other
<b>ASSIGNED MOTOR POWER AT 220/230 V, 60 HZ, 3-PHASE</b>	0.5 HP
<b>EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT PVID</b>	27 W
<b>HEAT DISSIPATION CAPACITY PDISS</b>	0 W
<b>HEAT DISSIPATION PER POLE, CURRENT-DEPENDENT PVID</b>	0 W
<b>INPUT CURRENT ILN AT 150% OVERLOAD</b>	7.3 A
<b>MAINS CURRENT DISTORTION</b>	120 %
<b>ASSIGNED MOTOR CURRENT IM AT 220 - 240 V, 60 HZ, 150% OVERLOAD</b>	2.2 A
<b>ASSIGNED MOTOR CURRENT IM AT 230 V, 50 HZ, 150% OVERLOAD</b>	2.7 A
<b>PROTOCOL</b>	MODBUS EtherNet/IP Other bus systems CAN
<b>OVERLOAD CURRENT IL AT 150% OVERLOAD</b>	4.05 A
<b>RATED FREQUENCY - MAX</b>	66 Hz
<b>RATED FREQUENCY - MIN</b>	45 Hz
<b>RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)</b>	2.7 A
<b>BRAKING CURRENT</b>	≤ 0.6 A (max. 6 A for 120 ms), Actuator for external motor brake

<b>ELECTROMAGNETIC COMPATIBILITY</b>	1st and 2nd environments (according to EN 61800-3)
<b>BRAKING TORQUE</b>	Adjustable to 100 %, DC - Main circuit Max. 30 % MN, Standard - Main circuit
<b>CABLE LENGTH</b>	C2 ≤ 10 m, Radio interference level, maximum motor cable length C3 ≤ 25 m, Radio interference level, maximum motor cable length C1 ≤ 5 m, Radio interference level, maximum motor cable length
<b>OUTPUT VOLTAGE (U2)</b>	240 V AC, 3-phase 230 V AC, 3-phase
<b>DELAY TIME</b>	< 10 ms, On-delay < 10 ms, Off-delay
<b>NUMBER OF INPUTS (ANALOG)</b>	1 (parameterizable, 0 - 10 V DC, 0/4 - 20 mA)
<b>NUMBER OF INPUTS (DIGITAL)</b>	4 (parameterizable, 10 - 30 V DC)
<b>RADIO INTERFERENCE CLASS</b>	C2, C3: depending on the motor cable length, the connected load, and ambient conditions. External radio interference suppression filters (optional) may be necessary. C1: for conducted emissions only Optional external radio interference suppression filter for longer motor cable lengths and for use in different EMC environments
<b>NUMBER OF OUTPUTS (DIGITAL)</b>	0
<b>STARTING CURRENT - MAX</b>	200 %, IH, max. starting current (High Overload), For 1.875 seconds every 600 seconds, Power section
<b>NUMBER OF PHASES (INPUT)</b>	1
<b>NUMBER OF RELAY</b>	1 (parameterizable, N/O, 6

<b>OUTPUTS</b>	A (250 V, AC-1) / 5 A (30 V, DC-1))
<b>NUMBER OF PHASES (OUTPUT)</b>	3
<b>POWER CONSUMPTION</b>	27 W
<b>RATED CONTROL SUPPLY VOLTAGE</b>	10 V DC (Us, max. 0.2 mA)
<b>SUPPLY FREQUENCY</b>	50/60 Hz
<b>LEAKAGE CURRENT AT GROUND IPE - MAX</b>	< 10 mA (DC-operated) < 3.5 mA (AC-operated)
<b>MAINS VOLTAGE - MIN</b>	200 V
<b>NOMINAL OUTPUT CURRENT I2N</b>	2.7 A
<b>NUMBER OF HW-INTERFACES (INDUSTRIAL ETHERNET)</b>	0
<b>NUMBER OF HW-INTERFACES (OTHER)</b>	0
<b>NUMBER OF HW-INTERFACES (PARALLEL)</b>	0
<b>NUMBER OF HW-INTERFACES (RS-232)</b>	0
<b>NUMBER OF HW-INTERFACES (RS-422)</b>	0
<b>NUMBER OF HW-INTERFACES (RS-485)</b>	1
<b>NUMBER OF HW-INTERFACES (SERIAL TTY)</b>	0
<b>NUMBER OF HW-INTERFACES (USB)</b>	0
<b>NUMBER OF INTERFACES (PROFINET)</b>	0
<b>NUMBER OF OUTPUTS (ANALOG)</b>	0
<b>OUTPUT AT LINEAR LOAD AT RATED OUTPUT VOLTAGE - MAX</b>	0.55 kW
<b>OUTPUT AT QUADRATIC LOAD AT RATED OUTPUT VOLTAGE - MAX</b>	0.55 kW
<b>OUTPUT FREQUENCY - MAX</b>	300 Hz
<b>OUTPUT FREQUENCY - MIN</b>	0 Hz
<b>SHORT-CIRCUIT PROTECTION (EXTERNAL OUTPUT CIRCUITS)</b>	Type 1 coordination via the power bus' feeder unit, Main circuit

<b>SHOCK RESISTANCE</b>	15 g, Mechanical, According to IEC/EN 60068-2-27, 11 ms
<b>SUITABLE FOR</b>	Branch circuits, (UL/CSA)
<b>SWITCHING FREQUENCY</b>	16 kHz, 4 - 32 kHz adjustable (audible), fPWM, Power section, Main circuit
<b>RATED OPERATIONAL CURRENT (IE)</b>	2.7 A at 150% overload (at an operating frequency of 16 kHz and an ambient air temperature of +50 °C)
<b>RATED OPERATIONAL VOLTAGE</b>	230 V AC, 1-phase 240 V AC, 1-phase
<b>SHORT-CIRCUIT PROTECTION RATING</b>	10 A, UL (Class CC or J), Safety device (fuse or miniature circuit-breaker), Power Wiring
<b>VIBRATION</b>	Resistance: According to EN 61800-5-1
<b>HEAT DISSIPATION AT CURRENT/SPEED</b>	10 W at 25% current and 0% speed 10 W at 25% current and 50% speed 10.9 W at 50% current and 0% speed 12.3 W at 50% current and 50% speed 15.1 W at 50% current and 90% speed 19.8 W at 100% current and 50% speed 25 W at 100% current and 90% speed 25.3 W at 100% current and 0% speed

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

:



Eaton House  
30 Pembroke Road  
Dublin 4,  
Eaton.com

© 2025

Follow us on social media to get the  
latest product and support  
information.

