



## Eaton 185516

Eaton xComfort KLV LV systems Final Distribution Boards. Hollow-wall-mounting expansion kit with screw terminal, 2-rows, form of delivery for projects, F2HWS-4PR



<b>PRODUCT NAME</b>	Eaton xComfort KLV project delivery form
<b>CATALOG NUMBER</b>	185516
<b>PRODUCT LENGTH/DEPTH</b>	40 mm
<b>PRODUCT HEIGHT</b>	465 mm
<b>PRODUCT WIDTH</b>	360 mm
<b>PRODUCT WEIGHT</b>	2.26 kg
<b>COMPLIANCES</b>	RoHS conform
<b>CERTIFICATIONS</b>	IEC/EN 62208, IEC/EN 60670-24 (PD)



Powering Business Worldwide

□□□□

<b>USED WITH</b>	KLV for projects Basic device Installation distribution boards
<b>SPECIAL FEATURES</b>	IP30 Protection Class II Sheet steel door, white (RAL 9016)
<b>TYPE</b>	Basic device Installation distribution boards KLV for projects
<b>ACCESSORY/SPARE PART TYPE</b>	Other Accessory
<b>FITTED WITH:</b>	Neutral-/protective conductor terminal Imprintable sheet Cable retainer 3D adjustment element for mounting Device support rails Front cover Installation instructions
<b>FREQUENCY RATING</b>	50 Hz
<b>COLOR</b>	Traffic white (RAL 9016)
<b>DEGREE OF PROTECTION</b>	IK05 (impact resistance) IP30
<b>TERMINAL TYPE</b>	Screw terminals
<b>AMBIENT OPERATING TEMPERATURE DETAILS</b>	-5 °C - 40 °C
<b>APPLICATION</b>	Indoor (installation site)
<b>COVER/DOOR COLOR</b>	White
<b>MATERIAL</b>	Polystyren (plastic) Sheet steel, powder-coated
<b>NUMBER OF ROWS</b>	2
<b>INSTALLATION TYPE</b>	Hollow-wall mounting
<b>MOUNTING METHOD</b>	Hollow wall
<b>FUNCTIONS</b>	Basic device Additional equipment
<b>MODULE RACK TYPE</b>	Rail frame
<b>NUMBER OF MODULE SPACE UNITS PER ROW</b>	12
<b>PROTECTION CLASS</b>	II (totally insulated)
<b>PROTECTIVE SHROUDING MATERIAL</b>	Plastic
<b>PE AND N TERMINAL NUMBER AND CROSS SECTION</b>	N: 13 x (0.75 mm <sup>2</sup> - 16 mm <sup>2</sup> ) PE: 13 x (0.75 mm <sup>2</sup> - 16 mm <sup>2</sup> )

□□

□□□□

[eaton-xcomfort-compact-distribution-boxes-brochure-br014015en-en-us.pdf](#)

