

Eaton 185761

Eaton DC1 Variable frequency drive, 400 V AC, 3-phase, 18 A, 7.5 kW, IP20/NEMA 0, Radio interference suppression filter, Brake chopper, FS3 DC1-34018FB-A20CE1

PRODUCT NAME	Eaton DC1 Variable frequency drive
CATALOG NUMBER	185761
PRODUCT LENGTH/DEPTH	175 mm
PRODUCT HEIGHT	273 mm
PRODUCT WIDTH	129 mm
PRODUCT WEIGHT	6 kg
CERTIFICATIONS	IEC/EN61800-3 UL 508C Certified by UL for use in Canada UL report applies to both US and Canada UL IEC/EN61800-5 Specification for general requirements: IEC/EN 61800-2 UL File No.: E172143 CSA-C22.2 No. 14 IEC/EN 61800-3 RoHS, ISO 9001 UL Category Control No.: NMMS, NMMS7 RCM CE CUL EAC Safety requirements: IEC/EN 61800-5-1 UkrSEPRO
CATALOG NOTES	<ul style="list-style-type: none">• Environmental class: 3C2, 3S2• Overload cycle for 60 s every 600 s

FEATURES	Parameterization: drivesConnect Parameterization: drivesConnect mobile (App) Parameterization: Fieldbus
	Parameterization: Keypad
10.10 TEMPERATURE RISE	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 SHORT-CIRCUIT RATING	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 ELECTROMAGNETIC COMPATIBILITY	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 MECHANICAL FUNCTION	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.
10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	Meets the product standard's requirements.
10.2.5 LIFTING	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 MECHANICAL	Does not apply, since the

DECLARATIONS OF CONFORMITY	eaton-variable-frequency-drive-declaration-of-conformity-uk251078en.pdf
INSTALLATION VIDEOS	Video PowerXL DA1
	IL04020009Z
	eaton-powerxl-variable-frequency-drives-dc1-da1-brochure-br040001en-en-us.pdf
	eaton-frequency-inverter-dimensions-020.eps
	eaton-frequency-inverter-3d-drawing-009.eps
	The OP System Bus - Parameterizing - Control
	How does the internal motor protection work?
	DX-COM-STICK3 Connection

IMPACT	entire switchgear needs to be evaluated.
10.2.7 INSCRIPTIONS	Meets the product standard's requirements.
10.3 DEGREE OF PROTECTION OF ASSEMBLIES	Does not apply, since the entire switchgear needs to be evaluated.
10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
FITTED WITH:	Brake chopper 7-digital display assembly IGBT inverter Radio interference suppression filter PC connection Control unit Internal DC link Breaking resistance Additional PCB protection
CLIMATIC PROOFING	< 95 average relative humidity (RH), no condensation, no corrosion
CONNECTION TO SMARTWIRE-DT	Yes In conjunction with DX-NET-SWD3 SmartWire DT module
OPERATING MODE	U/f control Sensorless vector control (SLV) Speed control with slip compensation

	BLDC motors PM motors Synchronous reluctance motors
RATED IMPULSE WITHSTAND VOLTAGE (UIMP)	2000 V
FRAME SIZE	FS3
ALTITUDE	Above 1000 m with 1 % derating per 100 m Max. 4000 m
APPLICATION IN DOMESTIC AND COMMERCIAL AREA PERMITTED	Yes
MAINS SWITCH-ON FREQUENCY	Maximum of one time every 30 seconds
AMBIENT OPERATING TEMPERATURE - MAX	50 °C
AMBIENT OPERATING TEMPERATURE - MIN	-10 °C
MAINS VOLTAGE - MAX	480 V
OUTPUT VOLTAGE - MAX	500 V
RELATIVE SYMMETRIC NET FREQUENCY TOLERANCE	10 %
RELATIVE SYMMETRIC NET VOLTAGE TOLERANCE	10 %
AMBIENT OPERATING TEMPERATURE AT 150% OVERLOAD - MAX	50 °C
AMBIENT OPERATING TEMPERATURE AT 150% OVERLOAD - MIN	-10 °C
AMBIENT STORAGE TEMPERATURE - MAX	60 °C
AMBIENT STORAGE TEMPERATURE - MIN	-40 °C
APPARENT POWER AT 400 V	12.47 kVA
APPARENT POWER AT 480 V	14.96 kVA
APPLICATION IN INDUSTRIAL AREA PERMITTED	Yes
HEAT DISSIPATION DETAILS	Operation (with 150 % overload)

PRODUCT CATEGORY	Variable frequency drives
PROTECTION	Finger and back-of-hand proof, Protection against direct contact (BGV A3, VBG4)
RESOLUTION	0.1 Hz (Frequency resolution, setpoint value)
STATIC HEAT DISSIPATION, NON-CURRENT-DEPENDENT PVS	0 W
SWITCH-ON THRESHOLD FOR THE BRAKING TRANSISTOR	780 VDC
VOLTAGE RATING - MAX	480 V
MOUNTING POSITION	Vertical
OVERVOLTAGE CATEGORY	III
COMMUNICATION INTERFACE	SmartWire-DT, optional Modbus RTU, built in OP-Bus (RS485), built in CANopen®, built in
CONVERTER TYPE	U converter
DEGREE OF PROTECTION	IP20 NEMA Other
ASSIGNED MOTOR POWER AT 460/480 V, 60 HZ, 3-PHASE	10 HP
BRAKING RESISTANCE	80 Ω
EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT PVID	300 W
HEAT DISSIPATION CAPACITY PDISS	0 W
HEAT DISSIPATION PER POLE, CURRENT-DEPENDENT PVID	0 W
INPUT CURRENT ILN AT 150% OVERLOAD	21.2 A
MAINS CURRENT DISTORTION	120 %
PROTOCOL	Other bus systems MODBUS CAN EtherNet/IP
OVERLOAD CURRENT IL AT 150% OVERLOAD	27 A
RATED FREQUENCY -	62 Hz

MAX	
RATED FREQUENCY - MIN	48 Hz
RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)	18 A
RATED OPERATIONAL POWER AT 380/400 V, 50 HZ, 3-PHASE	7.5 kW
ASSIGNED MOTOR CURRENT IM AT 400 V, 50 HZ, 150% OVERLOAD	15.2 A
ASSIGNED MOTOR CURRENT IM AT 440 - 480 V, 60 HZ, 150% OVERLOAD	14 A
SYSTEM CONFIGURATION TYPE	AC supply systems with earthed center point
BRAKING CURRENT	≤ 0.6 A (max. 6 A for 120 ms), Actuator for external motor brake
ELECTROMAGNETIC COMPATIBILITY	1st and 2nd environments (according to EN 61800-3)
BRAKING TORQUE	Max. 30 % MN, Standard - Main circuit Max. 100 % of rated operational current I_e , variable, DC - Main circuit Max. 100 % of rated operational current I_e with external braking resistor - Main circuit
CABLE LENGTH	C3 ≤ 25 m, Radio interference level, maximum motor cable length 300 m, unscreened, with motor choke, maximum permissible, Motor feeder 100 m, screened, maximum permissible, Motor feeder 200 m, screened, with motor choke, maximum permissible, Motor feeder 150 m, unscreened, maximum permissible, Motor feeder C2 ≤ 5 m, Radio interference level, maximum motor cable length
FUNCTIONS	4-quadrant operation

	possible
OUTPUT VOLTAGE (U2)	480 V AC, 3-phase 400 V AC, 3-phase
DELAY TIME	< 10 ms, On-delay < 10 ms, Off-delay
NUMBER OF INPUTS (ANALOG)	2 (parameterizable, 0 - 10 V DC, 0/4 - 20 mA)
NUMBER OF INPUTS (DIGITAL)	4 (parameterizable, 10 - 30 V DC)
RADIO INTERFERENCE CLASS	C2, C3: depending on the motor cable length, the connected load, and ambient conditions. External radio interference suppression filters (optional) may be necessary. Optional external radio interference suppression filter for longer motor cable lengths and for use in different EMC environments
NUMBER OF OUTPUTS (DIGITAL)	1
STARTING CURRENT - MAX	175 %, I _H , max. starting current (High Overload), For 2.5 seconds every 600 seconds, Power section
NUMBER OF PHASES (INPUT)	3
NUMBER OF RELAY OUTPUTS	1 (parameterizable, N/O, 6 A (250 V, AC-1) / 5 A (30 V, DC-1))
NUMBER OF PHASES (OUTPUT)	3
POWER CONSUMPTION	300W
RATED CONTROL SUPPLY VOLTAGE	10 V DC (U _s , max. 10 mA)
EFFICIENCY	97 % (η)
SUPPLY FREQUENCY	50/60 Hz
LEAKAGE CURRENT AT GROUND IPE - MAX	12.7 mA
MAINS VOLTAGE - MIN	380 V
NOMINAL OUTPUT CURRENT I_{2N}	18 A
NUMBER OF HW-INTERFACES (INDUSTRIAL ETHERNET)	0

NUMBER OF HW-INTERFACES (OTHER)	0
NUMBER OF HW-INTERFACES (PARALLEL)	0
NUMBER OF HW-INTERFACES (RS-232)	0
NUMBER OF HW-INTERFACES (RS-422)	0
NUMBER OF HW-INTERFACES (RS-485)	1
NUMBER OF HW-INTERFACES (SERIAL TTY)	0
NUMBER OF HW-INTERFACES (USB)	0
NUMBER OF INTERFACES (PROFINET)	0
NUMBER OF OUTPUTS (ANALOG)	1
OUTPUT AT LINEAR LOAD AT RATED OUTPUT VOLTAGE - MAX	7.5 kW
OUTPUT AT QUADRATIC LOAD AT RATED OUTPUT VOLTAGE - MAX	7.5 kW
OUTPUT FREQUENCY - MAX	500 Hz
OUTPUT FREQUENCY - MIN	0 Hz
SHORT-CIRCUIT PROTECTION (EXTERNAL OUTPUT CIRCUITS)	Type 1 coordination via the power bus' feeder unit, Main circuit
SUITABLE FOR	Branch circuits, (UL/CSA)
SWITCHING FREQUENCY	8 kHz, 4 - 24 kHz adjustable (audible), fPWM, Power section, Main circuit
RATED OPERATIONAL CURRENT (IE)	18 A at 150% overload (at an operating frequency of 16 kHz and an ambient air temperature of +50 °C)
RATED OPERATIONAL VOLTAGE	400 V AC, 3-phase 480 V AC, 3-phase
SHORT-CIRCUIT PROTECTION RATING	25 A, UL (Class CC or J), Safety device (fuse or miniature circuit-breaker), Power Wiring
HEAT DISSIPATION AT CURRENT/SPEED	105 W at 50% current and 0% speed 111 W at 50% current and

50% speed
118 W at 50% current and
90% speed
167 W at 100% current
and 0% speed
194 W at 100% current
and 50% speed
209 W at 100% current
and 90% speed
64 W at 25% current and
0% speed
84 W at 25% current and
50% speed

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

