



## Eaton 186909

Eaton Moeller® series ZFS Clamp with label,  
For use with T0, T3, P1, 48 x 17 mm,  
Inscribed with "Supply disconnecting device"  
(IEC/EN 60204), Language Etonian

□□□□

<b>PRODUCT NAME</b>	Eaton Moeller® series ZFS Accessory Clamp with label
<b>CATALOG NUMBER</b>	186909
<b>PRODUCT LENGTH/DEPTH</b>	48 mm
<b>PRODUCT HEIGHT</b>	3 mm
<b>PRODUCT WIDTH</b>	17 mm
<b>PRODUCT WEIGHT</b>	1 g
<b>COMPLIANCES</b>	CE



Powering Business Worldwide

<b>USED WITH</b>	For mechanisms with padlocking feature
<b>TYPE</b>	Front plates
<b>10.10 TEMPERATURE RISE</b>	Not applicable.
<b>10.11 SHORT-CIRCUIT RATING</b>	Not applicable.
<b>10.12 ELECTROMAGNETIC COMPATIBILITY</b>	Not applicable.
<b>10.13 MECHANICAL FUNCTION</b>	Not applicable.
<b>10.2.2 CORROSION RESISTANCE</b>	Meets the product standard's requirements.
<b>10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES</b>	Meets the product standard's requirements.
<b>10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT</b>	Meets the product standard's requirements.
<b>10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS</b>	Meets the product standard's requirements.
<b>10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION</b>	Meets the product standard's requirements.
<b>10.2.5 LIFTING</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.2.6 MECHANICAL IMPACT</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.2.7 INSCRIPTIONS</b>	Meets the product standard's requirements.
<b>10.3 DEGREE OF PROTECTION OF ASSEMBLIES</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.4 CLEARANCES AND CREEPAGE DISTANCES</b>	Meets the product standard's requirements.
<b>10.5 PROTECTION AGAINST ELECTRIC SHOCK</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS</b>	Is the panel builder's responsibility.
<b>10.8 CONNECTIONS FOR</b>	Is the panel builder's

<b>EXTERNAL CONDUCTORS</b>	responsibility.
<b>10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH</b>	Is the panel builder's responsibility.
<b>10.9.3 IMPULSE WITHSTAND VOLTAGE</b>	Is the panel builder's responsibility.
<b>10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL</b>	Is the panel builder's responsibility.
<b>FITTED WITH:</b>	Label mount Insert label
<b>ACCESSORY/SPARE PART TYPE</b>	Device labeling system
<b>AMBIENT OPERATING TEMPERATURE - MAX</b>	50 °C
<b>AMBIENT OPERATING TEMPERATURE - MIN</b>	-25 °C
<b>EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT PVID</b>	0 W
<b>HEAT DISSIPATION CAPACITY PDISS</b>	0 W
<b>HEAT DISSIPATION PER POLE, CURRENT-DEPENDENT PVID</b>	0 W
<b>RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)</b>	0 A
<b>STATIC HEAT DISSIPATION, NON-CURRENT-DEPENDENT PVS</b>	0 W
<b>LANGUAGE</b>	Etonian
<b>CONNECTION TYPE</b>	Plug-in
<b>FUNCTIONS</b>	Add-on front plates
<b>INSCRIPTION</b>	Supply disconnecting device

