



□□□□

## Eaton 187023

Eaton Moeller® series M30 Illuminated selector switch actuator, RMQ-Titan, With thumb-grip, maintained, 2 positions, Blue, Metal bezel

□□□□

<b>PRODUCT NAME</b>	Eaton Moeller® series M30 illuminated selector switch
<b>CATALOG NUMBER</b>	187023
<b>PRODUCT LENGTH/DEPTH</b>	36 mm
<b>PRODUCT HEIGHT</b>	47 mm
<b>PRODUCT WIDTH</b>	46 mm
<b>PRODUCT WEIGHT</b>	0.042 kg
<b>CERTIFICATIONS</b>	VDE 0660 IEC/EN 60947



Powering Business Worldwide

<b>TYPE</b>	Illuminated selector switch actuator
<b>ACTUATOR COLOR</b>	Blue
<b>ACTUATOR FUNCTION</b>	Maintained Switching function latching
<b>10.10 TEMPERATURE RISE</b>	Not applicable.
<b>10.11 SHORT-CIRCUIT RATING</b>	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
<b>10.12 ELECTROMAGNETIC COMPATIBILITY</b>	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
<b>10.13 MECHANICAL FUNCTION</b>	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
<b>10.2.2 CORROSION RESISTANCE</b>	Meets the product standard's requirements.
<b>10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES</b>	Meets the product standard's requirements.
<b>10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT</b>	Meets the product standard's requirements.
<b>10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS</b>	Meets the product standard's requirements.
<b>10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION</b>	Please enquire
<b>10.2.5 LIFTING</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.2.6 MECHANICAL IMPACT</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.2.7 INSCRIPTIONS</b>	Meets the product standard's requirements.
<b>10.3 DEGREE OF PROTECTION OF ASSEMBLIES</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.4 CLEARANCES AND CREEPAGE DISTANCES</b>	Meets the product standard's requirements.

[eaton-operating-m30-dimensions-005.eps](#)

[eaton-operating-m30-dimensions-006.eps](#)

□□

[eaton-operating-m30-dimensions-004.eps](#)

[eaton-operating-m30-dimensions-002.eps](#)

[eaton-operating-3d-drawing-008.eps](#)

<b>10.5 PROTECTION AGAINST ELECTRIC SHOCK</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS</b>	Is the panel builder's responsibility.
<b>10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS</b>	Is the panel builder's responsibility.
<b>10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH</b>	Is the panel builder's responsibility.
<b>10.9.3 IMPULSE WITHSTAND VOLTAGE</b>	Is the panel builder's responsibility.
<b>10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL</b>	Is the panel builder's responsibility.
<b>FITTED WITH:</b>	Front ring
<b>OPERATING FREQUENCY</b>	2000 Operations/h
<b>POLLUTION DEGREE</b>	3
<b>CLIMATIC PROOFING</b>	Damp heat, cyclic, to IEC 60068-2-30 Damp heat, constant, to IEC 60068-2-78
<b>CONNECTION TO SMARTWIRE-DT</b>	Yes With SWD-RMQ connections
<b>ACTUATOR TYPE</b>	Toggle
<b>AMBIENT OPERATING TEMPERATURE - MAX</b>	70 °C
<b>AMBIENT OPERATING TEMPERATURE - MIN</b>	-25 °C
<b>EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT PVID</b>	0 W
<b>FORCE FOR POSITIVE OPENING - MIN</b>	0 N
<b>HEAT DISSIPATION CAPACITY PDISS</b>	0 W
<b>HEAT DISSIPATION PER POLE, CURRENT-DEPENDENT PVID</b>	0 W
<b>OPENING DIAMETER</b>	30 mm
<b>OPERATING TORQUE</b>	0.3 Nm
<b>RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)</b>	0 A
<b>STATIC HEAT DISSIPATION, NON-</b>	0 W

