



Eaton 183472

Eaton Moeller series IZMX/INX - ACB. Circuit-breaker, 3p, 1250A, 42 kA, P measurement, IEC, Withdrawable

□□□□

PRODUCT NAME	Eaton Moeller series IZMX/INX circuit-breaker
CATALOG NUMBER	183472
PRODUCT LENGTH/DEPTH	584 mm
PRODUCT HEIGHT	597 mm
PRODUCT WIDTH	521 mm
PRODUCT WEIGHT	27.74 kg
COMPLIANCES	IEC/EN 60947 IEC RoHS conform

USED WITH	Air circuit breakers/switch-disconnector Open circuit breaker
AMPERAGE RATING	1250 A
FEATURES	Motor drive optional Complete device with protection unit
10.10 TEMPERATURE RISE	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 SHORT-CIRCUIT RATING	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 ELECTROMAGNETIC COMPATIBILITY	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 MECHANICAL FUNCTION	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.
10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	Meets the product standard's requirements.
10.2.5 LIFTING	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 MECHANICAL IMPACT	Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 INSCRIPTIONS	Meets the product

[eaton-circuit-breaker-izmx-inx-mccb-dimensions-012.eps](#)

[eaton-circuit-breaker-mounting-izmx-inx-mccb-dimensions-002.eps](#)

[eaton-circuit-breaker-mounting-izmx-inx-mccb-dimensions.eps](#)

[eaton-circuit-breaker-izmx-inx-rating-plug-3d-drawing-002.eps](#)

	standard's requirements.
10.3 DEGREE OF PROTECTION OF ASSEMBLIES	Does not apply, since the entire switchgear needs to be evaluated.
10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
FITTED WITH:	Switched-off indicator
FRAME	IZMX16
POLLUTION DEGREE	3
RATED UNINTERRUPTED CURRENT (IU)	1250 A
MOUNTING METHOD	Withdrawable
EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT	180 W
RATED IMPULSE WITHSTAND VOLTAGE (UIMP)	12 kV AC
UTILIZATION CATEGORY	B
DEVICE CONSTRUCTION	Built-in device slide-in technique (withdrawable)
DIRECTION OF INCOMING SUPPLY	As required
ELECTRICAL CONNECTION TYPE OF MAIN CIRCUIT	Rail connection
ACTUATOR TYPE	Push button
SHORT-CIRCUIT RELEASE NON-DELAYED SETTING	1.5 - 10 x I _r
ADJUSTMENT RANGE SHORT-TERM DELAYED	12500 A

SHORT-CIRCUIT RELEASE - MAX	
ADJUSTMENT RANGE SHORT-TERM DELAYED SHORT-CIRCUIT RELEASE - MIN	750 A
ADJUSTMENT RANGE UNDELAYED SHORT- CIRCUIT RELEASE - MAX	18750 A
ADJUSTMENT RANGE UNDELAYED SHORT- CIRCUIT RELEASE - MIN	2500 A
AMBIENT OPERATING TEMPERATURE - MAX	70 °C
AMBIENT OPERATING TEMPERATURE - MIN	-20 °C
AMBIENT STORAGE TEMPERATURE - MAX	70 °C
AMBIENT STORAGE TEMPERATURE - MIN	-20 °C
NUMBER OF AUXILIARY CONTACTS (CHANGE- OVER CONTACTS)	2
NUMBER OF AUXILIARY CONTACTS (NORMALLY CLOSED CONTACTS)	0
NUMBER OF AUXILIARY CONTACTS (NORMALLY OPEN CONTACTS)	0
NUMBER OF STANDARD MECHANICAL OPERATIONS PER HOUR - MAX	60
OPERATING SEQUENCE UP TO 690 V, 50/60 HZ (IEC/EN 60947)	42 kA
OVERLOAD RELEASE CURRENT SETTING - MAX	1250 A
OVERLOAD RELEASE CURRENT SETTING - MIN	500 A
POWER OF WITHDRAWABLE SWITCH WITH CASSETTE	180 W
RATED INSULATION VOLTAGE (UI)	1000 V
LIFESPAN, MECHANICAL	25000 operations (switching capacity, with maintenance) 12500 switching cycles (ON/OFF)
OVERVOLTAGE CATEGORY	III

SHORT-CIRCUIT RELEASE NON-DELAYED SETTING - MIN	0 A
WEIGHT OF CASSETTE VERSION (3-POLE)	18 kg
WEIGHT OF FIXED WITHDRAWABLE VERSION (3-POLE)	28 kg
AMBIENT OPERATING TEMPERATURE DETAILS	-20 °C - 70 °C
PROTECTION	P measurement
VOLTAGE RATING AT AC	690 V AC
SHORT-CIRCUIT RELEASE NON-DELAYED SETTING - MAX	18750 A
SHORT-CIRCUIT RELEASE DELAYED SETTING - MAX	12500 A
NUMBER OF POLES	Three-pole
DEGREE OF PROTECTION	IP31 IP31 with door seals IP55 with protective cover
CLOSING DELAY VIA SPRING RELEASE	30 ms
LIFESPAN, ELECTRICAL	20000 operations (switching cycles ON/OFF, with maintenance) 10000 operations (switching capacity)
TYPE	• Air circuit breakers/switch-disconnector • Open circuit breaker
SPECIAL FEATURES	• Cassette must be separately ordered. • External IZMX-DTP-PTM-1 voltage measuring module required (1 module is suitable for 16 circuit breakers) • IZMX-DTP-PTM external voltage measuring module required • suitable for zone selectivity • suitable for communication • with integrated system monitor

- with integrated test possibility
- With graphic LCD display
- optionally fittable by user with comprehensive accessories
- Terminal capacity
hint: These are values used in separate switchgear. The actual values will depend on the temperature around the circuit breaker, which is influenced by the ambient temperature, the degree of protection (IP), the mounting height, the partitions, and any external ventilation. Depending on the specific switchgear design, this may result in derating, which can then be compensated for by increasing the cross-sectional area. Temperature rise tests in the specific switchgear can provide specific and detailed information.

**POSITION OF
CONNECTION FOR MAIN
CURRENT CIRCUIT**

Back side

RELEASE SYSTEM

Electronic release

**RATED OPERATING
VOLTAGE (UE) - MAX**

690 V

**RATED OPERATING
VOLTAGE (UE) - MIN**

690 V

**RATED OPERATIONAL
CURRENT FOR SPECIFIED
HEAT DISSIPATION (IN)**

1250 A

**RATED SHORT-CIRCUIT
BREAKING CAPACITY AT
400 V, 50 HZ**

42 kA

RATED SHORT-CIRCUIT MAKING CAPACITY UP TO 440 V, 50/60 HZ	88 kA
RATED SHORT-CIRCUIT MAKING CAPACITY UP TO 690 V, 50/60 HZ	88 kA
RATED SHORT-TIME WITHSTAND CURRENT (T = 1 S)	42 kA
RATED UNINTERRUPTED CURRENT (IU) AT 50°C	1250 A
RATED UNINTERRUPTED CURRENT (IU) AT 60°C	1250 A
RATED UNINTERRUPTED CURRENT (IU) AT 70°C	1250 A
SHORT-CIRCUIT RELEASE DELAYED SETTING - MIN	937.5 A
TERMINAL CAPACITY (COPPER BAR)	5 mm x 80 mm (2x) for withdrawable units (black)
POWER LOSS	180 W

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY: