

Eaton 183793

Eaton Moeller series IZMX/INX - ACB. Circuit-breaker, 4 pole, 3200A, 85 kA, P measurement, IEC, Withdrawable

PRODUCT NAME	Eaton Moeller series IZMX/INX circuit-breaker
CATALOG NUMBER	183793
PRODUCT LENGTH/DEPTH	584 mm
PRODUCT HEIGHT	597 mm
PRODUCT WIDTH	521 mm
PRODUCT WEIGHT	86 kg
COMPLIANCES	IEC IEC/EN 60947 RoHS conform

USED WITH	Air circuit breakers/switch-disconnector Open circuit breaker
AMPERAGE RATING	3200 A
FEATURES	Motor drive optional Complete device with protection unit
10.10 TEMPERATURE RISE	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 SHORT-CIRCUIT RATING	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 ELECTROMAGNETIC COMPATIBILITY	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 MECHANICAL FUNCTION	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.
10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	Meets the product standard's requirements.
10.2.5 LIFTING	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 MECHANICAL	Does not apply, since the

eaton-circuit-breaker-izmx-inx-mccb-dimensions-015.eps
eaton-circuit-breaker-mounting-izmx-inx-mccb-dimensions-002.eps
eaton-circuit-breaker-mounting-izmx-inx-mccb-dimensions.eps
eaton-circuit-breaker-izmx-inx-mccb-dimensions-014.eps

IMPACT	entire switchgear needs to be evaluated.
10.2.7 INSCRIPTIONS	Meets the product standard's requirements.
10.3 DEGREE OF PROTECTION OF ASSEMBLIES	Does not apply, since the entire switchgear needs to be evaluated.
10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
FITTED WITH:	Switched-off indicator
FRAME	IZMX40
POLLUTION DEGREE	3
RATED UNINTERRUPTED CURRENT (IU)	3200 A
MOUNTING METHOD	Withdrawable
EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT	560 W
RATED IMPULSE WITHSTAND VOLTAGE (UIMP)	12 kV AC
UTILIZATION CATEGORY	B
DEVICE CONSTRUCTION	Built-in device slide-in technique (withdrawable)
DIRECTION OF INCOMING SUPPLY	As required
ELECTRICAL CONNECTION TYPE OF MAIN CIRCUIT	Rail connection

ACTUATOR TYPE	Push button
SHORT-CIRCUIT RELEASE NON-DELAYED SETTING	1.5 - 10 x I _r
ADJUSTMENT RANGE SHORT-TERM DELAYED SHORT-CIRCUIT RELEASE - MAX	32000 A
ADJUSTMENT RANGE SHORT-TERM DELAYED SHORT-CIRCUIT RELEASE - MIN	1920 A
ADJUSTMENT RANGE UNDELAYED SHORT- CIRCUIT RELEASE - MAX	48000 A
ADJUSTMENT RANGE UNDELAYED SHORT- CIRCUIT RELEASE - MIN	6400 A
AMBIENT OPERATING TEMPERATURE - MAX	70 °C
AMBIENT OPERATING TEMPERATURE - MIN	-20 °C
AMBIENT STORAGE TEMPERATURE - MAX	70 °C
AMBIENT STORAGE TEMPERATURE - MIN	-20 °C
NUMBER OF AUXILIARY CONTACTS (CHANGE- OVER CONTACTS)	2
NUMBER OF AUXILIARY CONTACTS (NORMALLY CLOSED CONTACTS)	0
NUMBER OF AUXILIARY CONTACTS (NORMALLY OPEN CONTACTS)	0
NUMBER OF STANDARD MECHANICAL OPERATIONS PER HOUR - MAX	60
OPERATING SEQUENCE UP TO 690 V, 50/60 HZ (IEC/EN 60947)	75 kA
OVERLOAD RELEASE CURRENT SETTING - MAX	3200 A
OVERLOAD RELEASE CURRENT SETTING - MIN	1280 A
POWER OF WITHDRAWABLE SWITCH WITH CASSETTE	560 W
RATED INSULATION	1000 V

VOLTAGE (UI)	
LIFESPAN, MECHANICAL	10000 switching cycles (ON/OFF) 20000 operations (switching capacity, with maintenance)
OVERVOLTAGE CATEGORY	III
SHORT-CIRCUIT RELEASE NON-DELAYED SETTING - MIN	0 A
WEIGHT OF CASSETTE VERSION (4-POLE)	35 kg
WEIGHT OF FIXED WITHDRAWABLE VERSION (4-POLE)	86 kg
AMBIENT OPERATING TEMPERATURE DETAILS	-20 °C - 70 °C
PROTECTION	P measurement
VOLTAGE RATING AT AC	690 V AC
SHORT-CIRCUIT RELEASE NON-DELAYED SETTING - MAX	48000 A
SHORT-CIRCUIT RELEASE DELAYED SETTING - MAX	32000 A
NUMBER OF POLES	Four-pole
DEGREE OF PROTECTION	IP31 with door seals IP55 with protective cover IP31
CLOSING DELAY VIA SPRING RELEASE	35 ms
LIFESPAN, ELECTRICAL	10000 operations (switching cycles ON/OFF, with maintenance) 5000 operations (switching capacity)
TYPE	<ul style="list-style-type: none"> • Air circuit breakers/switch-disconnector • Open circuit breaker
SPECIAL FEATURES	<ul style="list-style-type: none"> • Cassette must be separately ordered. • External IZMX-DTP-PTM-1 voltage measuring module required (1 module

is suitable for 16
circuit breakers)

- IZMX-DTP-PTM
external voltage
measuring module
required
- suitable for zone
selectivity
- suitable for
communication
- with integrated
system monitor
- with integrated test
possibility
- With graphic LCD
display
- optionally fittable
by user with
comprehensive
accessories
- Terminal capacity
hint: These are
values used in
separate
switchgear. The
actual values will
depend on the
temperature
around the circuit
breaker, which is
influenced by the
ambient
temperature, the
degree of
protection (IP), the
mounting height,
the partitions, and
any external
ventilation.
Depending on the
specific switchgear
design, this may
result in derating,
which can then be
compensated for
by increasing the
cross-sectional
area. Temperature
rise tests in the
specific switchgear
can provide specific
and detailed
information.

CURRENT CIRCUIT	
RELEASE SYSTEM	Electronic release
RATED OPERATING VOLTAGE (UE) - MAX	690 V
RATED OPERATING VOLTAGE (UE) - MIN	690 V
RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)	3200 A
RATED SHORT-CIRCUIT BREAKING CAPACITY AT 400 V, 50 HZ	85 kA
RATED SHORT-CIRCUIT MAKING CAPACITY UP TO 440 V, 50/60 HZ	187 kA
RATED SHORT-CIRCUIT MAKING CAPACITY UP TO 690 V, 50/60 HZ	166 kA
RATED SHORT-TIME WITHSTAND CURRENT (T = 1 S)	85 kA
RATED SHORT-TIME WITHSTAND CURRENT AT 50/60 HZ (T = 3 S)	66 kA
RATED UNINTERRUPTED CURRENT (IU) AT 50°C	3200 A
RATED UNINTERRUPTED CURRENT (IU) AT 60°C	3200 A
RATED UNINTERRUPTED CURRENT (IU) AT 70°C	3200 A
SHORT-CIRCUIT RELEASE DELAYED SETTING - MIN	2400 A
TERMINAL CAPACITY (COPPER BAR)	80 mm x 10 mm (3x) for withdrawable units (black)
POWER LOSS	560 W

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
: