



Eaton 184126

Eaton Moeller series IZMX/INX - ACB. Eaton Moeller series IZMX/INX - ACB. Reset remote, 110-125VAC/DC, EMEA

□□□□

PRODUCT NAME	Eaton Moeller series IZMX/INX remote reset
CATALOG NUMBER	184126
PRODUCT LENGTH/DEPTH	150 mm
PRODUCT HEIGHT	100 mm
PRODUCT WIDTH	100 mm
PRODUCT WEIGHT	0.125 kg
COMPLIANCES	RoHS conform



Powering Business Worldwide

□□□□

USED WITH	IZMX40...F IZMX40...W
ELECTRIC CONNECTION TYPE	Flat plug-in connection
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 50 HZ - MAX	127 V
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 50 HZ - MIN	110 V
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 60 HZ - MAX	127 V
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 60 HZ - MIN	110 V
RATED CONTROL SUPPLY VOLTAGE (US) AT DC - MAX	125 V
RATED CONTROL SUPPLY VOLTAGE (US) AT DC - MIN	110 V
ACCESSORY/SPARE PART TYPE	Trip indication / Reset options
ADJUSTMENT RANGE UNDELAYED SHORT-CIRCUIT RELEASE (END VALUE) - MAX	0 A
AMBIENT OPERATING TEMPERATURE - MAX	70 °C
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
INITIAL VALUE OF THE UNDELAYED SHORT-CIRCUIT RELEASE - MIN	0 A
NUMBER OF CONTACTS (CHANGE-OVER CONTACTS)	0
NUMBER OF CONTACTS (NORMALLY CLOSED CONTACTS)	0
NUMBER OF CONTACTS (NORMALLY OPEN CONTACTS)	0
VOLTAGE TYPE	AC/DC
CONTROL VOLTAGE OPERATING RANGE	110 - 125 V DC 110 - 127 V AC (50/60 Hz)
TYPE	Accessory

□□

□□□□□

[eaton-izmx16-izmx40-pop-out-trip-indicators-il0131126en-us.pdf](#)

SPECIAL FEATURES

- The circuit-breaker is equipped with a mechanical trip indicator (red pin).
- After the remote reset coil is electrically actuated, the reclosing lockout can be reset.
- Cannot be combined with remote reset.
- The retrofit kit includes the required SEC control cable terminals.

POWER CONSUMPTION 540 VA/W AC/DC

SUITABLE FOR Power circuit breaker
Overload relay
Off-load switch

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

□□:



□□□□
Eaton House
30 Pembroke Road
Dublin 4, □□□
Eaton.com

© 2025 □□ □□□□□□

Follow us on social media to get the latest product and support information.

