

Eaton 184255

Eaton Moeller series IZMX/INX - ACB. Motor operator 24 VDC, 40, +

PRODUCT NAME	Eaton Moeller series IZMX/INX motor operator
CATALOG NUMBER	184255
PRODUCT LENGTH/DEPTH	200 mm
PRODUCT HEIGHT	100 mm
PRODUCT WIDTH	150 mm
PRODUCT WEIGHT	1.25 kg
COMPLIANCES	RoHS conform



USED WITH	IZMX40... INX40...
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 50 HZ - MAX	0 V
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 50 HZ - MIN	0 V
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 60 HZ - MAX	0 V
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 60 HZ - MIN	0 V
RATED CONTROL SUPPLY VOLTAGE (US) AT DC - MAX	24 V
RATED CONTROL SUPPLY VOLTAGE (US) AT DC - MIN	24 V
ACCESSORY/SPARE PART TYPE	Remote switching
STARTING CURRENT RATING	25 A DC
SWITCH DRIVE TYPE	Motor drive
AMBIENT OPERATING TEMPERATURE - MAX	70 °C
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
NUMBER OF ACTUATION PER MINUTE - MAX	3
VOLTAGE TYPE	DC
CONTROL VOLTAGE OPERATING RANGE	24 V DC 0.85 - 1.1 x Us
TYPE	Accessory

SPECIAL FEATURES	• Signalling switch for “Spring-operated stored energy mechanism tensioned” message is included as standard. • Switching frequency = 60/h • The motor automatically
------------------	---



eaton-izmx16-40-spring-release-latch-check-il0131088en-us.pdf
eaton-circuit-breaker-izmx-inx-motor-operator-3d-drawing-002.eps

tensions the spring
force storage
mechanism for
remote or local
actuation.

POWER CONSUMPTION	200 W DC
--------------------------	----------

NECESSARY TIME FOR CHARGING SPRING- OPERATED STORED ENERGY MECHANISM AT 1 X US	6 s DC
---	--------

RATED OPERATIONAL CURRENT	7 A DC
--------------------------------------	--------

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the
latest product and support
information.

