

Eaton 184274

Eaton Moeller series IZMX/INX - ACB. Shunt release 220-240 VAC/DC, 1

PRODUCT NAME	Eaton Moeller series IZMX/INX shunt release
CATALOG NUMBER	184274
PRODUCT LENGTH/DEPTH	150 mm
PRODUCT HEIGHT	100 mm
PRODUCT WIDTH	100 mm
PRODUCT WEIGHT	0.113 kg
COMPLIANCES	RoHS conform

USED WITH	IZMX16..., IZMX40... INX16..., INX40...
ELECTRIC CONNECTION TYPE	Flat plug-in connection
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 50 HZ - MAX	240 V
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 50 HZ - MIN	208 V
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 60 HZ - MAX	240 V
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 60 HZ - MIN	208 V
RATED CONTROL SUPPLY VOLTAGE (US) AT DC - MAX	250 V
RATED CONTROL SUPPLY VOLTAGE (US) AT DC - MIN	220 V
ACCESSORY/SPARE PART TYPE	Remote switching
CURRENT RATING - MAX	0.034 A (maximum holding current)
PICK-UP POWER CONSUMPTION AT 35 MS - MAX	500 VA/W
STARTING CURRENT RATING	3.01 A (35 ms)
ADJUSTMENT RANGE UNDELAYED SHORT-CIRCUIT RELEASE (END VALUE) - MAX	0 A
AMBIENT OPERATING TEMPERATURE - MAX	70 °C
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
INITIAL VALUE OF THE UNDELAYED SHORT-CIRCUIT RELEASE - MIN	0 A
NUMBER OF ACTUATION PER MINUTE - MAX	3
NUMBER OF CONTACTS (CHANGE-OVER CONTACTS)	0

eaton-izmx16-izmx40-uvr-st-ots-il0131087en-z.pdf	
eaton-circuit-breaker-izmx-inx-acb-3d-drawing-010.eps	

NUMBER OF CONTACTS (NORMALLY CLOSED CONTACTS)	0
NUMBER OF CONTACTS (NORMALLY OPEN CONTACTS)	0
VOLTAGE TYPE	AC/DC
CIRCUIT BREAKER TOTAL SWITCHING TIME	35 ms (Us = 100%) (IZMX40..., INX40...) 30 ms (Us = 100%) (IZMX16..., INX16...)
CONTROL VOLTAGE OPERATING RANGE	208 - 240 V AC (50/60 Hz) 0.7 - 1.1 x Us 208 - 250 V DC
TYPE	Accessory

SPECIAL FEATURES

- Can be combined with an undervoltage release or a second shunt release.
- Retrofitting kit
- Limited to 3/min due to the high pick-up current for 35 ms.
- Please note - the circuit-breaker's switching frequency = 60/h
- The retrofit kit includes the required SEC control cable terminals.

POWER CONSUMPTION	9 VA/W AC/DC
RATED OPERATIONAL CURRENT	0.034 A (maximum holding current)
SUITABLE FOR	Power circuit breaker Off-load switch Overload relay

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

