

Eaton 184277

Eaton Moeller series IZMX/INX - ACB. Shunt release (2) 60 VDC

PRODUCT NAME	Eaton Moeller series IZMX/INX shunt release
CATALOG NUMBER	184277
PRODUCT LENGTH/DEPTH	150 mm
PRODUCT HEIGHT	100 mm
PRODUCT WIDTH	100 mm
PRODUCT WEIGHT	0.113 kg
COMPLIANCES	RoHS conform

USED WITH	IZMX16..., IZMX40... INX16..., INX40...
ELECTRIC CONNECTION TYPE	Flat plug-in connection
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 50 HZ - MAX	0 V
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 50 HZ - MIN	0 V
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 60 HZ - MAX	0 V
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 60 HZ - MIN	0 V
RATED CONTROL SUPPLY VOLTAGE (US) AT DC - MAX	60 V
RATED CONTROL SUPPLY VOLTAGE (US) AT DC - MIN	60 V
ACCESSORY/SPARE PART TYPE	Remote switching
CURRENT RATING - MAX	0.07 A (maximum holding current)
PICK-UP POWER CONSUMPTION AT 35 MS - MAX	540 VA/W
ADJUSTMENT RANGE UNDELAYED SHORT-CIRCUIT RELEASE (END VALUE) - MAX	0 A
AMBIENT OPERATING TEMPERATURE - MAX	70 °C
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
INITIAL VALUE OF THE UNDELAYED SHORT-CIRCUIT RELEASE - MIN	0 A
NUMBER OF ACTUATION PER MINUTE - MAX	3
NUMBER OF CONTACTS (CHANGE-OVER CONTACTS)	0
NUMBER OF CONTACTS (NORMALLY CLOSED CONTACTS)	0

eaton-izmx16-izmx40-uvr-st-ots-il0131087en-z.pdf	
eaton-circuit-breaker-izmx-inx-acb-3d-drawing-010.eps	

NUMBER OF CONTACTS (NORMALLY OPEN CONTACTS)	0
VOLTAGE TYPE	DC
CIRCUIT BREAKER TOTAL SWITCHING TIME	30 ms (Us = 100%) (IZMX16..., INX16...) 35 ms (Us = 100%) (IZMX40..., INX40...)
CONTROL VOLTAGE OPERATING RANGE	60 V DC 0.7 - 1.1 x Us
TYPE	Accessory
SPECIAL FEATURES	• Limited to 3/min due to the high pick-up current for 35 ms. • Please note - the circuit-breaker's switching frequency = 60/h • Only in combination with a \"first\" shunt release. • Cannot be combined with an undervoltage release."
POWER CONSUMPTION	5 VA/W AC/DC
RATED OPERATIONAL CURRENT	0.07 A (maximum holding current)
SUITABLE FOR	Off-load switch Power circuit breaker

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
: