

Eaton 184286

Eaton Moeller series IZMX/INX - ACB. Closing release 110-125 VAC/DC, +, 1

PRODUCT NAME	Eaton Moeller series IZMX/INX closing release
CATALOG NUMBER	184286
PRODUCT LENGTH/DEPTH	100 mm
PRODUCT HEIGHT	100 mm
PRODUCT WIDTH	100 mm
PRODUCT WEIGHT	0.068 kg
COMPLIANCES	RoHS conform

USED WITH	INX16..., INX40... IZMX16..., IZMX40...
ELECTRIC CONNECTION TYPE	Flat plug-in connection
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 50 HZ - MAX	127 V
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 50 HZ - MIN	110 V
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 60 HZ - MAX	127 V
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 60 HZ - MIN	110 V
RATED CONTROL SUPPLY VOLTAGE (US) AT DC - MAX	125 V
RATED CONTROL SUPPLY VOLTAGE (US) AT DC - MIN	110 V
ACCESSORY/SPARE PART TYPE	Remote switching
PICK-UP POWER CONSUMPTION AT 35 MS - MAX	540 VA/W
ADJUSTMENT RANGE UNDELAYED SHORT-CIRCUIT RELEASE (END VALUE) - MAX	0 A
AMBIENT OPERATING TEMPERATURE - MAX	70 °C
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
INITIAL VALUE OF THE UNDELAYED SHORT-CIRCUIT RELEASE - MIN	0 A
NUMBER OF ACTUATION PER MINUTE - MAX	3
NUMBER OF CONTACTS (CHANGE-OVER CONTACTS)	0
NUMBER OF CONTACTS (NORMALLY CLOSED CONTACTS)	0
NUMBER OF CONTACTS (NORMALLY OPEN)	0

eaton-izmx16-40-spring-release-latch-check-il0131088en-us.pdf
eaton-circuit-breaker-izmx-inx-closing-release-3d-drawing.eps

CONTACTS)	
VOLTAGE TYPE	AC/DC
CIRCUIT BREAKER TOTAL SWITCHING TIME	30 ms (Us = 100%) (IZMX16..., INX16...)
	35 ms (Us = 100%) (IZMX40..., INX40...)
CONTROL VOLTAGE OPERATING RANGE	0.85 - 1.1 x Us
	110 - 127 V AC (50/60 Hz)
	110 - 125 V DC
TYPE	Accessory

SPECIAL FEATURES	• Can be combined with a shunt release and an undervoltage release. • Limited to 3/min due to the high pick-up current for 35 ms. • Please note - the circuit-breaker's switching frequency = 60/h
-------------------------	--

SUITABLE FOR	Off-load switch Power circuit breaker
---------------------	--

PROJECT NAME:	
PROJECT NUMBER:	
PREPARED BY:	
:	