



Eaton 187842

Eaton xEnergy Basic LV systems Low voltage switchgear. Floor standing distribution board with locking rotary lever, for F3A gland plate inserts, W=600mm, H = 1760 mm, D = 300 mm

□□□□

PRODUCT NAME	Eaton xEnergy Basic empty enclosure
CATALOG NUMBER	187842
PRODUCT LENGTH/DEPTH	300 mm
PRODUCT HEIGHT	1760 mm
PRODUCT WIDTH	600 mm
PRODUCT WEIGHT	41 kg
COMPLIANCES	RoHS conform

TYPE	Basic device
FEATURES	EMC-version
10.2.6 MECHANICAL IMPACT	IK08
FITTED WITH:	Door
SURFACE FINISHING	Powder coating With powder coating
DEGREE OF PROTECTION	IK08 (impact resistance) IP30 Other IK08
GRADE MATERIAL	Sheet steel
MATERIAL QUALITY	Other
COLOR	Gray Light gray (RAL 7035)
COVER/DOOR TYPE	Rotary lever
PERMISSIBLE LOAD OF THE MOUNTING PLATE ACCORDING TO IEC 62208 - MAX	0 N
NUMBER OF LOCKS	0
RAL-NUMBER	7035
APPLICATION	Indoor (installation site)
MATERIAL	Steel Sheet steel
MOUNTING METHOD	Floor standing distribution board Detached
FUNCTIONS	Basic device
INSTALLATION TYPE	Floor installation possible
NUMBER OF COVERS/DOORS	1
SUITABLE FOR	Metrical mounting
PERMISSIBLE LOAD OF THE ENCLOSURE ACCORDING TO IEC 62208 - MAX	0 N
PERMISSIBLE LOAD OF THE DOOR(S) ACCORDING TO IEC 62208 - MAX	0 N
THERMAL DISSIPATION (DELTA T = 20 K) ACCORDING TO IEC/TR 60890	0 W
NUMBER OF CONNECTOR HOLES	0

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



 Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

