

## Eaton 185809

Eaton DC1 Variable frequency drive, 230 V AC, 1-phase, 7 A, 1.5 kW, IP20/NEMA 0, Radio interference suppression filter, FS1 DC1-127D0FN-A20CE1

<b>PRODUCT NAME</b>	Eaton DC1 Variable frequency drive
<b>CATALOG NUMBER</b>	185809
<b>PRODUCT LENGTH/DEPTH</b>	124 mm
<b>PRODUCT HEIGHT</b>	184 mm
<b>PRODUCT WIDTH</b>	81 mm
<b>PRODUCT WEIGHT</b>	1.2 kg
<b>CERTIFICATIONS</b>	IEC/EN61800-5 Certified by UL for use in Canada RCM RoHS, ISO 9001 UL 508C EAC Specification for general requirements: IEC/EN 61800-2 UL CUL IEC/EN 61800-3 UkrSEPRO Safety requirements: IEC/EN 61800-5-1 UL Category Control No.: NMMS, NMMS7 UL File No.: E172143 IEC/EN61800-3 UL report applies to both US and Canada CE CSA-C22.2 No. 14
<b>CATALOG NOTES</b>	<ul style="list-style-type: none"><li>• Environmental class: 3C2, 3S2</li><li>• Overload cycle for 60 s every 600 s</li></ul>

<b>FEATURES</b>	Parameterization: drivesConnect Parameterization: drivesConnect mobile (App) Parameterization: Fieldbus
	Parameterization: Keypad
<b>10.10 TEMPERATURE RISE</b>	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
<b>10.11 SHORT-CIRCUIT RATING</b>	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
<b>10.12 ELECTROMAGNETIC COMPATIBILITY</b>	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
<b>10.13 MECHANICAL FUNCTION</b>	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
<b>10.2.2 CORROSION RESISTANCE</b>	Meets the product standard's requirements.
<b>10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES</b>	Meets the product standard's requirements.
<b>10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT</b>	Meets the product standard's requirements.
<b>10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS</b>	Meets the product standard's requirements.
<b>10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION</b>	Meets the product standard's requirements.
<b>10.2.5 LIFTING</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.2.6 MECHANICAL</b>	Does not apply, since the

<b>INSTALLATION VIDEOS</b>	<a href="#">Video PowerXL DA1</a>
	<a href="#">IL04020009Z</a>
	<a href="#">eaton-powerxl-variable-frequency-drives-dc1-da1-brochure-br040001en-en-us.pdf</a>
	<a href="#">eaton-frequency-inverter-dimensions-016.eps</a>
	<a href="#">eaton-frequency-inverter-dimensions-017.eps</a>
	<a href="#">eaton-frequency-inverter-3d-drawing-003.eps</a>
	<a href="#">The OP System Bus - Parameterizing - Control</a>
	<a href="#">How does the internal motor protection work?</a>
	<a href="#">DX-COM-STICK3 Connection</a>

<b>IMPACT</b>	entire switchgear needs to be evaluated.
<b>10.2.7 INSCRIPTIONS</b>	Meets the product standard's requirements.
<b>10.3 DEGREE OF PROTECTION OF ASSEMBLIES</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.4 CLEARANCES AND CREEPAGE DISTANCES</b>	Meets the product standard's requirements.
<b>10.5 PROTECTION AGAINST ELECTRIC SHOCK</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS</b>	Is the panel builder's responsibility.
<b>10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS</b>	Is the panel builder's responsibility.
<b>10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH</b>	Is the panel builder's responsibility.
<b>10.9.3 IMPULSE WITHSTAND VOLTAGE</b>	Is the panel builder's responsibility.
<b>10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL</b>	Is the panel builder's responsibility.
<b>FITTED WITH:</b>	Control unit IGBT inverter 7-digital display assembly Internal DC link Radio interference suppression filter PC connection Additional PCB protection
<b>CLIMATIC PROOFING</b>	< 95 average relative humidity (RH), no condensation, no corrosion
<b>CONNECTION TO SMARTWIRE-DT</b>	Yes In conjunction with DX-NET-SWD3 SmartWire DT module
<b>OPERATING MODE</b>	Sensorless vector control (SLV) Speed control with slip compensation U/f control BLDC motors PM motors

	Synchronous reluctance motors
<b>RATED IMPULSE WITHSTAND VOLTAGE (UIMP)</b>	2000 V
<b>FRAME SIZE</b>	FS1
<b>ALTITUDE</b>	Max. 4000 m Above 1000 m with 1 % derating per 100 m
<b>APPLICATION IN DOMESTIC AND COMMERCIAL AREA PERMITTED</b>	Yes
<b>MAINS SWITCH-ON FREQUENCY</b>	Maximum of one time every 30 seconds
<b>AMBIENT OPERATING TEMPERATURE - MAX</b>	50 °C
<b>AMBIENT OPERATING TEMPERATURE - MIN</b>	-10 °C
<b>MAINS VOLTAGE - MAX</b>	240 V
<b>OUTPUT VOLTAGE - MAX</b>	250 V
<b>RATED OPERATIONAL POWER AT 220/230 V, 50 HZ, 3-PHASE</b>	1.5 kW
<b>RELATIVE SYMMETRIC NET FREQUENCY TOLERANCE</b>	10 %
<b>RELATIVE SYMMETRIC NET VOLTAGE TOLERANCE</b>	10 %
<b>AMBIENT OPERATING TEMPERATURE AT 150% OVERLOAD - MAX</b>	50 °C
<b>AMBIENT OPERATING TEMPERATURE AT 150% OVERLOAD - MIN</b>	-10 °C
<b>AMBIENT STORAGE TEMPERATURE - MAX</b>	60 °C
<b>AMBIENT STORAGE TEMPERATURE - MIN</b>	-40 °C
<b>APPARENT POWER AT 230 V</b>	2.79 kVA
<b>APPARENT POWER AT 240 V</b>	2.91 kVA
<b>APPLICATION IN INDUSTRIAL AREA PERMITTED</b>	Yes
<b>PRODUCT CATEGORY</b>	Variable frequency drives

<b>PROTECTION</b>	Finger and back-of-hand proof, Protection against direct contact (BGV A3, VBG4)
<b>RESOLUTION</b>	0.1 Hz (Frequency resolution, setpoint value)
<b>STATIC HEAT DISSIPATION, NON-CURRENT-DEPENDENT PVS</b>	0 W
<b>VOLTAGE RATING - MAX</b>	240 V
<b>MOUNTING POSITION</b>	Vertical
<b>OVERVOLTAGE CATEGORY</b>	III
<b>COMMUNICATION INTERFACE</b>	SmartWire-DT, optional CANopen®, built in Modbus RTU, built in OP-Bus (RS485), built in
<b>CONVERTER TYPE</b>	U converter
<b>DEGREE OF PROTECTION</b>	IP20 NEMA Other
<b>ASSIGNED MOTOR POWER AT 220/230 V, 60 HZ, 3-PHASE</b>	2 HP
<b>EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT PVID</b>	63 W
<b>HEAT DISSIPATION CAPACITY PDISS</b>	0 W
<b>HEAT DISSIPATION PER POLE, CURRENT-DEPENDENT PVID</b>	0 W
<b>INPUT CURRENT ILN AT 150% OVERLOAD</b>	12.9 A
<b>MAINS CURRENT DISTORTION</b>	120 %
<b>ASSIGNED MOTOR CURRENT IM AT 220 - 240 V, 60 HZ, 150% OVERLOAD</b>	6.8 A
<b>ASSIGNED MOTOR CURRENT IM AT 230 V, 50 HZ, 150% OVERLOAD</b>	6.3 A
<b>PROTOCOL</b>	Other bus systems CAN EtherNet/IP MODBUS
<b>OVERLOAD CURRENT IL AT 150% OVERLOAD</b>	10.5 A

<b>RATED FREQUENCY - MAX</b>	62 Hz
<b>RATED FREQUENCY - MIN</b>	48 Hz
<b>RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)</b>	7 A
<b>SYSTEM CONFIGURATION TYPE</b>	AC supply systems with earthed center point
<b>BRAKING CURRENT</b>	$\leq 0.6$ A (max. 6 A for 120 ms), Actuator for external motor brake
<b>ELECTROMAGNETIC COMPATIBILITY</b>	1st and 2nd environments (according to EN 61800-3)
<b>BRAKING TORQUE</b>	Max. 100 % of rated operational current $I_e$ , variable, DC - Main circuit Max. 30 % MN, Standard - Main circuit
<b>CABLE LENGTH</b>	50 m, screened, maximum permissible, Motor feeder 100 m, screened, with motor choke, maximum permissible, Motor feeder C2 $\leq 5$ m, Radio interference level, maximum motor cable length C3 $\leq 25$ m, Radio interference level, maximum motor cable length 75 m, unscreened, maximum permissible, Motor feeder 150 m, unscreened, with motor choke, maximum permissible, Motor feeder C1 $\leq 1$ m, Radio interference level, maximum motor cable length
<b>OUTPUT VOLTAGE (U2)</b>	230 V AC, 3-phase 240 V AC, 3-phase
<b>DELAY TIME</b>	< 10 ms, On-delay < 10 ms, Off-delay
<b>NUMBER OF INPUTS (ANALOG)</b>	2 (parameterizable, 0 - 10 V DC, 0/4 - 20 mA)
<b>NUMBER OF INPUTS (DIGITAL)</b>	4 (parameterizable, 10 - 30 V DC)
<b>RADIO INTERFERENCE CLASS</b>	C2, C3: depending on the motor cable length, the connected load, and

	<p>ambient conditions.</p> <p>External radio interference suppression filters (optional) may be necessary.</p> <p>C1: for conducted emissions only</p> <p>Optional external radio interference suppression filter for longer motor cable lengths and for use in different EMC environments</p>
<b>NUMBER OF OUTPUTS (DIGITAL)</b>	1
<b>STARTING CURRENT - MAX</b>	175 %, IH, max. starting current (High Overload), For 2.5 seconds every 600 seconds, Power section
<b>NUMBER OF PHASES (INPUT)</b>	1
<b>NUMBER OF RELAY OUTPUTS</b>	1 (parameterizable, N/O, 6 A (250 V, AC-1) / 5 A (30 V, DC-1))
<b>NUMBER OF PHASES (OUTPUT)</b>	3
<b>POWER CONSUMPTION</b>	63 W
<b>RATED CONTROL SUPPLY VOLTAGE</b>	10 V DC (Us, max. 10 mA)
<b>EFFICIENCY</b>	95.8 % ( $\eta$ )
<b>SUPPLY FREQUENCY</b>	50/60 Hz
<b>LEAKAGE CURRENT AT GROUND IPE - MAX</b>	4.8 mA
<b>MAINS VOLTAGE - MIN</b>	200 V
<b>NOMINAL OUTPUT CURRENT I2N</b>	7 A
<b>NUMBER OF HW-INTERFACES (INDUSTRIAL ETHERNET)</b>	0
<b>NUMBER OF HW-INTERFACES (OTHER)</b>	0
<b>NUMBER OF HW-INTERFACES (PARALLEL)</b>	0
<b>NUMBER OF HW-INTERFACES (RS-232)</b>	0
<b>NUMBER OF HW-INTERFACES (RS-422)</b>	0
<b>NUMBER OF HW-INTERFACES (RS-485)</b>	1

<b>NUMBER OF HW-INTERFACES (SERIAL TTY)</b>	0
<b>NUMBER OF HW-INTERFACES (USB)</b>	0
<b>NUMBER OF INTERFACES (PROFINET)</b>	0
<b>NUMBER OF OUTPUTS (ANALOG)</b>	1
<b>OUTPUT AT LINEAR LOAD AT RATED OUTPUT VOLTAGE - MAX</b>	1.5 kW
<b>OUTPUT AT QUADRATIC LOAD AT RATED OUTPUT VOLTAGE - MAX</b>	1.5 kW
<b>OUTPUT FREQUENCY - MAX</b>	500 Hz
<b>OUTPUT FREQUENCY - MIN</b>	0 Hz
<b>SHORT-CIRCUIT PROTECTION (EXTERNAL OUTPUT CIRCUITS)</b>	Type 1 coordination via the power bus' feeder unit, Main circuit
<b>SUITABLE FOR</b>	Branch circuits, (UL/CSA)
<b>SWITCHING FREQUENCY</b>	8 kHz, 4 - 32 kHz adjustable (audible), fPWM, Power section, Main circuit
<b>RATED OPERATIONAL CURRENT (IE)</b>	7 A at 150% overload (at an operating frequency of 16 kHz and an ambient air temperature of +50 °C)
<b>RATED OPERATIONAL VOLTAGE</b>	240 V AC, 1-phase 230 V AC, 1-phase
<b>SHORT-CIRCUIT PROTECTION RATING</b>	15 A, UL (Class CC or J), Safety device (fuse or miniature circuit-breaker), Power Wiring
<b>HEAT DISSIPATION AT CURRENT/SPEED</b>	26 W at 25% current and 0% speed 26 W at 25% current and 50% speed 31 W at 50% current and 0% speed 40 W at 50% current and 50% speed 48 W at 100% current and 0% speed 48 W at 50% current and 90% speed 68 W at 100% current and 50% speed 78 W at 100% current and 90% speed



PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House  
30 Pembroke Road  
Dublin 4,  
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

