

Eaton 188061

Eaton Moeller® series M30 Illuminated pushbutton actuator, RMQ-Titan, flat, momentary, yellow, blank, Front ring stainless steel M30I-FDL-Y

PRODUCT NAME	Eaton Moeller® series M30 Illuminated pushbutton actuator
CATALOG NUMBER	188061
PRODUCT LENGTH/DEPTH	36 mm
PRODUCT HEIGHT	30 mm
PRODUCT WIDTH	46 mm
PRODUCT WEIGHT	0.041 kg
CERTIFICATIONS	VDE 0660 IEC/EN 60947 CSA File No.: 012528 CSA Class No.: 3211-03 DNV UL File No.: E29184 GL IEC/EN 60947-5 UL 508 CSA-C22.2 No. 14-05 and 94-M91 CE marking UL Category Control No.: NKCR UL Listed CSA certified

TYPE	Illuminated pushbutton actuator
ACTUATOR COLOR	Yellow
ACTUATOR FUNCTION	Spring-return Momentary
FITTED WITH:	Front ring
OPERATING FREQUENCY	3600 Operations/h
CLIMATIC PROOFING	Damp heat, cyclic, to IEC 60068-2-30 Damp heat, constant, to IEC 60068-2-78
CONNECTION TO SMARTWIRE-DT	With SWD-RMQ connections Yes
ACTUATING FORCE	5 N
AMBIENT OPERATING TEMPERATURE - MAX	70 °C
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
FORCE FOR POSITIVE OPENING - MIN	0 N
NUMBER OF COMMAND POSITIONS	1
OPENING DIAMETER	30.5 mm
OPENING HEIGHT	0 mm
BEZEL COLOR	Stainless steel
SHOCK RESISTANCE	15 g, Mechanical, According to IEC/EN 60068-2-27, Sinusoidal shock 11 ms Mechanical, According to IEC/EN 60068-2-27
BEZEL MATERIAL	Metal
DESIGN	Flat Flat front
MOUNTING POSITION	As required
DEGREE OF PROTECTION	IP69 IP66 IP67
DEGREE OF PROTECTION (FRONT SIDE)	IP67 NEMA 4X, 13
INSCRIPTION	Blank
FRONT ELEMENT TYPE	Flat
LENS TYPE	Round
LIFESPAN, MECHANICAL	5,000,000 Operations

	eaton-operating-devices-m30-rmq-titan-flat-front-instruction-leaflet-il047019zu.pdf
	eaton-operating-m30-dimensions-006.eps
	eaton-operating-m30-dimensions-005.eps
	eaton-operating-m30-dimensions-004.eps
	eaton-operating-m30-dimensions.eps
	eaton-operating-m30-3d-drawing.eps
/	RMQ small E-Stop emergency-stop button

WIDTH OPENING	0 mm
PRODUCT CATEGORY	RMQ-Titan
SIZE	Front dimensions: Ø 36 mm
SUITABLE FOR	Illumination

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
: