



□□□□

Eaton 190929

Eaton M22 Emergency stop/emergency switching off pushbutton, Classical, Mushroom-shaped, pull-release, 38 mm, 2 N/C

□□□□

PRODUCT NAME	Eaton Moeller® series M22 emergency stop/emergency switching off pushbutton
CATALOG NUMBER	190929
PRODUCT LENGTH/DEPTH	150 mm
PRODUCT HEIGHT	30 mm
PRODUCT WIDTH	242 mm
PRODUCT WEIGHT	0.084 kg
CERTIFICATIONS	GL IEC/EN 60947 LR UL File No.: E29184 CSA File No.: 012528 UL 508 IEC/EN 60947-5 CSA-C22.2 No. 14-05 UL Listed CSA Class No.: 3211-03 DNV VDE 0660 UL Category Control No.: NKCR CSA certified CSA-C22.2 No. 94-91 CE marking
CATALOG NOTES	Contacts with safety function, by positive opening to IEC/EN 60947-5-1



Powering Business Worldwide

□□□□

TYPE	Controlled stop pushbutton/emergency-stop button
ACTUATOR COLOR	Red
FEATURES	Tamper-proof (according to ISO 13850, EN 418)
ACTUATOR FUNCTION	Pull-to-release
OPERATING FREQUENCY	600 Operations/h
POLLUTION DEGREE	3
CLIMATIC PROOFING	Damp heat, constant, to IEC 60068-2-78 Damp heat, cyclic, to IEC 60068-2-30
CONNECTION TO SMARTWIRE-DT	No
ILLUMINATION	Non-illuminated
BASE COLOR	Yellow
ACTUATING FORCE	50 N
ACTUATOR DIAMETER	38 mm
ACTUATOR TRAVEL AND ACTUATION FORCE (DIN EN 60947-5-1)	4.8 mm
AMBIENT OPERATING TEMPERATURE - MAX	70 °C
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
DIAMETER CAP	38 mm
FORCE FOR POSITIVE OPENING - MIN	15 N
KNOB TRAVEL	5.7 mm
NUMBER OF CONTACTS (NORMALLY CLOSED CONTACTS)	2
NUMBER OF CONTACTS (NORMALLY OPEN CONTACTS)	0
DESIGN	Mushroom-shaped Classical
MOUNTING POSITION	As required
RATED CONDITIONAL SHORT-CIRCUIT CURRENT (IQ)	1 kA
MOUNTING METHOD	Built-in
OVERVOLTAGE CATEGORY	III
CONNECTION TYPE (AUXILIARY CIRCUIT)	Screw connection

□□

DECLARATIONS OF CONFORMITY	eaton-emergency-stop-emergency-switching-off-pushbutton-declaration-of-conformity-uk251132en.pdf
□□□□□	IL04716005Z.pdf IL04716002Z

