

## Eaton 191340

NZMH3-AX630-S1. NZM3 PXR10 circuit breaker, 630A, 3p, screw terminal

<b>PRODUCT NAME</b>	Eaton Moeller series NZM molded case circuit breaker electronic
<b>CATALOG NUMBER</b>	191340
<b>PRODUCT LENGTH/DEPTH</b>	166 mm
<b>PRODUCT HEIGHT</b>	275 mm
<b>PRODUCT WIDTH</b>	140 mm
<b>PRODUCT WEIGHT</b>	6.34 kg
<b>COMPLIANCES</b>	RoHS conform
<b>CERTIFICATIONS</b>	IEC

<b>AMPERAGE RATING</b>	630 A
<b>VOLTAGE RATING</b>	1000 V - 1000 V
<b>CIRCUIT BREAKER FRAME TYPE</b>	NZM3
<b>FEATURES</b>	Motor drive optional Protection unit
<b>10.10 TEMPERATURE RISE</b>	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
<b>10.11 SHORT-CIRCUIT RATING</b>	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
<b>10.12 ELECTROMAGNETIC COMPATIBILITY</b>	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
<b>10.13 MECHANICAL FUNCTION</b>	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
<b>10.2.2 CORROSION RESISTANCE</b>	Meets the product standard's requirements.
<b>10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES</b>	Meets the product standard's requirements.
<b>10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT</b>	Meets the product standard's requirements.
<b>10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS</b>	Meets the product standard's requirements.
<b>10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION</b>	Meets the product standard's requirements.
<b>10.2.5 LIFTING</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.2.6 MECHANICAL IMPACT</b>	Does not apply, since the entire switchgear needs to

<b>CHARACTERISTIC CURVE</b>	<a href="#">eaton-circuit-breaker-nzm-mccb-characteristic-curve-012.eps</a>
	<a href="#">eaton-circuit-breaker-nzm-mccb-characteristic-curve-016.eps</a>
	<a href="#">eaton-circuit-breaker-basic-unit-bg3-il012100zu.pdf</a>
	<a href="#">eaton-circuit-breaker-switch-nzm-mccb-dimensions-016.eps</a>
	<a href="#">eaton-circuit-breaker-nzm-mccb-dimensions-020.eps</a>

	be evaluated.
<b>10.2.7 INSCRIPTIONS</b>	Meets the product standard's requirements.
<b>10.3 DEGREE OF PROTECTION OF ASSEMBLIES</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.4 CLEARANCES AND CREEPAGE DISTANCES</b>	Meets the product standard's requirements.
<b>10.5 PROTECTION AGAINST ELECTRIC SHOCK</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS</b>	Is the panel builder's responsibility.
<b>10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS</b>	Is the panel builder's responsibility.
<b>10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH</b>	Is the panel builder's responsibility.
<b>10.9.3 IMPULSE WITHSTAND VOLTAGE</b>	Is the panel builder's responsibility.
<b>10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL</b>	Is the panel builder's responsibility.
<b>POLLUTION DEGREE</b>	3
<b>MOUNTING METHOD</b>	Built-in device fixed built-in technique Fixed
<b>EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT</b>	119.07 W
<b>UTILIZATION CATEGORY</b>	A
<b>AMBIENT OPERATING TEMPERATURE - MAX</b>	70 °C
<b>AMBIENT OPERATING TEMPERATURE - MIN</b>	-25 °C
<b>AMBIENT STORAGE TEMPERATURE - MAX</b>	70 °C
<b>AMBIENT STORAGE TEMPERATURE - MIN</b>	40 °C
<b>NUMBER OF AUXILIARY CONTACTS (CHANGE-OVER CONTACTS)</b>	0
<b>NUMBER OF AUXILIARY CONTACTS (NORMALLY</b>	0

<b>CLOSED CONTACTS)</b>	
<b>NUMBER OF AUXILIARY CONTACTS (NORMALLY OPEN CONTACTS)</b>	0
<b>DEGREE OF PROTECTION</b>	IP20
<b>ELECTRICAL CONNECTION TYPE OF MAIN CIRCUIT</b>	Screw connection
<b>LIFESPAN, MECHANICAL</b>	15000 operations
<b>OVERVOLTAGE CATEGORY</b>	III
<b>NUMBER OF POLES</b>	Three-pole
<b>TERMINAL CAPACITY (COPPER STRIP)</b>	<p>Max. 8 segments of 24 mm x 1 mm (2x) at box terminal</p> <p>Max. 10 segments of 24 mm x 1 mm + 5 segments of 24 mm x 1 mm</p> <p>Max. 10 segments of 32 mm x 1 mm + 5 segments of 32 mm x 1 mm at rear-side connection (punched)</p> <p>Min. 6 segments of 16 mm x 0.8 mm at box terminal</p> <p>Min. 6 segments of 16 mm x 0.8 mm at rear-side connection (punched)</p> <p>10 segments of 50 mm x 1 mm (2x) at rear-side width extension</p>
<b>LIFESPAN, ELECTRICAL</b>	1000 operations at 1000 V AC-1
<b>FUNCTIONS</b>	System and cable protection
<b>TYPE</b>	Circuit breaker
<b>SPECIAL FEATURES</b>	<ul style="list-style-type: none"> <li>• Lifespan, mechanical: of which max. 50 % trip by shunt/undervoltage release</li> <li>• Overload and short-circuit protection LI</li> <li>• R.m.s. value measurement and "thermal memory"</li> <li>• USB interface for configuration and test function with Power Xpert</li> </ul>

	Protection Manager software <ul style="list-style-type: none"> <li>Rated current = rated uninterrupted current: 630 A</li> <li>Terminal capacity hint: Up to 240 mm<sup>2</sup> can be connected depending on the cable manufacturer.</li> </ul>
<b>APPLICATION</b>	Use in unearthed supply systems at 690 V
<b>POSITION OF CONNECTION FOR MAIN CURRENT CIRCUIT</b>	Front side
<b>RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)</b>	630 A
<b>RELEASE SYSTEM</b>	Electronic release
<b>RATED SHORT-TIME WITHSTAND CURRENT (T = 0.3 S)</b>	3.3 kA
<b>RATED SHORT-TIME WITHSTAND CURRENT (T = 1 S)</b>	3.3 kA
<b>SHORT-CIRCUIT RELEASE NON-DELAYED SETTING - MAX</b>	5040 A
<b>SHORT-CIRCUIT RELEASE NON-DELAYED SETTING - MIN</b>	1260 A
<b>TERMINAL CAPACITY (CONTROL CABLE)</b>	0.75 mm <sup>2</sup> - 1.5 mm <sup>2</sup> (2x) 0.75 mm <sup>2</sup> - 2.5 mm <sup>2</sup> (1x)
<b>TERMINAL CAPACITY (COPPER BUSBAR)</b>	M10 at rear-side screw connection Max. 30 mm x 10 mm + 30 mm x 5 mm direct at switch rear-side connection Max. 10 mm x 50 mm (2x) at rear-side width extension Min. 20 mm x 5 mm direct at switch rear-side connection
<b>TERMINAL CAPACITY (COPPER SOLID CONDUCTOR/CABLE)</b>	16 mm <sup>2</sup> (1x) at tunnel terminal 16 mm <sup>2</sup> (1x) direct at

	switch rear-side connection 16 mm <sup>2</sup> (2x) direct at switch rear-side connection 16 mm <sup>2</sup> (2x) at box terminal 300 mm <sup>2</sup> (2x) at rear-side width extension
<b>TERMINAL CAPACITY (ALUMINUM SOLID CONDUCTOR/CABLE)</b>	16 mm <sup>2</sup> (1x) at tunnel terminal
<b>TERMINAL CAPACITY (COPPER STRANDED CONDUCTOR/CABLE)</b>	16 mm <sup>2</sup> - 185 mm <sup>2</sup> (1x) at tunnel terminal 25 mm <sup>2</sup> - 120 mm <sup>2</sup> (2x) at box terminal 25 mm <sup>2</sup> - 240 mm <sup>2</sup> (2x) direct at switch rear-side connection 35 mm <sup>2</sup> - 240 mm <sup>2</sup> (1x) at box terminal 25 mm <sup>2</sup> - 240 mm <sup>2</sup> (1x) direct at switch rear-side connection
<b>TERMINAL CAPACITY (ALUMINUM STRANDED CONDUCTOR/CABLE)</b>	25 mm <sup>2</sup> - 185 mm <sup>2</sup> (1x) at tunnel terminal 50 mm <sup>2</sup> - 240 mm <sup>2</sup> (1x) at 2-hole tunnel terminal 50 mm <sup>2</sup> - 240 mm <sup>2</sup> (2x) at 2-hole tunnel terminal
<b>HANDLE TYPE</b>	Rocker lever
<b>SHORT DELAY CURRENT SETTING (ISD) - MAX</b>	0 A
<b>SHORT DELAY CURRENT SETTING (ISD) - MIN</b>	0 A
<b>INSTANTANEOUS CURRENT SETTING (II) - MAX</b>	10080 A
<b>INSTANTANEOUS CURRENT SETTING (II) - MIN</b>	1260 A
<b>NUMBER OF OPERATIONS PER HOUR - MAX</b>	60
<b>OVERLOAD CURRENT SETTING (IR) - MAX</b>	630 A
<b>OVERLOAD CURRENT SETTING (IR) - MIN</b>	252 A
<b>RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 1000 V, 50/60 HZ</b>	10 kA

<b>RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 230 V, 50/60 HZ</b>	150 kA
<b>RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 400/415 V, 50/60 HZ</b>	150 kA
<b>RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 440 V, 50/60 HZ</b>	130 kA
<b>RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 525 V, 50/60 HZ</b>	33 kA
<b>RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 690 V, 50/60 HZ</b>	9 kA
<b>RATED SHORT-CIRCUIT MAKING CAPACITY ICM AT 1000 V, 50/60 HZ</b>	17 kA
<b>RATED SHORT-CIRCUIT MAKING CAPACITY ICM AT 400/415 V, 50/60 HZ</b>	330 kA
<b>RATED SHORT-CIRCUIT MAKING CAPACITY ICM AT 440 V, 50/60 HZ</b>	286 kA
<b>RATED SHORT-CIRCUIT MAKING CAPACITY ICM AT 525 V, 50/60 HZ</b>	143 kA
<b>RATED SHORT-CIRCUIT MAKING CAPACITY ICM AT 690 V, 50/60 HZ</b>	70 kA
<b>STANDARD TERMINALS</b>	Screw terminal
<b>RATED SHORT-CIRCUIT MAKING CAPACITY ICM AT 240 V, 50/60 HZ</b>	330 kA
<b>RATED IMPULSE WITHSTAND VOLTAGE (UIMP) AT AUXILIARY CONTACTS</b>	6000 V
<b>RATED IMPULSE WITHSTAND VOLTAGE (UIMP) AT MAIN CONTACTS</b>	8000 V
<b>RATED INSULATION VOLTAGE (UI)</b>	690 V AC

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House  
30 Pembroke Road  
Dublin 4,  
Eaton.com  
© 2025

Follow us on social media to get the latest product and support information.

