



Eaton 188177

Eaton Moeller® series M30 Key-operated actuator, Flat Front, momentary, 2 positions 0, Bezel: stainless steel, Suitable for master key systems

□□□□

PRODUCT NAME	Eaton Moeller® series M30 key-operated actuator
CATALOG NUMBER	188177
PRODUCT LENGTH/DEPTH	36 mm
PRODUCT HEIGHT	75 mm
PRODUCT WIDTH	46 mm
PRODUCT WEIGHT	0.085 kg
CERTIFICATIONS	VDE 0660 IEC/EN 60947 CSA file No. 012528 CSA Class No.: 3211-03 DNV UL File No.: E29184 GL IEC/EN 60947-5 UL 508 CSA-C22.2 No. 14-05 CSA-C22.2 No. 94-91 CE marking UL Category Control No.: NKCR UL Listed CSA certified

□□□□

TYPE	Key-operated button
ACCESSORIES	2 keys included with supplied equipment.
ACTUATOR COLOR	Black
ACTUATOR FUNCTION	Spring-return Key withdrawable in position 0 Momentary
10.10 TEMPERATURE RISE	Not applicable.
10.11 SHORT-CIRCUIT RATING	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 ELECTROMAGNETIC COMPATIBILITY	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 MECHANICAL FUNCTION	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.
10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	Please enquire
10.2.5 LIFTING	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 MECHANICAL IMPACT	Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 INSCRIPTIONS	Meets the product standard's requirements.
10.3 DEGREE OF PROTECTION OF	Does not apply, since the entire switchgear needs to

□□

DECLARATIONS OF CONFORMITY

[eaton-key-operated-actuator-declaration-of-conformity-uk251346en.pdf](#)

[eaton-key-operated-actuator-declaration-of-conformity-uk251347en.pdf](#)

□□□□□

[eaton-operating-devices-m30-rmq-titan-flat-front-instruction-leaflet-il047019zu.pdf](#)

[eaton-operating-m30-dimensions-006.eps](#)

[eaton-operating-m30-key-operated-actuator-dimensions-002.eps](#)

□□

[eaton-operating-m30-dimensions-005.eps](#)

[eaton-operating-m30-dimensions-004.eps](#)

[eaton-operating-m30-key-operated-actuator-3d-drawing-002.eps](#)

ASSEMBLIES	be evaluated.
10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
FITTED WITH:	Front ring
OPERATING FREQUENCY	100 Operations/h
POLLUTION DEGREE	3
CLIMATIC PROOFING	Damp heat, cyclic, to IEC 60068-2-30 Damp heat, constant, to IEC 60068-2-78
CONNECTION TO SMARTWIRE-DT	Yes With SWD-RMQ connections
ACTUATOR TYPE	Key
AMBIENT OPERATING TEMPERATURE - MAX	70 °C
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT PVID	0 W
FORCE FOR POSITIVE OPENING - MIN	0 N
HEAT DISSIPATION CAPACITY PDISS	0 W
HEAT DISSIPATION PER POLE, CURRENT-DEPENDENT PVID	0 W
OPENING DIAMETER	30 mm
OPENING HEIGHT	0 mm
OPERATING TORQUE	0.5 Nm

RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)	0 A
STATIC HEAT DISSIPATION, NON- CURRENT-DEPENDENT PVS	0 W
SWITCHING ANGLE	40 °
WIDTH OPENING	0 mm
BEZEL COLOR	Stainless steel
SHOCK RESISTANCE	Mechanical, According to IEC/EN 60068-2-27 15 g, Mechanical, According to IEC/EN 60068-2-27, Sinusoidal shock 11 ms
BEZEL MATERIAL	Metal
DESIGN	Key operation lock mechanism Flat front
MOUNTING POSITION	As required
OVERVOLTAGE CATEGORY	III
DEGREE OF PROTECTION	NEMA 4X, 13
DEGREE OF PROTECTION (FRONT SIDE)	IP66
INDICATOR COLOR	Other
LENS TYPE	Round
LIFESPAN, MECHANICAL	100,000 Operations
NUMBER OF SWITCH POSITIONS	2
SIZE	Front dimensions: Ø 36 mm
PRODUCT CATEGORY	RMQ-Titan
SUITABLE FOR	Master key systems

