

## Eaton 189612

NZMN4-PX800-TAZ. NZM4 PXR25 circuit breaker - integrated energy measurement class 1, 800A, 3p, Screw terminal, earth-fault protection, ARMS and zone selectivity

<b>PRODUCT NAME</b>	Eaton Moeller series NZM molded case circuit breaker electronic
<b>CATALOG NUMBER</b>	189612
<b>PRODUCT LENGTH/DEPTH</b>	375 mm
<b>PRODUCT HEIGHT</b>	170 mm
<b>PRODUCT WIDTH</b>	210 mm
<b>PRODUCT WEIGHT</b>	19 kg
<b>COMPLIANCES</b>	RoHS conform
<b>CERTIFICATIONS</b>	IEC IEC/EN 60947

<b>AMPERAGE RATING</b>	800 A
<b>VOLTAGE RATING</b>	690 V - 690 V
<b>CIRCUIT BREAKER FRAME TYPE</b>	NZM4
<b>FEATURES</b>	Motor drive optional Protection unit
<b>10.10 TEMPERATURE RISE</b>	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
<b>10.11 SHORT-CIRCUIT RATING</b>	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
<b>10.12 ELECTROMAGNETIC COMPATIBILITY</b>	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
<b>10.13 MECHANICAL FUNCTION</b>	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
<b>10.2.2 CORROSION RESISTANCE</b>	Meets the product standard's requirements.
<b>10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES</b>	Meets the product standard's requirements.
<b>10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT</b>	Meets the product standard's requirements.
<b>10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS</b>	Meets the product standard's requirements.
<b>10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION</b>	Meets the product standard's requirements.
<b>10.2.5 LIFTING</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.2.6 MECHANICAL IMPACT</b>	Does not apply, since the entire switchgear needs to

<a href="#">eaton-circuit-breaker-basic-unit-bg4-il012101zu.pdf</a>	
<a href="#">eaton-circuit-breaker-nzm-mccb-dimensions-022.eps</a>	

	be evaluated.
<b>10.2.7 INSCRIPTIONS</b>	Meets the product standard's requirements.
<b>10.3 DEGREE OF PROTECTION OF ASSEMBLIES</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.4 CLEARANCES AND CREEPAGE DISTANCES</b>	Meets the product standard's requirements.
<b>10.5 PROTECTION AGAINST ELECTRIC SHOCK</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS</b>	Is the panel builder's responsibility.
<b>10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS</b>	Is the panel builder's responsibility.
<b>10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH</b>	Is the panel builder's responsibility.
<b>10.9.3 IMPULSE WITHSTAND VOLTAGE</b>	Is the panel builder's responsibility.
<b>10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL</b>	Is the panel builder's responsibility.
<b>POLLUTION DEGREE</b>	3
<b>MOUNTING METHOD</b>	Built-in device fixed built-in technique Fixed
<b>CLIMATIC PROOFING</b>	Damp heat, cyclic, to IEC 60068-2-30 Damp heat, constant, to IEC 60068-2-78
<b>EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT</b>	106 W
<b>UTILIZATION CATEGORY</b>	B (IEC/EN 60947-2)
<b>ISOLATION</b>	500 V AC (between auxiliary contacts and main contacts) 300 V AC (between the auxiliary contacts)
<b>AMBIENT OPERATING TEMPERATURE - MAX</b>	70 °C
<b>AMBIENT OPERATING TEMPERATURE - MIN</b>	-25 °C
<b>AMBIENT STORAGE</b>	70 °C

<b>TEMPERATURE - MAX</b>	
<b>AMBIENT STORAGE TEMPERATURE - MIN</b>	40 °C
<b>NUMBER OF AUXILIARY CONTACTS (CHANGE-OVER CONTACTS)</b>	0
<b>NUMBER OF AUXILIARY CONTACTS (NORMALLY CLOSED CONTACTS)</b>	0
<b>NUMBER OF AUXILIARY CONTACTS (NORMALLY OPEN CONTACTS)</b>	0
<b>PROTECTION AGAINST DIRECT CONTACT</b>	Finger and back-of-hand proof to VDE 0106 part 100
<b>DEGREE OF PROTECTION</b>	IP20 (basic degree of protection, in the operating controls area) IP20
<b>DIRECTION OF INCOMING SUPPLY</b>	As required
<b>ELECTRICAL CONNECTION TYPE OF MAIN CIRCUIT</b>	Screw connection
<b>LIFESPAN, MECHANICAL</b>	10000 operations
<b>OVERVOLTAGE CATEGORY</b>	III
<b>DEGREE OF PROTECTION (IP), FRONT SIDE</b>	IP66 (with door coupling rotary handle) IP40 (with insulating surround)
<b>DEGREE OF PROTECTION (TERMINATIONS)</b>	IP00 (terminations, phase isolator and strip terminal) IP10 (tunnel terminal)
<b>NUMBER OF POLES</b>	Three-pole
<b>TERMINAL CAPACITY (COPPER STRIP)</b>	10 segments of 50 mm x 1 mm (2x) at 1-hole module plate Min. 6 segments of 16 mm x 0.8 mm at flat conductor terminal Max. 10 segments of 32 mm x 1 mm (2x) at flat conductor terminal 10 segments of 80 mm x 1 mm (2x) at rear-side width extension Min. 10 segments of 50 mm x 1 mm (2x) at rear-side connection (punched)

	Min. 5 segments of 25 mm x 1 mm at rear-side connection (punched)
<b>LIFESPAN, ELECTRICAL</b>	2000 operations at 690 V AC-1 3000 operations at 415 V AC-1 3000 operations at 400 V AC-1
<b>FUNCTIONS</b>	Earth-fault protection Zone selectivity ARMS maintenance mode Integrated earth fault protection Systems, cable, selectivity and generator protection
<b>EARTH-FAULT CURRENT SETTING (IG) - MAX</b>	800 x I <sub>n</sub>
<b>TYPE</b>	Circuit breaker

#### SPECIAL FEATURES

- LSI<sub>G</sub> overload protection and delayed and non-delayed short-circuit protective device, earth-fault protection
- Class 1 energy measurement, r.m.s. value measurement, and "thermal memory"
- USB interface for configuration and test function with Power Xpert Protection Manager software
- Zone selectivity ZSI
- Maintenance Mode ARMS
- Interface module in equipment supplied.
- Optionally communication-capable with internal Modbus RTU module or CAM
- Maximum back-up fuse, if the expected short-

- circuit currents at the installation location exceed the switching capacity of the circuit breaker (Rated short-circuit breaking capacity  $I_{cn}$ )
- Rated current = rated uninterrupted current: 800 A

<b>APPLICATION</b>	525 V
<b>SHOCK RESISTANCE</b>	15 g (half-sinusoidal shock 11 ms)
<b>EARTH-FAULT CURRENT SETTING (IG) - MIN</b>	$160 \times I_n$
<b>POSITION OF CONNECTION FOR MAIN CURRENT CIRCUIT</b>	Front side
<b>RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)</b>	800 A
<b>RELEASE SYSTEM</b>	Electronic release
<b>SHORT-CIRCUIT TOTAL BREAKTIME</b>	< 25 ms ( < 415 V); < 35 ms (> 415 V)
<b>RATED SHORT-TIME WITHSTAND CURRENT (T = 0.3 S)</b>	12 kA
<b>RATED SHORT-TIME WITHSTAND CURRENT (T = 1 S)</b>	12 kA
<b>SHORT-CIRCUIT RELEASE DELAYED SETTING - MAX</b>	10 A
<b>SHORT-CIRCUIT RELEASE DELAYED SETTING - MIN</b>	2 A
<b>SHORT-CIRCUIT RELEASE NON-DELAYED SETTING - MAX</b>	15 A
<b>SHORT-CIRCUIT RELEASE NON-DELAYED SETTING - MIN</b>	2 A
<b>TERMINAL CAPACITY (CONTROL CABLE)</b>	0.75 mm <sup>2</sup> - 2.5 mm <sup>2</sup> (1x) 0.75 mm <sup>2</sup> - 1.5 mm <sup>2</sup> (2x)
<b>TERMINAL CAPACITY (COPPER BUSBAR)</b>	Max. 50 mm x 10 mm (2x) at rear-side 1-hole module plate Max. 80 mm x 10 mm (2x)

	at rear-side width extension Min. 25 mm x 5 mm direct at switch rear-side connection Min. 60 mm x 10 mm at rear-side width extension Max. 50 mm x 10 mm (2x) direct at switch rear-side connection Min. 25 mm x 5 mm at rear-side 1-hole module plate M10 at rear-side screw connection 50 mm x 10 mm (2x) at rear-side 2-hole module plate
<b>TERMINAL CAPACITY (COPPER SOLID CONDUCTOR/CABLE)</b>	300 mm <sup>2</sup> (4x) at rear-side width extension 35 mm <sup>2</sup> - 185 mm <sup>2</sup> (4x) at rear-side 2-hole module plate 50 mm <sup>2</sup> - 240 mm <sup>2</sup> (4x) at 4-hole tunnel terminal 120 mm <sup>2</sup> - 300 mm <sup>2</sup> (1x) at rear-side 1-hole module plate 95 mm <sup>2</sup> - 185 mm <sup>2</sup> (2x) at rear-side 2-hole module plate 95 mm <sup>2</sup> - 300 mm <sup>2</sup> (2x) at rear-side 1-hole module plate 95 mm <sup>2</sup> - 240 mm <sup>2</sup> (6x) at rear-side width extension
<b>TERMINAL CAPACITY (COPPER STRANDED CONDUCTOR/CABLE)</b>	50 mm <sup>2</sup> - 185 mm <sup>2</sup> (4x) direct at switch rear-side connection 120 mm <sup>2</sup> - 185 mm <sup>2</sup> (1x) direct at switch rear-side connection
<b>TERMINAL CAPACITY (ALUMINUM STRANDED CONDUCTOR/CABLE)</b>	50 mm <sup>2</sup> - 240 mm <sup>2</sup> (4x) at 4-hole tunnel terminal
<b>HANDLE TYPE</b>	Rocker lever
<b>SHORT DELAY CURRENT SETTING (ISD) - MAX</b>	10 A
<b>SHORT DELAY CURRENT SETTING (ISD) - MIN</b>	2 A
<b>INSTANTANEOUS CURRENT SETTING (II) - MAX</b>	18 A

<b>INSTANTANEOUS CURRENT SETTING (II) - MIN</b>	2 A
<b>NUMBER OF OPERATIONS PER HOUR - MAX</b>	60
<b>OVERLOAD CURRENT SETTING (IR) - MAX</b>	800 A
<b>OVERLOAD CURRENT SETTING (IR) - MIN</b>	320 A
<b>RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 230 V, 50/60 HZ</b>	37 kA
<b>RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 400/415 V, 50/60 HZ</b>	37 kA
<b>RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 440 V, 50/60 HZ</b>	26 kA
<b>RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 525 V, 50/60 HZ</b>	19 kA
<b>RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 690 V, 50/60 HZ</b>	15 kA
<b>RATED SHORT-CIRCUIT MAKING CAPACITY ICM AT 400/415 V, 50/60 HZ</b>	105 kA
<b>RATED SHORT-CIRCUIT MAKING CAPACITY ICM AT 440 V, 50/60 HZ</b>	74 kA
<b>RATED SHORT-CIRCUIT MAKING CAPACITY ICM AT 525 V, 50/60 HZ</b>	53 kA
<b>RATED SHORT-CIRCUIT MAKING CAPACITY ICM AT 690 V, 50/60 HZ</b>	40 kA
<b>STANDARD TERMINALS</b>	Screw connection
<b>OPTIONAL TERMINALS</b>	Connection on rear. Strip terminal. Tunnel terminal
<b>RATED SHORT-CIRCUIT MAKING CAPACITY ICM AT 240 V, 50/60 HZ</b>	105 kA
<b>RATED IMPULSE WITHSTAND VOLTAGE</b>	6000 V

<b>(UIMP) AT AUXILIARY CONTACTS</b>	
<b>RATED IMPULSE WITHSTAND VOLTAGE (UIMP) AT MAIN CONTACTS</b>	8000 V
<b>RATED SHORT-CIRCUIT BREAKING CAPACITY ICU (IEC/EN 60947) AT 525 V, 50/60 HZ</b>	25 kA
<b>RATED SHORT-CIRCUIT BREAKING CAPACITY ICU (IEC/EN 60947) AT 400/415 V, 50/60 HZ</b>	50 kA
<b>RATED SHORT-CIRCUIT BREAKING CAPACITY ICU (IEC/EN 60947) AT 230 V, 50/60 HZ</b>	50 kA
<b>RATED SHORT-CIRCUIT BREAKING CAPACITY ICU (IEC/EN 60947) AT 690 V, 50/60 HZ</b>	20 kA
<b>RATED SHORT-CIRCUIT BREAKING CAPACITY ICU (IEC/EN 60947) AT 440 V, 50/60 HZ</b>	35 kA
<b>RATED INSULATION VOLTAGE (UI)</b>	1000 V AC

<b>PROJECT NAME:</b>
<b>PROJECT NUMBER:</b>
<b>PREPARED BY:</b>
:



Eaton House  
30 Pembroke Road  
Dublin 4,  
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

