



□□□□□

Eaton 192035

NZMS2-VX40. Circuit-breaker, NZM2 PXR20, 3 pole, 40A, screw terminal

□□□□

PRODUCT NAME	Eaton Moeller series NZM molded case circuit breaker electronic
CATALOG NUMBER	192035
PRODUCT LENGTH/DEPTH	184 mm
PRODUCT HEIGHT	149 mm
PRODUCT WIDTH	105 mm
PRODUCT WEIGHT	2.437 kg
COMPLIANCES	RoHS conform
CERTIFICATIONS	IEC/EN 60947 IEC

□□□□

AMPERAGE RATING	40 A
VOLTAGE RATING	690 V - 690 V
CIRCUIT BREAKER FRAME TYPE	NZM2
FEATURES	Protection unit Motor drive optional
10.10 TEMPERATURE RISE	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 SHORT-CIRCUIT RATING	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 ELECTROMAGNETIC COMPATIBILITY	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 MECHANICAL FUNCTION	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.
10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	Meets the product standard's requirements.
10.2.5 LIFTING	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 MECHANICAL IMPACT	Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 INSCRIPTIONS	Meets the product standard's requirements.

□□

	eaton-circuit-breaker-nzm-mccb-characteristic-curve-020.eps
CHARACTERISTIC CURVE	eaton-circuit-breaker-nzm-mccb-characteristic-curve-024.eps
□□□□□	eaton-circuit-breakers-nzmb-nzmn-basic-unit-bg2-instruction-leaflet-il012099zu.pdf
□□	eaton-circuit-breaker-nzm-mccb-dimensions-019.eps

10.3 DEGREE OF PROTECTION OF ASSEMBLIES	Does not apply, since the entire switchgear needs to be evaluated.
10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
POLLUTION DEGREE	3
MOUNTING METHOD	DIN rail (top hat rail) mounting optional Built-in device fixed built-in technique Fixed
CLIMATIC PROOFING	Damp heat, constant, to IEC 60068-2-78 Damp heat, cyclic, to IEC 60068-2-30
EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT	1.32 W
UTILIZATION CATEGORY	A (IEC/EN 60947-2)
ISOLATION	500 V AC (between auxiliary contacts and main contacts) 300 V AC (between the auxiliary contacts)
AMBIENT OPERATING TEMPERATURE - MAX	70 °C
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
AMBIENT STORAGE TEMPERATURE - MAX	70 °C
AMBIENT STORAGE TEMPERATURE - MIN	40 °C
NUMBER OF AUXILIARY	0

CONTACTS (CHANGE-OVER CONTACTS)	
NUMBER OF AUXILIARY CONTACTS (NORMALLY CLOSED CONTACTS)	0
NUMBER OF AUXILIARY CONTACTS (NORMALLY OPEN CONTACTS)	0
PROTECTION AGAINST DIRECT CONTACT	Finger and back-of-hand proof to DIN EN 50274/VDE 0106 part 110
DEGREE OF PROTECTION	IP20 IP20 (basic degree of protection, in the operating controls area)
DIRECTION OF INCOMING SUPPLY	As required
ELECTRICAL CONNECTION TYPE OF MAIN CIRCUIT	Screw connection
LIFESPAN, MECHANICAL	20000 operations
OVERVOLTAGE CATEGORY	III
DEGREE OF PROTECTION (IP), FRONT SIDE	IP40 (with insulating surround) IP66 (with door coupling rotary handle)
DEGREE OF PROTECTION (TERMINATIONS)	IP00 (terminations, phase isolator and strip terminal)
	IP10 (tunnel terminal)
NUMBER OF POLES	Three-pole
TERMINAL CAPACITY (COPPER STRIP)	Max. 10 segments of 24 mm x 0.8 mm at rear-side connection (punched) Max. 8 segments of 24 mm x 1 mm (2x) at box terminal Max. 10 segments of 16 mm x 0.8 mm at box terminal Min. 2 segments of 16 mm x 0.8 mm at rear-side connection (punched) Min. 2 segments of 9 mm x 0.8 mm at box terminal
LIFESPAN, ELECTRICAL	10000 operations at 400 V AC-1 10000 operations at 415 V AC-1 7500 operations at 690 V AC-1
FUNCTIONS	Systems, cable, selectivity and generator protection

TYPE	Circuit breaker
SPECIAL FEATURES	• LSI overload protection and delayed and non-delayed short-circuit protective device • R.m.s. value measurement and “thermal memory” • USB interface for configuration and test function with Power Xpert Protection Manager software • Optionally communication-capable with interface module and internal Modbus RTU module or CAM • Maximum back-up fuse, if the expected short-circuit currents at the installation location exceed the switching capacity of the circuit breaker (Rated short-circuit breaking capacity I_{cn}) • Rated current = rated uninterrupted current: 40 A
APPLICATION	Use in unearthed supply systems at 690 V
SHOCK RESISTANCE	20 g (half-sinusoidal shock 20 ms)
POSITION OF CONNECTION FOR MAIN CURRENT CIRCUIT	Front side
RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)	40 A
RELEASE SYSTEM	Electronic release
SHORT-CIRCUIT TOTAL BREAKTIME	< 10 ms
RATED SHORT-TIME WITHSTAND CURRENT (T = 0.3 S)	1.9 kA

RATED SHORT-TIME WITHSTAND CURRENT (T = 1 S)	1.9 kA
SHORT-CIRCUIT RELEASE DELAYED SETTING - MAX	400 A
SHORT-CIRCUIT RELEASE DELAYED SETTING - MIN	40 A
SHORT-CIRCUIT RELEASE NON-DELAYED SETTING - MAX	720 A
SHORT-CIRCUIT RELEASE NON-DELAYED SETTING - MIN	80 A
TERMINAL CAPACITY (CONTROL CABLE)	0.75 mm ² - 2.5 mm ² (1x) 0.75 mm ² - 1.5 mm ² (2x)
TERMINAL CAPACITY (COPPER BUSBAR)	Max. 24 mm x 8 mm direct at switch rear-side connection M8 at rear-side screw connection Min. 16 mm x 5 mm direct at switch rear-side connection
TERMINAL CAPACITY (COPPER SOLID CONDUCTOR/CABLE)	6 mm ² - 16 mm ² (2x) direct at switch rear-side connection 10 mm ² - 16 mm ² (1x) at box terminal 10 mm ² - 16 mm ² (1x) direct at switch rear-side connection 6 mm ² - 16 mm ² (2x) at box terminal 16 mm ² (1x) at tunnel terminal
TERMINAL CAPACITY (ALUMINUM SOLID CONDUCTOR/CABLE)	16 mm ² (1x) at tunnel terminal
TERMINAL CAPACITY (COPPER STRANDED CONDUCTOR/CABLE)	25 mm ² - 70 mm ² (2x) at box terminal 25 mm ² - 185 mm ² (1x) at box terminal 25 mm ² - 185 mm ² (1x) at 1-hole tunnel terminal 25 mm ² - 185 mm ² (1x) direct at switch rear-side connection 25 mm ² - 70 mm ² (2x) direct at switch rear-side connection
TERMINAL CAPACITY (ALUMINUM STRANDED CONDUCTOR/CABLE)	25 mm ² - 185 mm ² (1x) at tunnel terminal
HANDLE TYPE	Rocker lever
SHORT DELAY CURRENT	10 A

SETTING (ISD) - MAX	
SHORT DELAY CURRENT SETTING (ISD) - MIN	2 A
INSTANTANEOUS CURRENT SETTING (II) - MAX	18 A
INSTANTANEOUS CURRENT SETTING (II) - MIN	2 A
NUMBER OF OPERATIONS PER HOUR - MAX	120
OVERLOAD CURRENT SETTING (IR) - MAX	40 A
OVERLOAD CURRENT SETTING (IR) - MIN	20 A
RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 230 V, 50/60 HZ	100 kA
RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 400/415 V, 50/60 HZ	70 kA
RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 440 V, 50/60 HZ	65 kA
RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 525 V, 50/60 HZ	36 kA
RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 690 V, 50/60 HZ	6 kA
RATED SHORT-CIRCUIT MAKING CAPACITY ICM AT 400/415 V, 50/60 HZ	154 kA
RATED SHORT-CIRCUIT MAKING CAPACITY ICM AT 440 V, 50/60 HZ	143 kA
RATED SHORT-CIRCUIT MAKING CAPACITY ICM AT 525 V, 50/60 HZ	80 kA
RATED SHORT-CIRCUIT MAKING CAPACITY ICM AT 690 V, 50/60 HZ	40 kA
STANDARD TERMINALS	Screw terminal
OPTIONAL TERMINALS	Box terminal. Connection on rear. Tunnel terminal
RATED SHORT-CIRCUIT	220 kA

MAKING CAPACITY ICM AT 240 V, 50/60 HZ	
RATED IMPULSE WITHSTAND VOLTAGE (UIMP) AT AUXILIARY CONTACTS	6000 V
RATED IMPULSE WITHSTAND VOLTAGE (UIMP) AT MAIN CONTACTS	8000 V
RATED INSULATION VOLTAGE (UI)	690 V AC

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY: