



□□□□□

Eaton 191103

Eaton Moeller® series MSC-DM DOL starter,
380 V 400 V 415 V: 0.09 kW, Ir= 0.25 - 0.4 A,
24 V DC, DC voltage MSC-DM-0,4-
M7(24VDC)/MSFA

□□□□

PRODUCT NAME	Eaton Moeller® series MSC-DM DOL starter
CATALOG NUMBER	191103
PRODUCT LENGTH/DEPTH	115 mm
PRODUCT HEIGHT	180 mm
PRODUCT WIDTH	45 mm
PRODUCT WEIGHT	0.724 kg
CERTIFICATIONS	UL 508 (on request) CSA-C22.2 No. 14 (on request)

TYPE	Starter with Bi-Metal release
10.10 TEMPERATURE RISE	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 SHORT-CIRCUIT RATING	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 ELECTROMAGNETIC COMPATIBILITY	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 MECHANICAL FUNCTION	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.
10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	Meets the product standard's requirements.
10.2.5 LIFTING	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 MECHANICAL IMPACT	Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 INSCRIPTIONS	Meets the product standard's requirements.
10.3 DEGREE OF PROTECTION OF ASSEMBLIES	Does not apply, since the entire switchgear needs to be evaluated.
10.4 CLEARANCES AND	Meets the product

DECLARATIONS OF CONFORMITY	eaton-dol-starter-declaration-of-conformity-uk251157en.pdf
□□□□□	IL034030ZU
□□□	eaton-manual-motor-starters-device-msc-d-dol-starter-wiring-diagram.eps
□□□□	eaton-msfs-motor-starter-feeder-system-brochure-br034005en-en-us.pdf
□□	eaton-manual-motor-starters-msc-d-dol-starter-dimensions-005.eps eaton-manual-motor-starters-msc-d-dol-starter-3d-drawing-003.eps

CREEPAGE DISTANCES	standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
FITTED WITH:	Short-circuit release
POLLUTION DEGREE	3
CLASS	CLASS 10 A
CONNECTION TO SMARTWIRE-DT	No
RATED IMPULSE WITHSTAND VOLTAGE (UIMP)	6000 V AC
MODEL	IEC starter
ALTITUDE	Max. 2000 m
ELECTRICAL CONNECTION TYPE OF MAIN CIRCUIT	Screw connection
VOLTAGE TYPE	DC
MOUNTING METHOD	Motor starter Feeder System
OVERVOLTAGE CATEGORY	III
CONNECTION	Screw terminals
FUNCTIONS	Temperature compensated overload protection
OVERLOAD RELEASE CURRENT SETTING - MIN	0.25 A
POWER CONSUMPTION (SEALING) AT DC	2.6 W
RATED CONDITIONAL SHORT-CIRCUIT CURRENT (IQ), TYPE 2, 230 V	50000 A
RATED CONDITIONAL	50000 A

SHORT-CIRCUIT CURRENT (IQ), TYPE 2, 380 V, 400 V, 415 V	
RATED CONDITIONAL SHORT-CIRCUIT CURRENT, TYPE 1, 480 Y/277 V	0 A
RATED CONDITIONAL SHORT-CIRCUIT CURRENT, TYPE 1, 600 Y/347 V	0 A
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 50 HZ - MAX	0 V
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 50 HZ - MIN	0 V
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 60 HZ - MAX	0 V
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 60 HZ - MIN	0 V
RATED CONTROL SUPPLY VOLTAGE (US) AT DC - MAX	24 V
RATED CONTROL SUPPLY VOLTAGE (US) AT DC - MIN	24 V
RATED OPERATIONAL CURRENT (IE) AT AC-3, 380 V, 400 V, 415 V	0.4 A
RATED OPERATIONAL CURRENT (IE)	0.31 A
RATED OPERATIONAL VOLTAGE	230 - 415 V AC
SUITABLE FOR	Also motors with efficiency class IE3
AMBIENT OPERATING TEMPERATURE - MAX	55 °C
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
COORDINATION TYPE	2
NUMBER OF AUXILIARY CONTACTS (NORMALLY CLOSED CONTACTS)	0
NUMBER OF AUXILIARY CONTACTS (NORMALLY OPEN CONTACTS)	1
NUMBER OF COMMAND POSITIONS	0
NUMBER OF PILOT	0

LIGHTS	
OVERLOAD RELEASE CURRENT SETTING - MAX	0.4 A
RATED OPERATIONAL POWER AT AC-3, 220/230 V, 50 HZ	0.06 kW
RATED OPERATIONAL POWER AT AC-3, 380/400 V, 50 HZ	0.09 kW
RATED POWER AT 460 V, 60 HZ, 3-PHASE	0 kW
RATED POWER AT 575 V, 60 HZ, 3-PHASE	0 kW
SHORT-CIRCUIT RELEASE (IRM) - MAX	6.2 A
COORDINATION CLASS (IEC 60947-4-3)	Class 2
DEGREE OF PROTECTION	IP20 NEMA Other
ELECTRICAL CONNECTION TYPE FOR AUXILIARY- AND CONTROL-CURRENT CIRCUIT	Screw connection
ACTUATING VOLTAGE	24 V DC
POWER CONSUMPTION	2.6 W

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



0000
Eaton House
30 Pembroke Road
Dublin 4, 0000
Eaton.com

© 2025 00 00000000

Follow us on social media to get the latest product and support information.

