



□□□□□

Eaton 192114

Eaton Moeller series NZM - Molded Case Circuit Breaker. NZM2 PXR25 circuit breaker - integrated energy measurement class 1, 220A, 3p, Screw terminal, H, 2

□□□□

PRODUCT NAME	Eaton Moeller series NZM molded case circuit breaker electronic
CATALOG NUMBER	192114
PRODUCT LENGTH/DEPTH	190 mm
PRODUCT HEIGHT	160 mm
PRODUCT WIDTH	115 mm
PRODUCT WEIGHT	2.4 kg
COMPLIANCES	RoHS conform
CERTIFICATIONS	IEC/EN 60947 IEC

□□□□	
AMPERAGE RATING	220 A
VOLTAGE RATING	690 V - 690 V
CIRCUIT BREAKER FRAME TYPE	NZM2
10.10 TEMPERATURE RISE	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 SHORT-CIRCUIT RATING	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 ELECTROMAGNETIC COMPATIBILITY	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 MECHANICAL FUNCTION	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.
10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	Meets the product standard's requirements.
10.2.5 LIFTING	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 MECHANICAL IMPACT	Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 INSCRIPTIONS	Meets the product standard's requirements.
10.3 DEGREE OF PROTECTION OF	Does not apply, since the entire switchgear needs to

□□	
CHARACTERISTIC CURVE	eaton-circuit-breaker-nzm-mccb-characteristic-curve-014.eps eaton-circuit-breaker-nzm-mccb-characteristic-curve-010.eps
□□□□□	eaton-circuit-breakers-nzmb-nzmn-basic-unit-bg2-instruction-leaflet-il012099zu.pdf
□□	eaton-circuit-breaker-nzm-mccb-dimensions-019.eps

ASSEMBLIES	be evaluated.
10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
FITTED WITH:	Thermal protection
POLLUTION DEGREE	3
MOUNTING METHOD	Fixed Built-in device fixed built-in technique
CLIMATIC PROOFING	Damp heat, cyclic, to IEC 60068-2-30 Damp heat, constant, to IEC 60068-2-78
EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT	39.93 W
UTILIZATION CATEGORY	A (IEC/EN 60947-2)
ISOLATION	300 V AC (between the auxiliary contacts) 500 V AC (between auxiliary contacts and main contacts)
AMBIENT OPERATING TEMPERATURE - MAX	70 °C
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
AMBIENT STORAGE TEMPERATURE - MAX	70 °C
AMBIENT STORAGE TEMPERATURE - MIN	40 °C
PROTECTION AGAINST DIRECT CONTACT	Finger and back-of-hand proof to VDE 0106 part 100

RATED INSULATION VOLTAGE (UI)	690 V
RATED OPERATING POWER AT AC-3, 230 V	55 kW
RATED OPERATING POWER AT AC-3, 400 V	110 kW
SWITCH OFF TECHNIQUE	Electronic
DEGREE OF PROTECTION	IP20 (basic degree of protection, in the operating controls area) IP20
DIRECTION OF INCOMING SUPPLY	As required
ELECTRICAL CONNECTION TYPE OF MAIN CIRCUIT	Screw connection
LIFESPAN, MECHANICAL	20000 operations
OVERVOLTAGE CATEGORY	III
DEGREE OF PROTECTION (IP), FRONT SIDE	IP40 (with insulating surround) IP66 (with door coupling rotary handle)
DEGREE OF PROTECTION (TERMINATIONS)	IP10 (tunnel terminal) IP00 (terminations, phase isolator and strip terminal)
NUMBER OF POLES	Three-pole
TERMINAL CAPACITY (COPPER STRIP)	Max. 10 segments of 24 mm x 0.8 mm at rear-side connection (punched) Max. 8 segments of 24 mm x 1 mm (2x) at box terminal Min. 2 segments of 16 mm x 0.8 mm at rear-side connection (punched) Min. 2 segments of 9 mm x 0.8 mm at box terminal Max. 10 segments of 16 mm x 0.8 mm at box terminal
LIFESPAN, ELECTRICAL	6500 operations at 415 V AC-3 10000 operations at 400 V AC-1 10000 operations at 415 V AC-1 6500 operations at 400 V AC-3 5000 operations at 690 V AC-3 7500 operations at 690 V AC-1
FUNCTIONS	Phase failure sensitive

	Motor protection
TYPE	Circuit breaker
SPECIAL FEATURES	<ul style="list-style-type: none"> • Maximum back-up fuse, if the expected short-circuit currents at the installation location exceed the switching capacity of the circuit breaker (Rated short-circuit breaking capacity I_{cn}) • Motor protection - overload- and short-circuit protective device LI Motor • Class 1 energy measurement, phase loss protection, r.m.s. value measurement, and "thermal memory" • USB interface for configuration and test function with Power Xpert Protection Manager software • Interface module in equipment supplied. • Optionally communication-capable with interface module and internal Modbus RTU module or CAM • Rated current = rated uninterrupted current: 220 A
APPLICATION	Use in unearthed supply systems at 690 V
SHOCK RESISTANCE	20 g (half-sinusoidal shock 20 ms)
RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)	220 A
RATED SHORT-TIME WITHSTAND CURRENT (T = 0.3 S)	1.9 kA

RATED SHORT-TIME WITHSTAND CURRENT (T = 1 S)	1.9 kA
SHORT-CIRCUIT RELEASE NON-DELAYED SETTING - MAX	3080 A
SHORT-CIRCUIT RELEASE NON-DELAYED SETTING - MIN	440 A
HANDLE TYPE	Rocker lever
INSTANTANEOUS CURRENT SETTING (II) - MAX	14 A
INSTANTANEOUS CURRENT SETTING (II) - MIN	2 A
NUMBER OF OPERATIONS PER HOUR - MAX	120
OVERLOAD CURRENT SETTING (IR) - MAX	220 A
OVERLOAD CURRENT SETTING (IR) - MIN	88 A
RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 230 V, 50/60 HZ	150 kA
RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 400/415 V, 50/60 HZ	130 kA
RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 440 V, 50/60 HZ	130 kA
RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 525 V, 50/60 HZ	37.5 kA
RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 690 V, 50/60 HZ	5 kA
STANDARD TERMINALS	Screw terminal
OPTIONAL TERMINALS	Box terminal. Connection on rear. Tunnel terminal
RELEASE SYSTEM	Electronic release
SHORT-CIRCUIT TOTAL BREAKTIME	< 10 ms
TERMINAL CAPACITY (ALUMINUM SOLID CONDUCTOR/CABLE)	16 mm ² (1x) at tunnel terminal

TERMINAL CAPACITY (ALUMINUM STRANDED CONDUCTOR/CABLE)	25 mm ² - 185 mm ² (1x) at tunnel terminal
TERMINAL CAPACITY (CONTROL CABLE)	0.75 mm ² - 1.5 mm ² (2x) 0.75 mm ² - 2.5 mm ² (1x)
TERMINAL CAPACITY (COPPER BUSBAR)	M8 at rear-side screw connection Max. 24 mm x 8 mm direct at switch rear-side connection Min. 16 mm x 5 mm direct at switch rear-side connection
TERMINAL CAPACITY (COPPER SOLID CONDUCTOR/CABLE)	6 mm ² - 16 mm ² (2x) at box terminal 6 mm ² - 16 mm ² (2x) direct at switch rear-side connection 10 mm ² - 16 mm ² (1x) direct at switch rear-side connection 16 mm ² (1x) at tunnel terminal 10 mm ² - 16 mm ² (1x) at box terminal
TERMINAL CAPACITY (COPPER STRANDED CONDUCTOR/CABLE)	25 mm ² - 185 mm ² (1x) at box terminal 25 mm ² - 185 mm ² (1x) at 1-hole tunnel terminal 25 mm ² - 70 mm ² (2x) at box terminal 25 mm ² - 185 mm ² (1x) direct at switch rear-side connection 25 mm ² - 70 mm ² (2x) direct at switch rear-side connection
RATED SHORT-CIRCUIT BREAKING CAPACITY ICU (IEC/EN 60947) AT 400/415 V, 50/60 HZ	130 kA
RATED SHORT-CIRCUIT MAKING CAPACITY ICM AT 400/415 V, 50/60 HZ	330 kA
RATED SHORT-CIRCUIT MAKING CAPACITY ICM AT 440 V, 50/60 HZ	286 kA
RATED SHORT-CIRCUIT MAKING CAPACITY ICM AT 525 V, 50/60 HZ	105 kA
RATED SHORT-CIRCUIT MAKING CAPACITY ICM AT 690 V, 50/60 HZ	40 kA
RATED SHORT-CIRCUIT MAKING CAPACITY ICM AT 240 V, 50/60 HZ	330 kA

RATED IMPULSE WITHSTAND VOLTAGE (UIMP) AT AUXILIARY CONTACTS	6000 V
RATED IMPULSE WITHSTAND VOLTAGE (UIMP) AT MAIN CONTACTS	8000 V

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY: