



□□□□

## Eaton 192233

NZMS2-4-PX63/VAR-T. NZM2 PXR25 circuit breaker - integrated energy measurement class 1, 63A, 4p, variable, Screw terminal, earth-fault protection and zone selectivity

□□□□

<b>PRODUCT NAME</b>	Eaton Moeller series NZM molded case circuit breaker electronic
<b>CATALOG NUMBER</b>	192233
<b>PRODUCT LENGTH/DEPTH</b>	149 mm
<b>PRODUCT HEIGHT</b>	184 mm
<b>PRODUCT WIDTH</b>	140 mm
<b>PRODUCT WEIGHT</b>	3 kg
<b>COMPLIANCES</b>	RoHS conform
<b>CERTIFICATIONS</b>	IEC IEC/EN 60947



Powering Business Worldwide

<b>AMPERAGE RATING</b>	63 A
<b>VOLTAGE RATING</b>	690 V - 690 V
<b>CIRCUIT BREAKER FRAME TYPE</b>	NZM2
<b>FEATURES</b>	Motor drive optional Protection unit
<b>10.10 TEMPERATURE RISE</b>	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
<b>10.11 SHORT-CIRCUIT RATING</b>	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
<b>10.12 ELECTROMAGNETIC COMPATIBILITY</b>	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
<b>10.13 MECHANICAL FUNCTION</b>	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
<b>10.2.2 CORROSION RESISTANCE</b>	Meets the product standard's requirements.
<b>10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES</b>	Meets the product standard's requirements.
<b>10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT</b>	Meets the product standard's requirements.
<b>10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS</b>	Meets the product standard's requirements.
<b>10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION</b>	Meets the product standard's requirements.
<b>10.2.5 LIFTING</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.2.6 MECHANICAL IMPACT</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.2.7 INSCRIPTIONS</b>	Meets the product standard's requirements.

<b>CHARACTERISTIC CURVE</b>	<a href="#">eaton-circuit-breaker-nzm-mccb-characteristic-curve-020.eps</a> <a href="#">eaton-circuit-breaker-nzm-mccb-characteristic-curve-024.eps</a>
□□□□□	<a href="#">eaton-circuit-breakers-nzmb-nzmn-basic-unit-bg2-instruction-leaflet-il012099zu.pdf</a>
□□	<a href="#">eaton-circuit-breaker-nzm-mccb-dimensions-035.eps</a>

<b>10.3 DEGREE OF PROTECTION OF ASSEMBLIES</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.4 CLEARANCES AND CREEPAGE DISTANCES</b>	Meets the product standard's requirements.
<b>10.5 PROTECTION AGAINST ELECTRIC SHOCK</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS</b>	Is the panel builder's responsibility.
<b>10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS</b>	Is the panel builder's responsibility.
<b>10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH</b>	Is the panel builder's responsibility.
<b>10.9.3 IMPULSE WITHSTAND VOLTAGE</b>	Is the panel builder's responsibility.
<b>10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL</b>	Is the panel builder's responsibility.
<b>POLLUTION DEGREE</b>	3
<b>LIFESPAN, MECHANICAL</b>	20000 operations
<b>UTILIZATION CATEGORY</b>	A (IEC/EN 60947-2)
<b>MOUNTING METHOD</b>	Built-in device fixed built-in technique DIN rail (top hat rail) mounting optional Fixed
<b>CLIMATIC PROOFING</b>	Damp heat, cyclic, to IEC 60068-2-30 Damp heat, constant, to IEC 60068-2-78
<b>EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT</b>	3.27 W
<b>ISOLATION</b>	300 V AC (between the auxiliary contacts) 500 V AC (between auxiliary contacts and main contacts)
<b>AMBIENT OPERATING TEMPERATURE - MAX</b>	70 °C
<b>AMBIENT OPERATING TEMPERATURE - MIN</b>	-25 °C
<b>AMBIENT STORAGE TEMPERATURE - MAX</b>	70 °C
<b>AMBIENT STORAGE TEMPERATURE - MIN</b>	40 °C

<b>NUMBER OF AUXILIARY CONTACTS (CHANGE-OVER CONTACTS)</b>	0
<b>NUMBER OF AUXILIARY CONTACTS (NORMALLY CLOSED CONTACTS)</b>	0
<b>NUMBER OF AUXILIARY CONTACTS (NORMALLY OPEN CONTACTS)</b>	0
<b>PROTECTION AGAINST DIRECT CONTACT</b>	Finger and back-of-hand proof to DIN EN 50274/VDE 0106 part 110
<b>DEGREE OF PROTECTION</b>	IP20 (basic degree of protection, in the operating controls area) IP20
<b>DIRECTION OF INCOMING SUPPLY</b>	As required
<b>ELECTRICAL CONNECTION TYPE OF MAIN CIRCUIT</b>	Screw connection
<b>CURRENT RATING OF NEUTRAL CONDUCTOR</b>	0 - 60% - 100% of phase conductor
<b>OVERVOLTAGE CATEGORY</b>	III
<b>DEGREE OF PROTECTION (IP), FRONT SIDE</b>	IP40 (with insulating surround) IP66 (with door coupling rotary handle)
<b>DEGREE OF PROTECTION (TERMINATIONS)</b>	IP10 (tunnel terminal) IP00 (terminations, phase isolator and strip terminal)
<b>NUMBER OF POLES</b>	Four-pole
<b>TERMINAL CAPACITY (COPPER STRIP)</b>	Max. 10 segments of 24 mm x 0.8 mm at rear-side connection (punched) Min. 2 segments of 16 mm x 0.8 mm at rear-side connection (punched) Max. 8 segments of 24 mm x 1 mm (2x) at box terminal Min. 2 segments of 9 mm x 0.8 mm at box terminal Max. 10 segments of 16 mm x 0.8 mm at box terminal Min. 2 segments of 16 mm x 0.8 mm at rear-side connection (punched)
<b>LIFESPAN, ELECTRICAL</b>	10000 operations at 400 V AC-1 7500 operations at 690 V AC-1

	10000 operations at 415 V AC-1
<b>FUNCTIONS</b>	Earth-fault protection Systems, cable, selectivity and generator protection Zone selectivity Integrated earth fault protection
<b>EARTH-FAULT CURRENT SETTING (IG) - MAX</b>	63 x In
<b>TYPE</b>	Circuit breaker
<b>SPECIAL FEATURES</b>	<ul style="list-style-type: none"> <li>• LSIG overload protection and delayed and non-delayed short-circuit protective device, earth-fault protection</li> <li>• Class 1 energy measurement, r.m.s. value measurement, and "thermal memory"</li> <li>• USB interface for configuration and test function with Power Xpert Protection Manager software</li> <li>• Zone selectivity ZSI</li> <li>• Interface module in equipment supplied.</li> <li>• Optionally communication-capable with internal Modbus RTU module or CAM</li> <li>• Maximum back-up fuse, if the expected short-circuit currents at the installation location exceed the switching capacity of the circuit breaker (Rated short-circuit breaking capacity I<sub>cn</sub>)</li> <li>• Rated current = rated uninterrupted current: 63 A</li> </ul>
<b>APPLICATION</b>	Use in unearthed supply

	systems at 690 V
<b>SHOCK RESISTANCE</b>	20 g (half-sinusoidal shock 20 ms)
<b>EARTH-FAULT CURRENT SETTING (IG) - MIN</b>	20 x In
<b>POSITION OF CONNECTION FOR MAIN CURRENT CIRCUIT</b>	Front side
<b>RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)</b>	63 A
<b>RELEASE SYSTEM</b>	Electronic release
<b>SHORT-CIRCUIT TOTAL BREAKTIME</b>	< 10 ms
<b>RATED SHORT-TIME WITHSTAND CURRENT (T = 0.3 S)</b>	1.9 kA
<b>RATED SHORT-TIME WITHSTAND CURRENT (T = 1 S)</b>	1.9 kA
<b>SHORT-CIRCUIT RELEASE DELAYED SETTING - MAX</b>	630 A
<b>SHORT-CIRCUIT RELEASE DELAYED SETTING - MIN</b>	50 A
<b>SHORT-CIRCUIT RELEASE NON-DELAYED SETTING - MAX</b>	1134 A
<b>SHORT-CIRCUIT RELEASE NON-DELAYED SETTING - MIN</b>	126 A
<b>TERMINAL CAPACITY (CONTROL CABLE)</b>	0.75 mm <sup>2</sup> - 2.5 mm <sup>2</sup> (1x) 0.75 mm <sup>2</sup> - 1.5 mm <sup>2</sup> (2x)
<b>TERMINAL CAPACITY (COPPER BUSBAR)</b>	Max. 24 mm x 8 mm direct at switch rear-side connection Min. 16 mm x 5 mm direct at switch rear-side connection M8 at rear-side screw connection
<b>TERMINAL CAPACITY (COPPER SOLID CONDUCTOR/CABLE)</b>	10 mm <sup>2</sup> - 16 mm <sup>2</sup> (1x) at box terminal 6 mm <sup>2</sup> - 16 mm <sup>2</sup> (2x) direct at switch rear-side connection 6 mm <sup>2</sup> - 16 mm <sup>2</sup> (2x) at box terminal 10 mm <sup>2</sup> - 16 mm <sup>2</sup> (1x) direct at switch rear-side connection 16 mm <sup>2</sup> (1x) at tunnel terminal
<b>TERMINAL CAPACITY</b>	16 mm <sup>2</sup> (1x) at tunnel

<b>(ALUMINUM SOLID CONDUCTOR/CABLE)</b>	terminal
<b>TERMINAL CAPACITY (COPPER STRANDED CONDUCTOR/CABLE)</b>	25 mm <sup>2</sup> - 185 mm <sup>2</sup> (1x) at 1-hole tunnel terminal 25 mm <sup>2</sup> - 70 mm <sup>2</sup> (2x) direct at switch rear-side connection 25 mm <sup>2</sup> - 185 mm <sup>2</sup> (1x) at box terminal 25 mm <sup>2</sup> - 70 mm <sup>2</sup> (2x) at box terminal 25 mm <sup>2</sup> - 185 mm <sup>2</sup> (1x) direct at switch rear-side connection
<b>TERMINAL CAPACITY (ALUMINUM STRANDED CONDUCTOR/CABLE)</b>	25 mm <sup>2</sup> - 185 mm <sup>2</sup> (1x) at tunnel terminal
<b>HANDLE TYPE</b>	Rocker lever
<b>SHORT DELAY CURRENT SETTING (ISD) - MAX</b>	10 A
<b>SHORT DELAY CURRENT SETTING (ISD) - MIN</b>	2 A
<b>INSTANTANEOUS CURRENT SETTING (II) - MAX</b>	18 A
<b>INSTANTANEOUS CURRENT SETTING (II) - MIN</b>	2 A
<b>NUMBER OF OPERATIONS PER HOUR - MAX</b>	120
<b>OVERLOAD CURRENT SETTING (IR) - MAX</b>	63 A
<b>OVERLOAD CURRENT SETTING (IR) - MIN</b>	25 A
<b>RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 230 V, 50/60 HZ</b>	100 kA
<b>RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 400/415 V, 50/60 HZ</b>	70 kA
<b>RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 440 V, 50/60 HZ</b>	65 kA
<b>RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 525 V, 50/60 HZ</b>	36 kA
<b>RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 690 V,</b>	6 kA

