



□□□□

## Eaton 192284

Eaton Moeller series NZM - Molded Case Circuit Breaker. NZM3 PXR25 circuit breaker - integrated energy measurement class 1, 400A, 4p, variable, Screw terminal, H, 3

□□□□

<b>PRODUCT NAME</b>	Eaton Moeller series NZM molded case circuit breaker electronic
<b>CATALOG NUMBER</b>	192284
<b>PRODUCT LENGTH/DEPTH</b>	275 mm
<b>PRODUCT HEIGHT</b>	120.5 mm
<b>PRODUCT WIDTH</b>	185 mm
<b>PRODUCT WEIGHT</b>	8.45 kg
<b>COMPLIANCES</b>	RoHS conform
<b>CERTIFICATIONS</b>	IEC/EN 60947 IEC



Powering Business Worldwide

□□□□

<b>AMPERAGE RATING</b>	400 A
<b>VOLTAGE RATING</b>	690 V - 690 V
<b>CIRCUIT BREAKER FRAME TYPE</b>	NZM3
<b>FEATURES</b>	Protection unit Motor drive optional
<b>10.10 TEMPERATURE RISE</b>	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
<b>10.11 SHORT-CIRCUIT RATING</b>	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
<b>10.12 ELECTROMAGNETIC COMPATIBILITY</b>	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
<b>10.13 MECHANICAL FUNCTION</b>	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
<b>10.2.2 CORROSION RESISTANCE</b>	Meets the product standard's requirements.
<b>10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES</b>	Meets the product standard's requirements.
<b>10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT</b>	Meets the product standard's requirements.
<b>10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS</b>	Meets the product standard's requirements.
<b>10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION</b>	Meets the product standard's requirements.
<b>10.2.5 LIFTING</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.2.6 MECHANICAL IMPACT</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.2.7 INSCRIPTIONS</b>	Meets the product standard's requirements.

□□

<b>CHARACTERISTIC CURVE</b>	<a href="#">eaton-circuit-breaker-nzm-mccb-characteristic-curve-012.eps</a> <a href="#">eaton-circuit-breaker-nzm-mccb-characteristic-curve-016.eps</a>
□□□□□	<a href="#">eaton-circuit-breaker-basic-unit-bg3-il012100zu.pdf</a>
□□	<a href="#">eaton-circuit-breaker-nzm-mccb-dimensions-021.eps</a> <a href="#">eaton-circuit-breaker-switch-nzm-mccb-dimensions-016.eps</a>

<b>10.3 DEGREE OF PROTECTION OF ASSEMBLIES</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.4 CLEARANCES AND CREEPAGE DISTANCES</b>	Meets the product standard's requirements.
<b>10.5 PROTECTION AGAINST ELECTRIC SHOCK</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS</b>	Is the panel builder's responsibility.
<b>10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS</b>	Is the panel builder's responsibility.
<b>10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH</b>	Is the panel builder's responsibility.
<b>10.9.3 IMPULSE WITHSTAND VOLTAGE</b>	Is the panel builder's responsibility.
<b>10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL</b>	Is the panel builder's responsibility.
<b>POLLUTION DEGREE</b>	3
<b>LIFESPAN, MECHANICAL</b>	15000 operations
<b>UTILIZATION CATEGORY</b>	A (IEC/EN 60947-2)
<b>MOUNTING METHOD</b>	Built-in device fixed built-in technique Fixed
<b>CLIMATIC PROOFING</b>	Damp heat, constant, to IEC 60068-2-78 Damp heat, cyclic, to IEC 60068-2-30
<b>EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT</b>	72 W
<b>ISOLATION</b>	300 V AC (between the auxiliary contacts) 500 V AC (between auxiliary contacts and main contacts)
<b>AMBIENT OPERATING TEMPERATURE - MAX</b>	70 °C
<b>AMBIENT OPERATING TEMPERATURE - MIN</b>	-25 °C
<b>AMBIENT STORAGE TEMPERATURE - MAX</b>	70 °C
<b>AMBIENT STORAGE TEMPERATURE - MIN</b>	40 °C
<b>NUMBER OF AUXILIARY</b>	0

<b>CONTACTS (CHANGE-OVER CONTACTS)</b>	
<b>NUMBER OF AUXILIARY CONTACTS (NORMALLY CLOSED CONTACTS)</b>	0
<b>NUMBER OF AUXILIARY CONTACTS (NORMALLY OPEN CONTACTS)</b>	0
<b>PROTECTION AGAINST DIRECT CONTACT</b>	Finger and back-of-hand proof to DIN EN 50274/VDE 0106 part 110
<b>DEGREE OF PROTECTION</b>	IP20 (basic degree of protection, in the operating controls area) IP20
<b>DIRECTION OF INCOMING SUPPLY</b>	As required
<b>ELECTRICAL CONNECTION TYPE OF MAIN CIRCUIT</b>	Screw connection
<b>CURRENT RATING OF NEUTRAL CONDUCTOR</b>	0 - 60% - 100% of phase conductor
<b>OVERVOLTAGE CATEGORY</b>	III
<b>DEGREE OF PROTECTION (IP), FRONT SIDE</b>	IP40 (with insulating surround) IP66 (with door coupling rotary handle)
<b>DEGREE OF PROTECTION (TERMINATIONS)</b>	IP00 (terminations, phase isolator and strip terminal) IP10 (tunnel terminal)
<b>NUMBER OF POLES</b>	Four-pole
<b>TERMINAL CAPACITY (COPPER STRIP)</b>	10 segments of 50 mm x 1 mm (2x) at rear-side width extension Max. 10 segments of 32 mm x 1 mm + 5 segments of 32 mm x 1 mm at rear-side connection (punched)  Max. 8 segments of 24 mm x 1 mm (2x) at box terminal Max. 10 segments of 24 mm x 1 mm + 5 segments of 24 mm x 1 mm Min. 6 segments of 16 mm x 0.8 mm at box terminal Min. 6 segments of 16 mm x 0.8 mm at rear-side connection (punched)
<b>LIFESPAN, ELECTRICAL</b>	5000 operations at 415 V AC-1

	3000 operations at 690 V AC-1 5000 operations at 400 V AC-1
<b>FUNCTIONS</b>	Systems, cable, selectivity and generator protection
<b>TYPE</b>	Circuit breaker

**SPECIAL FEATURES**

- LSI overload protection and delayed and non-delayed short-circuit protective device
- Class 1 energy measurement, r.m.s. value measurement, and "thermal memory"
- USB interface for configuration and test function with Power Xpert Protection Manager software
- Interface module in equipment supplied.
- Optionally communication-capable with internal Modbus RTU module or CAM
- Maximum back-up fuse, if the expected short-circuit currents at the installation location exceed the switching capacity of the circuit breaker (Rated short-circuit breaking capacity  $I_{cn}$ )
- Rated current = rated uninterrupted current: 400 A
- Terminal capacity hint: Up to 240 mm<sup>2</sup> can be connected depending on the cable manufacturer.

<b>APPLICATION</b>	Use in unearthed supply
--------------------	-------------------------

	systems at 690 V
<b>SHOCK RESISTANCE</b>	20 g (half-sinusoidal shock 20 ms)
<b>POSITION OF CONNECTION FOR MAIN CURRENT CIRCUIT</b>	Front side
<b>RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)</b>	400 A
<b>RELEASE SYSTEM</b>	Electronic release
<b>SHORT-CIRCUIT TOTAL BREAKTIME</b>	< 10 ms
<b>RATED SHORT-TIME WITHSTAND CURRENT (T = 0.3 S)</b>	3.3 kA
<b>RATED SHORT-TIME WITHSTAND CURRENT (T = 1 S)</b>	3.3 kA
<b>SHORT-CIRCUIT RELEASE DELAYED SETTING - MAX</b>	4000 A
<b>SHORT-CIRCUIT RELEASE DELAYED SETTING - MIN</b>	320 A
<b>SHORT-CIRCUIT RELEASE NON-DELAYED SETTING - MAX</b>	4800 A
<b>SHORT-CIRCUIT RELEASE NON-DELAYED SETTING - MIN</b>	800 A
<b>TERMINAL CAPACITY (CONTROL CABLE)</b>	0.75 mm <sup>2</sup> - 1.5 mm <sup>2</sup> (2x) 0.75 mm <sup>2</sup> - 2.5 mm <sup>2</sup> (1x)
<b>TERMINAL CAPACITY (COPPER BUSBAR)</b>	Max. 10 mm x 50 mm (2x) at rear-side width extension Min. 20 mm x 5 mm direct at switch rear-side connection Max. 30 mm x 10 mm + 30 mm x 5 mm direct at switch rear-side connection M10 at rear-side screw connection
<b>TERMINAL CAPACITY (COPPER SOLID CONDUCTOR/CABLE)</b>	300 mm <sup>2</sup> (2x) at rear-side width extension 16 mm <sup>2</sup> (2x) at box terminal 16 mm <sup>2</sup> (1x) at tunnel terminal 16 mm <sup>2</sup> (2x) direct at switch rear-side connection 16 mm <sup>2</sup> (1x) direct at switch rear-side connection

<b>TERMINAL CAPACITY (ALUMINUM SOLID CONDUCTOR/CABLE)</b>	16 mm <sup>2</sup> (1x) at tunnel terminal
<b>TERMINAL CAPACITY (COPPER STRANDED CONDUCTOR/CABLE)</b>	35 mm <sup>2</sup> - 240 mm <sup>2</sup> (1x) at box terminal 25 mm <sup>2</sup> - 240 mm <sup>2</sup> (1x) direct at switch rear-side connection 16 mm <sup>2</sup> - 185 mm <sup>2</sup> (1x) at 1-hole tunnel terminal 25 mm <sup>2</sup> - 120 mm <sup>2</sup> (2x) at box terminal 25 mm <sup>2</sup> - 240 mm <sup>2</sup> (2x) direct at switch rear-side connection
<b>TERMINAL CAPACITY (ALUMINUM STRANDED CONDUCTOR/CABLE)</b>	25 mm <sup>2</sup> - 185 mm <sup>2</sup> (1x) at tunnel terminal 50 mm <sup>2</sup> - 240 mm <sup>2</sup> (1x) at 2-hole tunnel terminal 50 mm <sup>2</sup> - 240 mm <sup>2</sup> (2x) at 2-hole tunnel terminal
<b>HANDLE TYPE</b>	Rocker lever
<b>SHORT DELAY CURRENT SETTING (ISD) - MAX</b>	10 A
<b>SHORT DELAY CURRENT SETTING (ISD) - MIN</b>	2 A
<b>INSTANTANEOUS CURRENT SETTING (II) - MAX</b>	12 A
<b>INSTANTANEOUS CURRENT SETTING (II) - MIN</b>	2 A
<b>NUMBER OF OPERATIONS PER HOUR - MAX</b>	60
<b>OVERLOAD CURRENT SETTING (IR) - MAX</b>	400 A
<b>OVERLOAD CURRENT SETTING (IR) - MIN</b>	160 A
<b>RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 230 V, 50/60 HZ</b>	150 kA
<b>RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 400/415 V, 50/60 HZ</b>	150 kA
<b>RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 440 V, 50/60 HZ</b>	130 kA
<b>RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 525 V,</b>	33 kA

---

**50/60 HZ**

---

<b>RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 690 V, 50/60 HZ</b>	9 kA
--	------

---

<b>RATED SHORT-CIRCUIT MAKING CAPACITY ICM AT 400/415 V, 50/60 HZ</b>	330 kA
---	--------

---

<b>RATED SHORT-CIRCUIT MAKING CAPACITY ICM AT 440 V, 50/60 HZ</b>	286 kA
---	--------

---

<b>RATED SHORT-CIRCUIT MAKING CAPACITY ICM AT 525 V, 50/60 HZ</b>	143 kA
---	--------

---

<b>RATED SHORT-CIRCUIT MAKING CAPACITY ICM AT 690 V, 50/60 HZ</b>	74 kA
---	-------

---

<b>STANDARD TERMINALS</b>	Screw terminal
---------------------------	----------------

---

<b>OPTIONAL TERMINALS</b>	Box terminal. Connection on rear. Tunnel terminal
---------------------------	--

---

<b>RATED SHORT-CIRCUIT MAKING CAPACITY ICM AT 240 V, 50/60 HZ</b>	330 kA
---	--------

---

<b>RATED IMPULSE WITHSTAND VOLTAGE (UIMP) AT AUXILIARY CONTACTS</b>	6000 V
---	--------

---

<b>RATED IMPULSE WITHSTAND VOLTAGE (UIMP) AT MAIN CONTACTS</b>	8000 V
--	--------

---

<b>RATED INSULATION VOLTAGE (UI)</b>	690 V AC
--	----------

---

---

□□□□:
-------

---

□□□□:
-------

---

□□□:
------

---

□□:
-----

---



□□□□ Eaton House  
30 Pembroke Road  
Dublin 4, □□□  
Eaton.com

