

Eaton 192313

Eaton Moeller series NZM - Molded Case Circuit Breaker. NZM3 PXR25, class 1, 250A, 4p, variable, earth-fault protection, ARMS and zone selectivity, withdrawable unit, N, 3

PRODUCT NAME	Eaton Moeller series NZM molded case circuit breaker electronic
CATALOG NUMBER	192313
PRODUCT LENGTH/DEPTH	346 mm
PRODUCT HEIGHT	260 mm
PRODUCT WIDTH	230 mm
PRODUCT WEIGHT	6.65 kg
COMPLIANCES	RoHS conform
CERTIFICATIONS	IEC IEC/EN 60947

AMPERAGE RATING	250 A
VOLTAGE RATING	690 V - 690 V
CIRCUIT BREAKER FRAME TYPE	NZM3
FEATURES	Protection unit Motor drive optional
ACCESSORIES REQUIRED	NZM3-4-XAVS
10.10 TEMPERATURE RISE	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 SHORT-CIRCUIT RATING	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 ELECTROMAGNETIC COMPATIBILITY	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 MECHANICAL FUNCTION	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.
10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	Meets the product standard's requirements.
10.2.5 LIFTING	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 MECHANICAL	Does not apply, since the

CHARACTERISTIC CURVE	eaton-circuit-breaker-nzm-mccb-characteristic-curve-015.eps eaton-circuit-breaker-nzm-mccb-characteristic-curve-011.eps
	eaton-circuit-breaker-basic-unit-bg3-il012100zu.pdf eaton-circuit-breaker-switch-nzm-mccb-dimensions-016.eps eaton-circuit-breaker-withdrawable-unit-nzm-mccb-dimensions-002.eps eaton-circuit-breaker-nzm-mccb-dimensions-021.eps

IMPACT	entire switchgear needs to be evaluated.
10.2.7 INSCRIPTIONS	Meets the product standard's requirements.
10.3 DEGREE OF PROTECTION OF ASSEMBLIES	Does not apply, since the entire switchgear needs to be evaluated.
10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
POLLUTION DEGREE	3
MOUNTING METHOD	Built-in device slide-in technique (withdrawable) Withdrawable
CLIMATIC PROOFING	Damp heat, constant, to IEC 60068-2-78 Damp heat, cyclic, to IEC 60068-2-30
EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT	28.13 W
UTILIZATION CATEGORY	A (IEC/EN 60947-2)
ISOLATION	300 V AC (between the auxiliary contacts) 500 V AC (between auxiliary contacts and main contacts)
AMBIENT OPERATING TEMPERATURE - MAX	70 °C
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C

AMBIENT STORAGE TEMPERATURE - MAX	70 °C
AMBIENT STORAGE TEMPERATURE - MIN	40 °C
NUMBER OF AUXILIARY CONTACTS (CHANGE-OVER CONTACTS)	0
NUMBER OF AUXILIARY CONTACTS (NORMALLY CLOSED CONTACTS)	0
NUMBER OF AUXILIARY CONTACTS (NORMALLY OPEN CONTACTS)	0
PROTECTION AGAINST DIRECT CONTACT	Finger and back-of-hand proof to DIN EN 50274/VDE 0106 part 110
DEGREE OF PROTECTION	IP20 IP20 (basic degree of protection, in the operating controls area)
DIRECTION OF INCOMING SUPPLY	As required
ELECTRICAL CONNECTION TYPE OF MAIN CIRCUIT	Other
CURRENT RATING OF NEUTRAL CONDUCTOR	0 - 60% - 100% of phase conductor
LIFESPAN, MECHANICAL	15000 operations
OVERVOLTAGE CATEGORY	III
DEGREE OF PROTECTION (IP), FRONT SIDE	IP66 (with door coupling rotary handle) IP40 (with insulating surround)
DEGREE OF PROTECTION (TERMINATIONS)	IP10 (tunnel terminal) IP00 (terminations, phase isolator and strip terminal)
NUMBER OF POLES	Four-pole
TERMINAL CAPACITY (COPPER STRIP)	Max. 8 segments of 24 mm x 1 mm (2x) at box terminal Max. 10 segments of 32 mm x 1 mm + 5 segments of 32 mm x 1 mm at rear-side connection (punched) Min. 6 segments of 16 mm x 0.8 mm at box terminal Max. 10 segments of 24 mm x 1 mm + 5 segments

	of 24 mm x 1 mm Min. 6 segments of 16 mm x 0.8 mm at rear-side connection (punched) 10 segments of 50 mm x 1 mm (2x) at rear-side width extension
LIFESPAN, ELECTRICAL	5000 operations at 400 V AC-1 5000 operations at 415 V AC-1 3000 operations at 690 V AC-1
FUNCTIONS	Systems, cable, selectivity and generator protection ARMS maintenance mode Integrated earth fault protection Zone selectivity Earth-fault protection
EARTH-FAULT CURRENT SETTING (IG) - MAX	250 x In
TYPE	Circuit breaker

SPECIAL FEATURES

- LSIG overload protection and delayed and non-delayed short-circuit protective device, earth-fault protection
- Class 1 energy measurement, r.m.s. value measurement, and "thermal memory"
- USB interface for configuration and test function with Power Xpert Protection Manager software
- Zone selectivity ZSI
- Maintenance Mode ARMS
- Interface module in equipment supplied.
- Optionally communication-capable with internal Modbus RTU module or CAM

- Maximum back-up fuse, if the expected short-circuit currents at the installation location exceed the switching capacity of the circuit breaker (Rated short-circuit breaking capacity I_{cn})
- Rated current = rated uninterrupted current: 250 A
- Terminal capacity hint: Up to 240 mm² can be connected depending on the cable manufacturer.

APPLICATION	Use in unearthed supply systems at 690 V
SHOCK RESISTANCE	20 g (half-sinusoidal shock 20 ms)
EARTH-FAULT CURRENT SETTING (IG) - MIN	50 x I_n
POSITION OF CONNECTION FOR MAIN CURRENT CIRCUIT	Connection at separate chassis part
RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)	250 A
RELEASE SYSTEM	Electronic release
SHORT-CIRCUIT TOTAL BREAKTIME	< 10 ms
RATED SHORT-TIME WITHSTAND CURRENT (T = 0.3 S)	3.3 kA
RATED SHORT-TIME WITHSTAND CURRENT (T = 1 S)	3.3 kA
SHORT-CIRCUIT RELEASE DELAYED SETTING - MAX	2500 A
SHORT-CIRCUIT RELEASE DELAYED SETTING - MIN	200 A
SHORT-CIRCUIT RELEASE NON-DELAYED SETTING -	4500 A

MAX	
SHORT-CIRCUIT RELEASE NON-DELAYED SETTING - MIN	500 A
TERMINAL CAPACITY (CONTROL CABLE)	0.75 mm ² - 2.5 mm ² (1x) 0.75 mm ² - 1.5 mm ² (2x)
TERMINAL CAPACITY (COPPER BUSBAR)	Min. 20 mm x 5 mm direct at switch rear-side connection M10 at rear-side screw connection Max. 30 mm x 10 mm + 30 mm x 5 mm direct at switch rear-side connection Max. 10 mm x 50 mm (2x) at rear-side width extension
TERMINAL CAPACITY (COPPER SOLID CONDUCTOR/CABLE)	16 mm ² (2x) direct at switch rear-side connection 16 mm ² (1x) at tunnel terminal 16 mm ² (1x) direct at switch rear-side connection 16 mm ² (2x) at box terminal 300 mm ² (2x) at rear-side width extension
TERMINAL CAPACITY (ALUMINUM SOLID CONDUCTOR/CABLE)	16 mm ² (1x) at tunnel terminal
TERMINAL CAPACITY (COPPER STRANDED CONDUCTOR/CABLE)	25 mm ² - 120 mm ² (2x) at box terminal 25 mm ² - 240 mm ² (2x) direct at switch rear-side connection 16 mm ² - 185 mm ² (1x) at 1-hole tunnel terminal 25 mm ² - 240 mm ² (1x) direct at switch rear-side connection 35 mm ² - 240 mm ² (1x) at box terminal
TERMINAL CAPACITY (ALUMINUM STRANDED CONDUCTOR/CABLE)	50 mm ² - 240 mm ² (1x) at 2-hole tunnel terminal 50 mm ² - 240 mm ² (2x) at 2-hole tunnel terminal 25 mm ² - 185 mm ² (1x) at tunnel terminal
HANDLE TYPE	Rocker lever
SHORT DELAY CURRENT	10 A

SETTING (ISD) - MAX	
SHORT DELAY CURRENT SETTING (ISD) - MIN	2 A
INSTANTANEOUS CURRENT SETTING (II) - MAX	18 A
INSTANTANEOUS CURRENT SETTING (II) - MIN	2 A
NUMBER OF OPERATIONS PER HOUR - MAX	60
OVERLOAD CURRENT SETTING (IR) - MAX	250 A
OVERLOAD CURRENT SETTING (IR) - MIN	100 A
RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 230 V, 50/60 HZ	85 kA
RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 400/415 V, 50/60 HZ	50 kA
RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 440 V, 50/60 HZ	35 kA
RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 525 V, 50/60 HZ	13 kA
RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 690 V, 50/60 HZ	5 kA
RATED SHORT-CIRCUIT MAKING CAPACITY ICM AT 400/415 V, 50/60 HZ	105 kA
RATED SHORT-CIRCUIT MAKING CAPACITY ICM AT 440 V, 50/60 HZ	74 kA
RATED SHORT-CIRCUIT MAKING CAPACITY ICM AT 525 V, 50/60 HZ	53 kA
RATED SHORT-CIRCUIT MAKING CAPACITY ICM AT 690 V, 50/60 HZ	40 kA
STANDARD TERMINALS	Screw terminal
OPTIONAL TERMINALS	Box terminal. Connection

	on rear. Tunnel terminal
RATED SHORT-CIRCUIT MAKING CAPACITY ICM AT 240 V, 50/60 HZ	187 kA
RATED IMPULSE WITHSTAND VOLTAGE (UIMP) AT AUXILIARY CONTACTS	6000 V
RATED IMPULSE WITHSTAND VOLTAGE (UIMP) AT MAIN CONTACTS	8000 V
RATED INSULATION VOLTAGE (UI)	690 V AC

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

